



## Reliable, affordable, and compact color inkjet printer perfect for at home use.

### Color Inkjet All-in-One Printer

The Brother Work Smart 1360 offers consistent results, ease-of-use, and seamless connectivity options in a compact footprint that is ideal for home use at an affordable price.

- Wireless connectivity and integration with the Brother Mobile Connect app<sup>6</sup>
- 1.8" color display enables printing from and scanning to Cloud-based apps<sup>5</sup>
- Automatic duplex (2-sided) printing
- 20-sheet single-sided automatic document feeder (ADF)<sup>10</sup>
- 150-sheet paper tray<sup>10</sup>
- Fast print speeds of up to 16 pages per minute (ppm) in black and 9ppm in color.<sup>1</sup>

### Specifications:

Print	
Print Technology	4-cartridge Color Inkjet
Simplex Print Speed (max.) <sup>1</sup>	Black: Up to 16.0ppm Color: Up to 9.0ppm
Time to First Page <sup>2</sup>	Black: Approx. 6.2 seconds Color: Approx. 9.6 seconds
Print Resolution (max.)	Windows: Up to 1,200 x 6,000 dpi Mac: 1,200 x 3,600 dpi
Borderless Printing	Up to 8.5" x 11" (Letter)
Scan	
Scan Speeds (max.) <sup>3</sup>	Up to 17.0ipm / 7.0ipm (black / color)
Scan Resolution (max.)	ADF (optical): Up to 1,200 x 600 dpi Glass (optical): Up to 1,200 x 2,400 dpi Interpolated: Up to 19,200 x 19,200 dpi <sup>4</sup>
Scan To Capability	PC (Image, Email, OCR, File), Chromebooks, Cloud Services <sup>5</sup> , Mobile Devices <sup>6</sup> , Easy Scan to Email <sup>7</sup>
Advanced Scanning Features	Auto deskew, Blank page skip, Background color removal
Duplex Scan	No
Copy	
Copy Speed <sup>8</sup>	Up to 11.0cpm / 3.5cpm (black / color)
Copy Resolution (max.)	Up to 1,200 x 1,200 dpi
Copy Options	Sorting, N-in-1, Multi-copying (up to 99), Reduce / Enlarge 25 - 400% in 1% increments
Duplex Copy	No
Connectivity & Compatibility	
Standard Interfaces	Wireless 802.11b/g/n (2.4GHz) / 802.11a/n (5GHz), Hi-Speed USB 2.0
Operating Systems Compatibility <sup>9</sup>	For the latest OS compatibility and to download drivers, visit support.brother.com.
Mobile Device Compatibility <sup>6</sup>	AirPrint®, Mopria®, Brother Mobile Connect, Wi-Fi Direct
Cloud Services (Web Connect) <sup>5</sup>	Scan to: Google Drive™, Evernote®, OneDrive, OneNote, Dropbox, Box, SharePoint Online
Brother Cloud Apps <sup>7</sup>	Easy Scan to Email, Cloud Secure Print, Scan to Searchable PDF, Scan to Word, Scan to Excel, Scan to PowerPoint, Email Print
Security	
Security Features	Enterprise Security (802.1x), SSL/TLS, IP Filter
Paper Handling	
Paper Input Capacity (max.) <sup>10</sup>	150-sheets paper tray
Output Capacity (max.) <sup>10</sup>	50 sheets
Document Glass Size	Up to 8.5" x 11" (Letter)
Auto Document Feeder Capacity <sup>10</sup>	20 pages
Paper Size (max.)	Standard Tray: Up to 8.5" x 14" (Legal) Duplex: Up to 8.5" x 11" (Letter) ADF: Up to 8.5" x 14" (Legal) <sup>11</sup>
Media Types	Standard Tray: Plain Paper, Inkjet Paper, Glossy Paper, Recycled Paper, Envelopes, Index Cards
Media Weights	Standard Tray: 17 to 58 lbs ADF: 17 to 24 lbs Duplex: 17 to 28 lbs
General	
Automatic Duplex Capability	Print Only
Display	1.8" Color Display
Processor	576 MHz
Memory (std.)	256 MB
Included Software <sup>6</sup>	Brother Mobile Connect for iOS® and Android™ Brother iPrint&Scan (desktop) BRAdmin Light
Refresh EZ Print Subscription Eligible	Yes
Energy Star® Qualified	Yes
EPEAT Certified	Yes (Silver Rated)
Maximum Monthly Duty Cycle <sup>12</sup>	Up to 2,000 pages
Recommended Monthly Volume <sup>13</sup>	50 to 1,000 pages
Warranty	1-year limited warranty

### Replacement Supplies & Optional Accessories:



LC501BKS	Standard Yield Black Ink Cartridge (250 pages) <sup>14</sup>
LC501CS	Standard Yield Cyan Ink Cartridge (200 pages) <sup>14</sup>
LC501MS	Standard Yield Magenta Ink Cartridge (200 pages) <sup>14</sup>
LC501YS	Standard Yield Yellow Ink Cartridge (200 pages) <sup>14</sup>
LC501 3PKS	3 Pack of Standard Yield Cyan, Magenta, and Yellow Ink Cartridges (200 pages) <sup>14</sup>
LC501XLBKS	High Yield Black Ink Cartridge (500 pages) <sup>14</sup>
LC501XLCS	High Yield Cyan Ink Cartridge (500 pages) <sup>14</sup>
LC501XLMMS	High Yield Magenta Ink Cartridge (500 pages) <sup>14</sup>
LC501XLYS	High Yield Yellow Ink Cartridge (500 pages) <sup>14</sup>
LC501XL 2PKS	Twin Pack of High Yield Black Ink Cartridges (500 pages per cartridge) <sup>14</sup>
LC501XL 3PKS	3 Pack of High Yield Cyan, Magenta, and Yellow Ink Cartridges (500 pages) <sup>14</sup>

### Dimensions / Weights:

Unit Dimensions / Weight	15.4" (W) x 13.5" (D) x 7.2" (H) / 16.8 lbs.
Carton Dimensions / Weight	18.2" (W) x 10.2" (D) x 18.0" (H) / 20.2 lbs.

### Carton Contents:

Brother MFC-J1360DW, Starter Black Ink Cartridge (200 pages)<sup>14</sup>, Starter Cyan, Magenta, Yellow Ink Cartridges (200 pages)<sup>14</sup>, AC Power Cord, Product Safety Guide, Reference Guide, Warranty Card, Quick Setup Guide



#### Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.

COMPATIBLE WITH  
**WINDOWS**



- Print speed based on ISO/IEC 24734. Based on single-sided printing.
- From ready mode and standard tray.
- Scan speed based on ISO/IEC 17991.
- Windows only.
- Requires an Internet connection and an account with desired service.
- Requires connection to a wireless network. May require free download. Compatibility may vary by device and operating system.
- Requires an Internet connection.
- Copy speed based on ISO/IEC 24735.
- For the latest OS compatibility and to download drivers, visit support.brother.com. Printing or scanning via macOS requires the use of AirPrint. Mac printer drivers are not provided.
- Maximum capacity based on using 20 lb. paper.
- Documents greater than 11.7" in length must be fed one at a time through the ADF.

- Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.
- The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.
- Approx. ink cartridge yield in accordance with ISO/IEC 24711 (letter/A4)