

LG UltraWide™ Monitor

Curved

34-inch UltraWide™ Curved Monitor

34BQ65VA-B



* Images shown are for illustration purposes only.

- 34-inch WQHD (3440 x 1440) Curved Display
- sRGB over 99% (Typ.) with HDR 10
- 100Hz Refresh Rate
- 3-side Virtually Borderless Design
- USB Type-C®
(Power Delivery 65W, Transmitting AV & Data)
- PBP & OnScreen Control
- Ergonomic Stand



Expansive Screen with Lifelike Detail to Maximize Productivity

34-inch WQHD | HDR10 | 100Hz Refresh Rate |
3-side Virtually Borderless Design

The 34BQ65VA features a fully immersive 34-inch 21:9 UltraWide™ HDR10 display, which delivers a more authentic, dynamic immersive experience and allows users to view multiple webpages and streams of critical information seamlessly. The WQHD (3440 x 1440) resolution with a speedy 100Hz refresh rate which allows for a smoother screen experience and the 3-side Virtually Borderless Design increases work immersion for an optimized workflow.

Sensible Connectivity for Optimal Manageability

USB Type-C® (Power Delivery 65W, Transmitting AV & Data) |
PBP | OnScreen Control

The 34BQ65VA comes bundled with a host of intuitive features, including OnScreen Control and PBP modes, which allow users to adjust, personalize, and view a wide range of display options and significant information such as ppts and notes simultaneously in a matter of clicks. In addition, the reversible capabilities of the USB Type-C® port allow users to charge connected devices from a laptop with a single cable while transmitting AV and data to create a manageable workflow.

Efficient Ergonomic Design and Sustainability

Ergonomic Stand¹⁾ | One Click Stand | EPEAT®²⁾

Thanks to its sensible ergonomic design, the 34BQ65VA provides customizable height and tilt adjustments so that users can optimize screen placement according to their needs for comfortable usage. It also meets the EPEAT® performance requirements.

* Images shown are for illustration purposes only.


1) Tilt (-5 ~ 20°), Height (110 mm)

2) 34BQ65VA certified EPEAT® Bronze by Global Electronics Council, which evaluates environmental performance criteria such as energy efficiency, material sourcing, and end-of-life management.

For more details, <https://www.epeat.net/search-computers-and-displays>.

Specifications

Model		34BQ65VA-B
Display	Size	34-inch
	Borderless Design	3-side Virtually Borderless Design
	Resolution	WQHD (3440 x 1440)
	Panel Type	VA
	Brightness (Typ.)	300 cd/m²
	Color Gamut (Typ.)	sRGB 99% (CIE1931)
	Contrast Ratio (Typ.)	3000:1
	Response Time (GtG)	5ms (GtG at faster)
	Refresh Rate	-
Features	HDR 10	Yes
	Flicker Safe	-
	Reader Mode	Yes
	Color Weakness	Yes
	Super Resolution+	Yes
	Black Stabilizer	Yes
	Dynamic Action Sync	Yes
	Smart Energy Saving	Yes
SW Application	OnScreen Control	Yes
	Dual Controller	Yes
Connectivity	HDMI	Yes (2ea)
	DisplayPort	Yes (1ea)
	USB	Yes (2ea, USB 3.2 Gen1 Downstream)
	USB Type-C®	Yes (1ea, Power Delivery 65W, Transmitting AV & Data)
	H/P Out	Yes
Power	Type	External Power (Adapter)
	AC Input	100~240V (50/60Hz)
	Power Consumption (Sleep Mode / DC Off)	0.5W / Less than 0.3W
Mechanical	Stand Adjustments	Tilt (-5 ~ 20°)
	Height	4.3 in / 110 mm
	Wall Mountable	Yes (3.9 x 3.9 in)
	Dimension with Stand (W x H x D)	31.9 x 22.4 x 10.2 in / 809 x 568.3 x 260mm (Up), 31.9 x 18 x 10.2 in / 809 x 458.3 x 260mm (Down)
Standard	Weight with Stand	17 lbs / 7.7 kg
	EPEAT®	Bronze
	ENERGY STAR®	Yes



Life's Good.