



PERFORMANCE

Processor
Intel® Core Ultra 7 265, 20C (8P + 12E) / 20T, Max Turbo up to 5.3GHz, 30MB

AI PC Category
AI PC^[1]

NPU
Integrated Intel® AI Boost, up to 13 TOPS

Graphics
NVIDIA® GeForce RTX™ 5060 8GB GDDR7

Chipset
Intel® Q870 Chipset

Memory
1x 32GB SODIMM DDR5-5600

Memory Slots
Two DDR5 SODIMM slots, dual-channel capable

Max Memory^[2]
Up to 64GB DDR5-5600

Storage
1TB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Max Storage Support^[3]
Up to four drives, 4x M.2 SSD • M.2 SSD up to 2TB each^[4]

RAID Preset
None

Card Reader
No card reader

Optical
None

Audio Chip
High Definition (HD) Audio, one of Realtek® ALC233VB / Realtek ALC256 / Conexant CX11771 codec.

Speakers
2Wx1

Power Supply
350W 92%

DESIGN

Keyboard
USB, Calliope, Black, English (US)

Mouse
USB Calliope Mouse, Black

Expansion Slots
Five M.2 slots (one for WLAN, four for SSD / discrete NPU)

Case Color
Luna Grey

Pen
Pen Not Supported

Form Factor
Tiny (3.6L)

Dimensions (WxDxH)^[5]
• Ultra (without rubber feet) | 195 x 191 x 108 mm (7.68 x 7.52 x 4.25 inches)
• Ultra (with rubber feet) | 195 x 191 x 111 mm (7.68 x 7.52 x 4.37 inches)

Weight^[6]
Around 3.7 kg (8.2 lbs)

CONNECTIVITY

WLAN + Bluetooth
Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®

WWAN
Non-WWAN

Ethernet
Integrated 100/1000M

Front Ports
• 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), data transfer only
• 2x USB-A (USB 10Gbps / USB 3.2 Gen 2), one supports 5V@2.1A charging
• 1x headphone / microphone combo jack (3.5mm)

Rear Ports^[7]
• 1x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer and DisplayPort™ 1.4b)
• 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
• 3x USB-A (USB 10Gbps / USB 3.2 Gen 2), one supports Smart Power On
• 1x HDMI® 2.1 TMDS
• 1x HDMI® 2.1b FRL
• 1x DisplayPort™ 1.4b
• 3x DisplayPort™ 2.1b
• 1x Ethernet (GbE RJ-45)

Optional Rear Ports (configured)
• Thunderbolt™ 4
• 3x DP 2.1b, 1x HDMI® 2.1b FRL on NVIDIA® GeForce RTX™ 5060

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Fingerprint Reader
No fingerprint reader

Physical Locks
Kensington® Security Slot™

MANAGEABILITY

System Management^[8]
Intel® vPro® Enterprise

SERVICE

Base Warranty
1-year, Onsite

Included Upgrade
None

CERTIFICATIONS

Green Certifications
• ErP Lot 3
• GREENGUARD®
• RoHS compliant
• TCO Certified, generation 10

Other Certifications
TÜV Rheinland® Low Noise

SOFTWARE

Operating System
Windows® 11 Pro, English

Bundled Software
None

ACCESSORIES

Bundled Accessories
None

MODEL

TopSeller	: Yes	EAN / UPC / JAN:	199272766285
Announce Date:	2025-08-26	End of Support	: 2032-01-10

Note:
^[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft Copilot key or using Win + C.
^[2] The max memory is based on the test results with current Lenovo memory offerings.
^[3] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.
^[4] Discrete NPU and 1st SSD are mutually exclusive.
^[5] The system dimensions may vary depending on configurations.
^[6] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
^[7] For video ports on discrete graphics, please see [graphics section](#)
^[8] Intel vPro offers a superset of DASH’s defined capabilities.
· Lenovo reserves the right to change specifications without notice.

Premier Support - A direct 24x7x365 line to our most elite technicians.

- 

Advanced technical support, 24x7x365, in more than 100 markets
- 

Technical Account Managers for proactive relationship and escalation management
- 

Comprehensive hardware & OEM software support
- 

Priority on service delivery and repair parts
- 

Single point of contact for simplified end-to-end case management
- 

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Self-Charging Bluetooth Keyboard-French Canadian 058 4Y41R69498



Lenovo Wired VoIP Headset 5000 4XD1R88995

Please click [here](#) to view the full list of accessories.

Recommended Services

BEST	4Y Premier Support Plus upgrade from 1Y Onsite (5WS1L39138)
BETTER	3Y Premier Support Plus upgrade from 1Y Onsite (5WS1L39561)
GOOD	3Y Premier Support Upgrade from 1Y Onsite (5WS0T36147)



PSREF
Product Specifications
Reference