



Cost-efficient printing, advanced scanning features, and reliable business performance

Business Color Laser All-in-One Printer

The Brother MFC-L8730CDW combines business quality, cost-efficient output, advanced scanning and security features, and expandable paper capacity, making it an excellent choice for busy offices and work teams.

- Fast printing and copying up to 33ppm¹
- Includes 3,000-page black / 1,800-page color toner cartridges. Cost-efficient output using 5,500-page black / 4,500-page color replacement toner cartridges¹⁸
- 300-sheet paper capacity¹⁴, expandable up to 800 sheets²³
- 80-page capacity auto document feeder¹⁴ offers two-sided scanning up to 58ipm to popular cloud services⁸
- 3.5" color touchscreen enables the creation of up to 48 customized shortcuts



MFC-L8730CDW

Business Color Laser All-in-One Printer with Duplex Print, Scan, Copy, Wireless Networking, and Advanced Security Features

brother
at your side

Specifications:

| Print | |
|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Print Technology | Electrophotographic Laser |
| Print Speeds (max.) ¹ | Up to 33ppm color / black |
| Time to First Page ² | Less than 9.9 seconds color / black |
| Print Resolution (max.) | Up to 2400 x 600 dpi class |
| Print Emulations | PCL6, BR-Script3 ³ , PDF Version 2.0 |
| Scan | |
| Scan Speeds (max.) ⁴ | Simplex: Up to 29ipm (black / color); Duplex: Up to 58ipm (black / color) |
| Scan Resolution (max.) | ADF (optical): Up to 600 x 600 dpi; Glass (optical): Up to 1200 x 1200 dpi; Interpolated ⁵ : Up to 19200 x 19200 dpi |
| Scan To Capability | PC (Image, E-mail, OCR, File), Network Folder ⁶ , E-mail Server ⁶ , SharePoint, FTP, FTPS, SSH Server (SFTP), USB Memory Stick ⁷ , Cloud Services (Web Connect) ⁸ , Mobile Devices ⁹ , Easy Scan to E-mail ¹⁰ |
| Advanced Scanning Features | Auto deskew, Blank page skip, Scan preview, File split, Multi-page to single-page, Base color removal, Scan profiles |
| Copy | |
| Copy Speed / Copy Resolution (max.) | Up to 33 cpm / Up to 1200 x 600 dpi |
| Copy Options | Sorting, N-in-1, Multi-copying (up to 999) Reduce / Enlarge 25 - 400% in 1% increments |
| Fax | |
| Fax Features | 33.6K bps modem speed, Fax page memory: up to 500 pages ¹¹ , Fax forward to: Network Folder ⁵ and E-mail, Internet Fax ¹⁰ , PC Fax ¹² |
| Connectivity & Compatibility | |
| Standard Interfaces | Dual Band Wireless 802.11b/g/n (2.4GHz) / 802.11a/n (5GHz), Gigabit Ethernet, Hi-Speed USB 2.0 |
| USB Host | Front: Print from and scan to USB memory stick; external card reader |
| Operating Systems Compatibility ¹³ | For the latest OS compatibility and to download drivers, visit support.brother.com |
| Mobile Device Compatibility ⁹ | AirPrint [®] , Mopria [™] , Brother Mobile Connect, Wi-Fi Direct [®] |
| Cloud Services (Web Connect) ⁸ | Google Drive [™] , Evernote [®] , OneDrive, OneNote, Dropbox, Box, SharePoint Online |
| Brother Cloud Apps ¹⁰ | Easy Scan to E-mail, Scan to Mobile, Cloud Secure Print, Fax Forward to Cloud or E-mail, Scan to Searchable PDF, Scan to Word, Scan to Excel, Scan to PowerPoint, E-mail Print |
| Security | |
| Security Features | Integrated NFC Card Reader, External Card Reader Compatibility, Active Directory, Enterprise Security (802.1x), Secure Print, SSL/TLS, IP Filter, Syslog Reporting, SNMP v3, LDAP, OAuth (SMTP, POP3, IMAP4), Secure Boot, Secure Function Lock, Setting Lock, Store Print Log, Firmware Encryption |
| Paper Handling | |
| Paper Input Capacity (max.) ¹⁴ | 250-sheet standard tray, 50-sheet multipurpose tray |
| Optional Input Capacity (max.) ¹⁴ | 800 sheets via optional trays |
| Output Capacity (max.) ¹⁴ | 150 sheets (face down), 1 sheet (face up) |
| Document Glass Size | Up to 8.5" x 11" (Letter) |
| Auto Document Feeder Capacity ¹⁴ | 80 pages |
| Paper Sizes (max.) | Standard Tray: Letter, Legal, Executive, A4, A5, A6, Folio Multipurpose Tray: 3" - 8.5" (W) / 5" - 14" (L) Duplex: Letter, Legal, Folio |
| Media Types | Standard Tray: Plain Paper, Recycled Paper, Colored Paper, Letterhead Multipurpose Tray: Plain Paper, Recycled Paper, Labels, Envelopes (up to 10), Glossy Paper (single sheet), Colored Paper, Letterhead |
| Media Weights ¹⁵ | Standard Tray: 16 to 28 lbs.; Multipurpose Tray: 16 to 43 lbs.; ADF: 16 to 28 lbs. |
| General | |
| Automatic Duplex | Print (default setting), plus single-pass copy, scan, fax |
| Display / Customizable Shortcuts | 3.5" Color Touchscreen / 48 |
| Processor | 1.2 GHz |
| Memory (std. / max.) | 512MB / 512MB |
| Included Software ⁹ | Brother Mobile Connect for iOS and Android [™] , Brother iPrint&Scan (desktop) for Windows and Mac [®] , BRAdmin Light ⁶ , BRAdmin Pro 4 ⁶ , Tungsten PaperPort [™] 14SE ⁵ |
| Optional Brother Value Added Services | Secure Print+, Remote Panel, Remote Connect, Custom UI, Barcode Print+, Barcode Utility, ThinPrint Client, Secure Print Advanced, Request Help, Order Supplies |
| Optional Solutions | 3manager, PaperCut, rndPrint, uniFLOW, Tungsten ControlSuite |
| Energy Star [®] Qualified | Yes |
| EPEAT Certified | Yes (Silver Rated) |
| Maximum Monthly Duty Cycle ¹⁶ | Up to 60,000 pages |
| Recommended Monthly Volume ¹⁷ | Up to 5,000 pages |
| Warranty | 1-year limited warranty |

Replacement Supplies & Optional Accessories:

| | |
|--------------|-------------------------------------------------------------------------------------------------|
| TN635BK | Standard Yield Toner Cartridge (3,000 pages) ¹⁸ |
| TN635C/M/Y | Standard Yield Toner Cartridge (1,800 pages) ¹⁸ |
| TN635 3PK | 3 Pack of Standard Yield Cyan, Magenta, and Yellow Toner Cartridges (1,800 pages) ¹⁸ |
| TN635XLBK | High Yield Toner Cartridge (5,500 pages) ¹⁸ |
| TN635XLC/M/Y | High Yield Toner Cartridge (4,500 pages) ¹⁸ |
| TN635XL 2PK | Twin Pack of High Yield Black Toner Cartridges (5,500 pages per cartridge) ¹⁸ |
| DR635CL | Drum Unit (30,000 pages) ¹⁹ |
| BU635CL | Belt Unit (50,000 pages) ²⁰ |
| WT229CL | Waste Toner Box (50,000 pages) ²¹ |
| FD-5000 | Fuser Unit (100,000 pages) ²² |
| PF-M5000 | Multipurpose Tray Paper Feeding Kit (50,000 pages) ²¹ |
| LT-350CL | Optional 250-Sheet Capacity Paper Tray ¹⁴ |
| CB-1010 | Optional 15.7" Printer Cabinet / Stand |
| CH-1000 | Optional Card Reader Holder |

Dimensions / Weights:

| | |
|----------------------------|-----------------------------------------------|
| Unit Dimensions / Weight | 15.9" (W) x 18.6" (D) x 18.1" (H) / 56.5 lbs. |
| Carton Dimensions / Weight | 25.6" (W) x 22" (D) x 25.3" (H) / 73.1 lbs. |

Carton Contents:

Brother MFC-L8730cdw, TN635BK Black Toner Cartridge (3,000 pages)¹⁸, TN635C/M/Y Cyan, Magenta, Yellow Toner Cartridges (1,800 pages)¹⁸, DR635CL Drum Unit (30,000 pages)¹⁹, BU635CL Belt Unit (50,000 pages)²⁰, WT229CL Waste Toner Box (50,000 pages)²¹, AC Power Cord, Quick Setup Guide, Telephone Line Cord



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.

COMPATIBLE WITH

WINDOWS



1 Based on one-sided printing. Change from default required.

2 From ready mode and standard tray.

3 PostScript3TM compatible.

4 Color and monochrome scan speeds in accordance with ISO/IEC 17991 with all advanced features turned off, using letter-sized paper at 200/300dpi.

5 Windows only.

6 Requires mail server support.

7 PDF (up to ver. 1.7), JPEG, XPS files. Secure PDF / Signed PDF scan only.

8 Requires an Internet connection and an account with desired service.

9 May require free download. Compatibility may vary by device and operating system. May require connection to a wireless network.

10 Requires an Internet connection.

11 Using ITU-T Test Chart #1 with JBIG coding and standard resolution.

12 B&W only. PC Fax Receive not available for Mac users.

13 For the latest OS compatibility and to download drivers, visit support.brother.com. Printing or scanning via macOS requires the use of AirPrint. Mac printer drivers are not provided. For Windows Server: USB connection supports printing and scanning; network connections support printing only.

14 Maximum capacity based on using 20 lb. paper.

15 Print speed may vary depending on size/type of paper used and paper source.

16 Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

17 The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.

18 Approximate toner cartridge yield in accordance with ISO/IEC 19798 (letter/A4).

19 Approximately 30,000 pages based on 1 page per job and 50,000 pages based on 3 pages per job (letter/A4 single-sided pages). The number of pages may be affected due to a variety of factors, including but not limited to media type and media size.

20 Approximately 50,000 pages based on 1 page per job and 100,000 pages based on 3 pages per job (letter/A4 single-sided pages). The number of pages may be affected due to a variety of factors, including but not limited to media type and media size.

21 Approximately 50,000 pages based on 5 pages per job (letter/A4 single-sided pages). The number of pages may be affected due to a variety of factors, including but not limited to media type and media size.

22 Approximately 100,000 pages based on 5 pages per job (letter/A4 single-sided pages). The number of pages may be affected due to a variety of factors, including but not limited to media type and media size.

23 Requires additional purchase.