



[DOWNLOAD SPECS](#)

imageCLASS MF663Cdw

General

Functions	Print, Scan, Copy
Print Speed	Up to 26ppm (Letter)
Document Feeder	50 sheet
First Print Out Time	Approximately 10.3 Seconds (Black / Colour, Letter)
Print Resolution	Up to 1200 x 1200 dpi
Copy / Scan Resolution	Up to 600 x 600 dpi
Print Memory	1 GB (Shared)
Printer Language	UFR II
Network Security	IP/MAC Address Filtering, IPSEC, TLS 1.3, SNMP V3.0, IEEE 802.1X, IPv4/IPv6, SMTP Authentication, POP3

Connectivity	USB 2.0 High-Speed, 10/100/1000Base-T/TX Ethernet (Network), Wi-Fi 802.11b/g/n, Wi-Fi® Direct Connection
Operating Systems	Windows® 11 / 10 / 8.1 / Windows® Server 2012 / 2012 R2 / 2016 / 2019 / 2022, Mac OS X (10.11 or later)
Paper Capacity	250-Sheet Standard Cassette, 50-sheet Simplex Automatic Document Feeder, 1-Sheet Manual Feed Slot
Min/Max Paper Size	Standard Cassette / 1-sheet Manual Feed Slot: 3" x 5" to 8.5" x 14"
USB Direct Print	JPG, TIFF, PDF
Display Panel	5 inch, Colour Touch LCD
Print Volumes	150-2,500 Pages
Energy Consumption	Approx: 1080 W (Max.), 9 W (Standby), 0.7 W (Sleep Mode)
Energy Star Certified	Yes
EPEAT	Silver
Unit Dimensions	16.8"(W) x 18.2"(D) x 15.7"(H)
Unit Weight	48.5 lbs.
