



Classic EQ USB-C® Headset with Mic and Volume Control

Part Number: K97464WW | UPC Code: 0 85896 97464 2

The essential USB-C® headset.

Whether attending virtual meetings, making calls, testing and doing homework, or simply listening to music, professionals and students alike need an affordable headset that delivers clear audio, whilst remaining comfortable and compatible with the latest USB-C® devices.

The Classic EQ USB-C® Headset with Mic and Volume Control allows you to communicate clearly. The passive noise-cancelling design reduces background noise for improved clarity and focus, and an in-line volume and mute controller offers convenience.

The adjustable padded headband and soft leatherette earpads provide hours of comfortable use. The plastic used in the Classic EQ USB-C® Headset contains 36% post-consumer recycled content.*

- Windows, macOS, iOS, iPadOS, Android, and ChromeOS compatible
- Adjustable headband and soft foam earpads
- 6.5ft (2m) long braided cable
- Passive noise-cancelling design
- Microphone can be worn on left or right side
- Built-in volume and mute controls on cord
- Safe listening limit protects ears: EN 50332-2 compliant
- 36% post-consumer recycled (PCR) plastic*
- Stereo sound with 40mm drivers
- 2-year limited warranty

*Excludes Printed Circuit Board (PCB) assembly.

Kensington®

Classic EQ USB-C® Headset with Mic and Volume Control

Part Number: K97464WW | UPC Code: 0 85896 97464 2



USB-C® Connection

Compatible with the latest USB-C® devices running Windows, macOS, iOS, iPadOS, Android, and ChromeOS.




Adjustable Comfort for All Head Sizes

Designed to provide a comfortable fit for all ages, the adjustable headband is padded and the foam earpads are wrapped in a soft leatherette cover.




6.5ft (2m) Nylon Braided Cord

The long braided cable supports flexible movement and improved durability.




Passive Noise-Cancelling Design with Stereo Sound

Passive resistance technology filters out ambient noise for improved clarity. 40mm drivers provide a well balanced audio experience.



Rotating Microphone with In-Line Controls

The microphone rotates up to 270°, allowing you to wear it on the left or right side. The volume and mute controls are integrated into the cord for quick and easy access.



Safe Listening Limit

EN 50332-2 compliant for safe listening, the maximum output is limited to protect ears from hearing loss associated with prolonged exposure.



Sustainability Attributes

The plastic in the Classic EQ USB-C® headset contains 36% post-consumer recycled (PCR) content*.



2-Year Limited Warranty

Backed by Kensington's professional support and a 2-year limited warranty.

Classic EQ USB-C® Headset with Mic and Volume Control

Part Number: K97464WW | UPC Code: 0 85896 97464 2

Audio Specifications

Driver Unit	40mm mylar speakers
Speaker Impedance	32Ω ± 150%
Rated Input Power	15mW
Maximum Input Power	20mW
Headphone Sensitivity	88± 5dB (Input Power=-10dBFS at 1kHz)
Headset Frequency Response	20Hz - 20kHz
Microphone Sensitivity	-27± 5dB at 1K Hz (0dB=1V/Pa)
Mic Current	0.5mA max

Product Specifications

Unit Dimensions	Width: 5.9in (150mm) Length: 7.28in (185mm) Height: 2.76in (70mm)
Inline Control Unit	Volume adjustment, mute/unmute
Rotatable Microphone	270°
Unit Weight	0.32lbs (0.145kg)
USB Cable Length	6.56 ft (2m)
Color and Material	<ul style="list-style-type: none">• Black / ABS housing• Nylon braided cable• Steel headband (SUS304)• Headband cushion: PU, foam

Packaging

Part Number	Packaging Style	Dimensions	Weight (including the products inside)
K97464WW (B2B packaging) UPC Code: 0 85896 97464 2	Bulk pack (10 units per master carton; 4 master carton per shipper carton)	Individual Packaging 5.67 x 2.8 x 7.09in (144 x 71 x 180mm)	0.224kg (0.4938lbs)
		Master Carton 12.60 x 12.20 x 7.80in (320 x 310 x 198mm)	1.97kg (4.34lbs)
		Shipper Carton 25.20 x 13.39 x 16.93in (640 x 340 x 430mm)	8.94kg (19.71lbs)



Classic EQ USB-C® Headset with Mic and Volume Control

Part Number: K97464WW | UPC Code: 0 85896 97464 2

Environmental

Storage Temperature	-20 to 60°C (-4 to 140°F)
Working Temperature	-10 to 50°C (14 to 122°F)
Relative Humidity	Up to 80% non-condensing

Country of Origin, Regulatory & Warranty

Country of Origin	China
Compliance & Certificates	FCC, IC, CE, UKCA, RCM, EN 50332-2, EU REACH, RoHS/WEEE, CA Prop 65, ACCO RSL
Warranty	2-Year Worldwide



All specifications are subject to change without notice. Products may not be available in all markets. Kensington and the ACCO name and design are registered trademarks of ACCO Brands. Kensington The Professionals' Choice is a trademark of ACCO Brands. All other registered and unregistered trademarks are the property of their respective owners. Thunderbolt and the Thunderbolt logo are trademarks of Intel Corporation in the U.S. and/or other countries. © 2025 Kensington Computer Products Group, a division of ACCO Brands. All rights reserved. k25-23087p

Kensington
The Professionals' Choice™

FOR MORE INFORMATION CONTACT: contact@kensington.com