



PRO DP400 14

PRO DP400 14NVR-011US

Specification

Manufacturer Part #	DP40014NVR011
OS	Windows 11 Pro
CPU	Intel® Core™ i7-14700F 20C/28T 33MB Cache
Chipset	Intel B760
Motherboard	MSI Proprietary
CPU Cooler	Air Cooled
VGA	GeForce RTX 5070 Ti
Memory (GB)	64GB' DDR5 U-DIMM (4 x 16GB @3000GHz) 6000 MHz
LAN	Realtek® RTL8125BG 2.5G LAN
Wireless Communication	WIFI 6E - AX 211
Audio	Front: 1 x Mic-in/Headphone-out Rear: 3 x Audio Jack
Video Port	1 x HDMI-out (supports 4K @60Hz as specified in HDMI 2.1) 1 x DP-out (1.4)
Expansion Slots	3 x M.2 Slots 4 x SATA 6G 1x 2.5” HDD/SSD 1x 3.5” HDD
USB	Front: 1 x USB 3.2 Gen 2 Type C 1 x USB 3.2 Gen 1 Type A Rear: 2 x USB 2.0 Type A 2 x USB 3.2 Gen 2 Type A 1 x USB 2.3 Gen 2 Type C
HDD/SSD	2TB M.2 NVMe
ODD	Super Multi ODD Drive
Peripherals	Wireless Copilot KBMS Set(BLK)
Power Supply	ATX 750W PSU
Power Efficiency Level	80Plus Gold
Chassis Size	19.5” x 19” x 9
VESA	N/A
Color	BLK
Dimensions	19.5” x 19” x 9
Weight	25.3lbs
Warranty	3 Year