



PERFORMANCE

Processor
Intel Core™ Ultra 5 225, 10C (6P + 4E) / 10T, Max Turbo up to 4.9GHz, 20MB Intel® Smart Cache

AI PC Category
AI PC^[1]

Graphics
Integrated Intel® Graphics

Chipset
Intel® B860 Chipset

Memory
1x 32GB UDIMM DDR5-5600

Memory Slots
Two DDR5 UDIMM slots, dual-channel capable

Max Memory^[2]
Up to 64GB DDR5-5600

Storage
1TB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Max Storage Support^[3]
• Up to three drives, 1x 3.5” HDD + 2x M.2 SSD • 3.5” HDD up to 2TB
• M.2 SSD up to 1TB each
• To install a HDD storage, 3.5” HDD screw and grommet kit is needed.

Card Reader
No Card Reader

Optical
None

Audio Chip
• High Definition (HD) Audio, Realtek® ALC623-CG codec
• 24-bit DAC supports 44.1K/48K/96K sample rate, 2 channel DAC supports 16/20/24-bit PCM format for independent two stereo channel or 2.1 audio playback
• 24-bit ADC supports 44.1K/48K/96K sample rate, 2 channel ADC supports 16/20/24-bit PCM format for independent two stereo channel audio inputs

Speakers
1Wx1

Power Supply
200W 90%

DESIGN

Keyboard
USB, Calliope, Black, English (US)

Mouse
USB Calliope Mouse, Black

Expansion Slots
• One PCIe® 4.0 x16, low-profile, length ≤ 155mm, height ≤ 70mm
• One PCIe® 3.0 x1, low-profile, length ≤ 155mm, height ≤ 70mm

• Three M.2 slots (one for WLAN, two for SSD)

Case Color
Raven Black

Stand
Vertical Stand

Pen
Pen Not Supported

Form Factor
SFF (8.2L)

Dimensions (WxDxH)^[4]
92.5 x 291.7 x 339.5 mm (3.6 x 11.5 x 13.4 inches)

Weight^[5]
Around 4.62 kg (10.19 lbs)

CONNECTIVITY

WLAN + Bluetooth
Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

WWAN
WWAN Not Supported

Ethernet
Integrated 100/1000M

Front Ports
• 1x USB-C® (USB 5Gbps / USB 3.2 Gen 1), with 15W charging
• 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
• 1x headphone / microphone combo jack (3.5mm)
• 1x microphone (3.5mm)

Rear Ports
• 2x USB-A (Hi-Speed USB / USB 2.0)
• 2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one supports Smart Power On
• 1x HDMI® 2.1 TMDS
• 1x DisplayPort™ 1.4
• 1x Ethernet (RJ-45)
• 1x line-out (3.5mm)

Optional Rear Ports (configured)
• 1x USB-A (Hi-Speed)
• 2x USB 3.2 Gen 1
• 1x Serial

Monitor Cable
None

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Physical Locks
• Kensington Security Slot™, 3 x 7 mm
• Padlock Loop

Smart Cable Clip

None

Chassis Intrusion Switch
None

Additional Security
None

MANAGEABILITY

System Management
Non-vPro®

SERVICE

Base Warranty
1-year, Onsite

Included Upgrade
None

CERTIFICATIONS

Green Certifications
RoHS / WEEE / REACH

SOFTWARE

Operating System
Windows® 11 Pro, English

Bundled Software
None

ACCESSORIES

Bundled Accessories
None

MODEL

TopSeller : Yes **EAN / UPC / JAN:** 199273030095

Announce Date: 2025-10-07 **End of Support** : 2032-04-09

Note:
[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft Copilot key or using Win + C.
[2] The max memory is based on the test results with current Lenovo memory offerings.
[3] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.
[4] The system dimensions may vary depending on configurations.
[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

• Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.

• Lenovo reserves the right to change specifications without notice.

Premier Support - A direct 24x7x365 line to our most elite technicians.

- 

Advanced technical support, 24x7x365, in more than 100 markets
- 

Technical Account Managers for proactive relationship and escalation management
- 

Comprehensive hardware & OEM software support
- 

Priority on service delivery and repair parts
- 

Single point of contact for simplified end-to-end case management
- 

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Dual-Mode Wireless ANC Headset 6550 (USB-C, Teams) 4XD1S19778



Lenovo Self-Charging Bluetooth Keyboard-French Canadian 058 4Y41R69498

Please click [here](#) to view the full list of accessories.

Recommended Services

BEST	4Y Premier Support Upgrade from 1Y Onsite (5WS1P43513)
BETTER	3Y Premier Support Upgrade from 1Y Onsite (5WS1P43563)
GOOD	3Y Onsite upgrade from 1Y Onsite (5WS1P43508)



PSREF
Product Specifications
Reference