




SPECIFICATIONS

Product Name	MAG FORGE M100R
Case Form Factor	Micro ATX Tower
Motherboard Form Factor Support	Micro-ATX / Mini-ITX
I/O Ports	2x USB 2.0 Type-A 1x USB 3.2 Gen 1 Type-A 1x Audio 1x Mic
Drive Mount Support	2x 2.5" 1x 2.5" / 3.5" 1x 3.5"
Expansion Slots	4
Maximum GPU Length	300 mm / 11.81 inches
Maximum CPU Cooler Height	160 mm / 6.3 inches
Power Supply Support	ATX
Maximum PSU Length	300 mm / 11.81 inches (without 3.5" HDD tray installed)
Fan Size Support	Front: 3 x 120 mm Top: 2 x 120 mm Rear: 1 x 120 mm
Pre-installed Fan Size	Front: 3 x 120mm Rear: 1 x 120mm
Pre-installed Fan Type	Front: 3 x ARGB Fan Rear: 1 x ARGB Fan
Radiator Size Support	Front: 120 / 240 mm Top: 120 / 240 mm Rear: 120 mm
Dimensions (DxWxH)	388 x 200 x 423mm / 15.28 x 7.87 x 16.65 inches
Net Weight	4.14 kg / 9.13 lbs
Gross Weight	5.03 kg / 11.09 lbs

FEATURES



Optimized Air Flow

Can install up to 6x system fans, providing ventilation and stable performance to the whole system.



ARGB Fan

Built-in ARGB fan with striking lighting and vivid lighting effects.



1 to 6 ARGB LED Control board

Bundle with 1 to 6 ARGB LED control board that gives you more ways to decorate your gaming rig.



Tempered Glass

Premium-grade 3mm thick tempered glass that guarantees window durability and viewing capability.



Magnetic Filter

The magnetic dust filter on top is designed to give users an easy un-installing and cleaning experience.

CONNECTIONS



1. Power Button
2. Reset Button
3. Mic in / Audio out
4. 2x USB 2.0 Type-A
5. 1x USB 3.2 Gen 1 Type-A
6. LED Switch Button



PC CASE

MAG FORGE M100R

BEYOND THE POWER

