

PERFORMANCE

Processor

Intel® Core™ Ultra 9 275HX, 24C (8P + 16E) / 24T, Max Turbo up to 5.4GHz, 36MB

AI PC Category^[1]

AI-Powered Gaming PC

NPU

Integrated Intel® AI Boost, up to 13 TOPS

Graphics

NVIDIA® GeForce RTX™ 5070 Ti 12GB GDDR7, Boost Clock 2220MHz, TGP 140W, 992 AI TOPS

Chipset

Intel® HM870 Chipset

Memory

2x 16GB CSODIMM DDR5-6400

Memory Slots

Two DDR5 CSODIMM slots, dual-channel capable

Max Memory^[2]

Up to 32GB DDR5-6400 offering

Storage

2x 1TB SSD M.2 2280 PCIe® 4.0x4 NVMe®

Storage Slot

Two M.2 slots

- One M.2 2280 PCIe® 5.0 x4 slot
- One M.2 2280 PCIe® 4.0 x4 slot

Max Storage Support^[3]

Up to two drives, 2x M.2 SSD

- M.2 2242 SSD up to 1TB
- M.2 2280 SSD up to 2TB

Audio Chip

High Definition (HD) Audio, Realtek® ALC3306 codec

Speakers

4 stereo speakers, 2W x2 (woofers), 2W x2 (tweeters), optimized with Nahimic Audio, Smart Amplifier (AMP)

Microphone

2x, Array

Camera

5.0MP with E-shutter

Battery

99.9Wh

Power Adapter

400W Slim Tip (3-pin)

Special Features

AI Chip: LA3

DESIGN

Display

16" WQXGA (2560x1600) OLED 500nits (Typical) / 1100nits (Peak) Glossy, 100% DCI-P3, 240Hz, DisplayHDR™ True Black 1000, Dolby Vision®, G-SYNC®, Low Blue Light, High Gaming Performance, Flicker Free

Screen-to-Body Ratio

92% AAR (active area ratio)

Color Calibration

Factory Color Calibration

Pen

Pen Not Supported

Keyboard

Per-key RGB Backlit, French / English

Touchpad

Buttonless Mylar® surface multi-touch touchpad, 75 x 120 mm (2.95 x 4.72 inches)

Dimensions (WxDxH)^[4]

364.38 x 275.94 x 21.9-26.65 mm (14.35 x 10.86 x 0.86-1.05 inches)

Weight^[5]

Starting at 2.57 kg (5.67 lbs)

Case Color

Eclipse Black

Case Material

Aluminium (Top), Aluminium (Bottom)

Surface Treatment

Anodizing Sandblasting

SOFTWARE

Operating System

Windows® 11 Home, French / English

Bundled Software

Office Trial

CONNECTIVITY

WLAN + Bluetooth^[6]

Wi-Fi® 7, 802.11be 2x2 + BT5.4

WWAN

Non-WWAN

Ethernet

2.5GbE (RJ-45)

Standard Ports

- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 65-100W and DisplayPort™ 2.1
- 1x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer and DisplayPort™ 2.1)
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (2.5GbE RJ-45)
- 1x Power connector

Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit ,

[Docking for Legion Pro 7 16IAX10H](#)

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0 Enabled

Other Security

E-shutter

SERVICE

Base Warranty

1-year, Courier or Carry-in

CERTIFICATIONS

Green Certifications

- ErP Lot 3
- RoHS compliant

Other Certifications

- TÜV Rheinland® Flicker Free
- TÜV Rheinland® High Gaming Performance
- TÜV Rheinland® Low Blue Light (Hardware Solution)

MODEL

TopSeller	: No	Announce Date	: 2025-04-24
EAN / UPC / JAN	: 198157894068	End of Support	: 2031-03-08

Note:

[1] AI-Powered Gaming PCs feature Lenovo AI Engine+ and NVIDIA GeForce RTX GPUs to handle AI-driven tasks and deliver exceptional gaming performance.

[2] The max memory is based on the test results with current Lenovo memory offerings.

[3] The storage capacity supported is based on the test.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo USB-C 7-in-1 Hub

4X90V55523

Travel - Ready Productivity. One-stop travel docking is finally here. Connect and charge new and legacy devices wherever you happen to be. Sleek and compact, the Lenovo USB-C 7-in-1 Hub fits unlimited productivity i...

Recommended Services

BEST	3Y Premium Care Plus upgrade from 1Y Courier/Carry-in (5WS1J38691)
BETTER	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0T73708)
GOOD	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0K76347)

Please click [here](#) to view the full list of accessories.



PSREF
Product Specifications
Reference