

COUNTER
STRIKE 2

AGON
BY AOC



UNLEASH POTENTIAL

CLAIM VICTORY

EXPLORED BY

CS25G

FAST IPS | HDR400 | **G-SYNC COMPATIBLE** | 310HZ | **0.3MS MPRT/1MS GTG** | LOW INPUT LAG

CS MODE | JOINT LOGO BOOST SCREEN | **GAMING MODE** | GAME COLOR | **SNIPER SCOPE** | DARK BOOST

MBR SYNC | SHADOW CONTROL | **FLICKER FREE** | G-MENU | **ANTI-BLUE LIGHT** | CS2 THEMED OSD

www.aoc.com

AOC

► Features



Rule the Competition with Fast IPS

Fast IPS annihilates the competition with a speed 4x faster than conventional IPS. Guaranteeing you true 1ms (GTG) response times and captivating visual quality, raise your gaming performance to the next level!



Illuminate your visuals

VESA-certified DisplayHDR 400 delivers a significant step-up from normal SDR displays. Unlike other 'HDR compatible' screens, true Display HDR 400 produces astonishing brightness, contrast and colors. With global dimming and peak brightness up-to 400 nits, images come to life with notable highlights while featuring deeper, more nuanced blacks. It renders a fuller palette of rich new colors, delivering a visual experience that engages your senses.



The e-sports professional standard for gaming

With a 310Hz refresh rate and 0.3ms response time, your display will be equipped to perform at the pro gaming standard. Enjoy an ultra-smooth experience with no visible screen blur to ensure you're always prepped to win.



Connecting your eyes with your hands

Unleash your reflexes by switching to AOC Low Input Lag mode. Forget graphical frills: this mode rewires the monitor in favor of raw response time, giving you the ultimate edge in a hair-trigger standoff.



Elevating your gaming experience

Experience seamless gameplay with our innovative MBR Sync technology. By combining MPRT with Adaptive Sync, we've revolutionized your gaming visuals, banishing motion blur and ghosting from your screen. Enjoy crisp, lightning-fast graphics that remain consistently sharp, even during intense gameplay sessions and at high frame rates. Say goodbye to distractions and hello to unparalleled gaming immersion.



Optimize your game settings

Activate CS Mode with a single click to unlock in-game enhancements, including sharper visuals, optimized gamma, reduced input lag, and ultra-smooth motion for the ultimate Counter-Strike experience.



Protect your eyes from screen flicker

Flicker-free technology reduces flicker to give you a more comfortable gaming experience. Normal LED-backlit monitors adjust brightness using PWM (Pulse Width Modulation) which causes flickering and results in eye discomfort over long periods of time. AOC flicker-free technology uses a DC (Direct Current) backlight system to provide a more comfortable and healthier viewing experience, minimizing the effects of eye fatigue during long, intense gaming sessions!



Sleek design with height adjustability

An adjustable stand allows for tilt, rotation, swivel and height adjustment to dial-in a comfortable and ergonomic viewing experience.



One place to control settings for your gaming experience with AOC G-MENU

With AOC G-MENU, you have one place to dial in your settings for your visual gaming experience on an intuitive GUI-based menu.

► Specifications

Model Name	CS25G
Panel	24.5" (Fast IPS)
Pixel Pitch (mm)	0.2832 (H) × 0.2802 (V)
Effective Viewing Area (mm)	543.744 (H) × 302.616 (V)
Brightness (typical)	350 cd/m ²
Contrast Ratio	1000 : 1, 1/MEGA DCR
Response Time	0.3ms (MPRT) / 1ms (GtG)
Viewing Angle	178° (H) / 178° (V) (CR > 10)
Color Gamut	NTSC 100% (CIE1976) / sRGB 117% (CIE1931) DCI-P3 91% (CIE1976)
Color Accuracy	Delta E < 2
Optimum Resolution	1920 × 1080 @ 310Hz (OC) – DisplayPort 1.4 1920 × 1080 @ 240Hz – HDMI 2.0
Display Colors	16.7 Million
Signal Input	HDMI 2.0 × 2 / DisplayPort 1.4 × 1
HDCP Version	HDMI: 2.3 / DisplayPort: 2.3
Power Supply	Internal 100 - 240V~1.5A, 50 / 60Hz
Power Consumption (typical)	30W
Speakers	no
Line in & Earphone	Earphone
Wall-Mount	100mm × 100mm
Adjustable Stand	Height: 130mm, Pivot: -90° ~ 90°, Swivel: -30° ~ 30°, Tilt: -5° ~ 23°
Product without Stand (mm)	324.8 (H) × 560.1 (W) × 52.1 (D)
Product with Stand (mm)	380.6~498.5 (H) × 560.1 (W) × 207.6 (D)
Packaging (mm)	481 (H) × 780 (W) × 162 (D)
Product without Stand (kg)	2.81
Product with Stand (kg)	4.63
Product with Packaging (kg)	8.15
Cabinet Color	-
Regulatory Approvals	CE / CB / FCC / RoHS