

Delight Your Life

Featuring a very patterned mesh front panel, the DLITE is designed to ensure optimal airflow. Front and rear fans are fully integrated structurally. Accented by mirror's signature two-brushed 5mm aluminum strip, exuding refined elegance. Available in stylish Matte Black and Matte White finishes, the DLITE's minimalist design and layout deliver a visually cohesive, high-quality build. The DLITE infuses clean lines and clever design into your daily life.

Next-Gen Ready

This streamlined ATX chassis supports up to 8 PCIe slots, offering full compatibility with the latest graphics cards. Its vertical GPU mount fits the latest graphics cards. Its flexible layout is designed to highlight top-tier components, balancing visual appeal with structural integrity.

Versatile GPU Support

DLITE is compatible with mirror's new cable bracket, allowing you to showcase your graphics card with both horizontal and vertical installation options.

*Please ensure your GPU is equipped with the required connectors for your chosen orientation.



Back-Connector Builds

This mid-tower case supports ATX motherboards and is fully compatible with back-connector motherboards, offering cleaner cable management and a more efficient build process. Perfectly aligned with the evolving needs of modern PC builders.

*Supports MSI, GIGABYTE and ASUS Back-Connector motherboards.

Flexible Cooling

Supporting up to 10 fans and 360 mm radiators, it offers flexible cooling options to maximize airflow and thermal efficiency. DLITE is ready to power your high-performance setup.

*Fits Intel(LGA 1700) Thermalright PA120 SE with TL-C12C-S Fans

Model	AM120
Colors	Black
Fan Size	120 x 120 x 25 mm
Materials	ABS PC
Rated Voltage	DC 12V
Rated Power	1.92W
Rated Current	0.16
ARGB Rated Voltage	DC 5V
ARGB Rated Power	0.6W
ARGB Rated Current	0.12A
Speed Mode	PWM 810 - 1500 RPM
Air Flow	61.80 CFM
Air Pressure	1.29 mm H2O
LED	Addressable RGB
Connector to MB	4-Pin (1x PWM), 3-Pin (5V, ARGB)
Noise Level	30.7 dB(A)
Bearing Type	Hydro-wi Bearing

* mirror's products comply with RoHS regulations.
* Specifications may vary based on different regions.

Full-Size Compatibility

Despite its compact footprint, the DLITE offers a spacious interior that supports full-sized components. It can accommodate GPUs up to 380 mm and power supplies up to 220 mm, with ample space for cable management.

Specifications

Model	DLITE
Model Number	WH-DLITEBMG-WHRGB / WH-DLITEFWA-WHRGB
Colors	Matte Blonde / Lilac Steel
Case Type	Mid Tower
Materials	SPCC, Tempered Glass, Aluminum, ABS
M/B Compatibility	ATX, Micro-ATX, Mini-ITX
Expansion Slots	8 + 1
Maximum Compatibility	GPU: Max 380 mm CPU: Heatsink Height: 165 mm
I/O Ports	1 x USB 5.0 Gen 2x2 Type-C 2 x USB 5.0 Gen 1 HD Audio (CTIA) - SPK/MIC Power Button with Green Switch Power Button
Internal Drive Bays	2 x 3.5" / 2 x 2.5"
Internal Drive Bays	Air Cooling Fans: Front: 3 x 120 mm ARGB PWM Fan (Pre-installed) Top: 3 x 120 / 2 x 140 mm Rear: 1 x 120 mm ARGB PWM Fan (Pre-installed) Bottom: 2 x 120 mm (Optional) Side: 2 x 120 mm Water Cooling Radiator: Front: 120/240/360 mm Top: 120/240/360 mm Rear: 120 mm
Power Supply Compatibility	PSU: ATX(R) Length: up to 200 mm
Product Dimensions (L x W x H)	464 x 240 x 508 mm 17.6 x 9.61 x 20.0"
Package Dimensions (L x W x H)	586 x 322 x 582 mm 23.4 x 12.7 x 23.1"
Net Weight	9.26 kg
Gross Weight	10.11 kg

* mirror's products comply with RoHS regulations.
* Specifications may vary based on different regions.