

LG Monitor

27-inch QHD Monitor

27BQ410B-B - 27-inch QHD Monitor



* Images shown are for illustration purposes only.

- 27-inch QHD (2560 x 1440) IPS Display
- 100Hz Refresh Rate
- Low Blue Light (Reader Mode)
- 3-side Virtually Borderless Design
- Tilt Stand / LG Switch
- Dual Controller



Effortless productivity

QHD (2560 x 1440) IPS Display | Dual Controller | LG OnScreen Control

The QHD resolution (2560 x 1440) IPS Monitor delivers precise and consistent color, featuring sharper resolutions. Its Dual Controller allows users to work with multiple devices via a single monitor, keyboard, and mouse. Doing so significantly improves productivity as users can drag and drop files from various devices into a single monitor. LG OnScreenControl lets users to customize their workspace in just a few simple clicks for a more simplified setup. Users can connect two LG QHD monitors and a laptop using respective cables for improved efficiency.

Comfortably immersive workstation

Tilt Stand | Built-in Power | 100Hz |
Low Blue Light(Reader Mode) & Flicker Safe

Its adjustable tilt design helps promote productivity, and users can easily adjust its display position as they desire, allowing them to remain comfortably immersed in what is on their screen. It also features Built-in Power, allowing for a cleaner, clutter-free setup. Its Low Blue Light (Reader Mode) adjusts the monitor's color temperature and luminance to reduce blue light emissions and allow for comfortable long-term viewing. With Flicker Safe, onscreen flicker levels are significantly reduced, which helps to reduce eye fatigue during lengthy workflows. The headphone-out port supports direct audio monitoring and helps maintain a tidy, professional workspace.


Specifications

Model		27BQ410B-B
Display	Size	27-inch
	Resolution	QHD (2560 x 1440)
	Panel Type	IPS
	Brightness (Typ.)	200 / 250 cd/m2
	Color Gamut (Typ.)	sRGB 99% (CIE1931)
	Refresh Rate	100 Hz
	Broderless Design	3-side Virtually Borderless Design
Features	Features	HDR 10, Flicker Safe, Low Blue Light (Reader Mode), Color Weakness, Super Resolution+, Auto Input Switch, Smart Energy Saving
	Picture Mode	(SDR) : Custom, Vivid, HDR Effect, Reader, Cinema, FPS, RTS, Color Weakness, (HDR): Custom, Vivid, Cinema, FPS, RTS
	Auto Pivot	Yes
SW Application	LG Switch	Yes
	Dual Controller	Yes
Connectivity	USB Type-C™	Yes (1ea, PD 15W)
	H/P Out	3-pole (Sound Only)
Power	Type	External Power (Adapter)
	AC Input	100~240V (50/60Hz)
	Power Consumption (Sleep Mode / DC Off)	0.5W / Less than 0.3W
Mechanical	Stand Adjustments	Tilt (-5~20°)
	Wall Mountable	Yes (394 x 394 in)
	Dimension with Stand (W x H x D)	24.1 x 17.9 x 8.5 in
Warranty		Limited 3yr Warranty

Various Ports

Adjustable Tilt

What's in the box



*The product's image is for illustrative purposes only and may differ from the actual product.
 *The size and design of the adapter may differ depending on the country.
 *The availability of power cords may differ depending on the country.

Easy and comfy



*The images simulated.

Life's Good.



#LoveWhatYouSeeLG



@LGforBusinessUSA

Copyright 2026 ©LG Electronics USA, Inc., 2000 Millbrook Drive Lincolnshire, IL 60069, USA. All rights reserved. LG and the LG logo are registered trademarks of LG Corp. All other products and brand names are trademarks or registered trademarks of their respective companies. Designs, features, and specifications are subject to change without notice. All screen images are simulated for illustrative purposes only. SPEC_27BQ410B-B_0126_6.0A

