



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- Snapdragon X X1-26-100, 8C, Max Turbo up to 3.0GHz, 30MB
- 32GB Soldered LPDDR5X-8448
- 1TB SSD M.2 2280 PCIe 4.0x4 NVMe Opal 2.0
- Integrated Qualcomm Adreno GPU
- Windows 11 Pro (on ARM), English
- Case color - Eclipse Black
- 1-year, Onsite

Premier Support - A direct 24x7x365 line to our most elite technicians.

- Advanced technical support, 24x7x365, in more than 100 markets
- Technical Account Managers for proactive relationship and escalation management
- Comprehensive hardware & OEM software support
- Priority on service delivery and repair parts
- Single point of contact for simplified end-to-end case management
- Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Recommended Accessories United Kingdom




ThinkPad Bluetooth Presenter Mouse (Aura Edition)

4Y51T62792



Lenovo Analog In-Ear Headphones Gen II Bulk Package (20pcs)

4XD1T54899



ThinkCentre 1TB Value PCIe Gen4 NVMe OPAL 2.0 M.2 2280 SSD II

4XB1T87552

>> [View More Accessories](#)

Recommended Services

Best

3Y Premier Support Upgrade from 1Y Onsite (5WSOT36147)

Better

5Y Onsite upgrade from 1Y Onsite (5WSOD80928)

Good

3Y Onsite upgrade from 1Y Onsite (5WSOD80967)

PERFORMANCE

Processor

Snapdragon® X X1-26-100, 8C, Max Turbo up to 3.0GHz, 30MB

AI PC Category

Copilot+ PC^[1]

NPU

Integrated Qualcomm® Hexagon™ NPU, up to 45 TOPS

Graphics

Integrated Qualcomm® Adreno™ GPU

Chipset

Qualcomm® SoC Platform

Memory

32GB Soldered LPDDR5X-8448

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory^[2]

32GB soldered memory, not upgradable

Storage

1TB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Max Storage Support^[3]

Up to two drives, 2x M.2 SSD • M.2 2280 SSD up to 1TB

Card Reader

No card reader

Optical

None

Audio Chip

High Definition (HD) Audio, Qualcomm® WCD9385 codec and WSA8845 amplifier

Speakers

2Wx1

Power Supply

65W 89% Adapter

DESIGN

Keyboard

USB, Calliope, Black, English (US)

Mouse

USB Calliope Mouse, Black

Expansion Slots

Three M.2 slots (one for WLAN, two for SSD)

Case Color

Eclipse Black

Stand

None

Adapter Cage

None

Toolless Chassis Screw

None

Mounting

None

IO Box

No IO box

Pen

Pen Not Supported

Form Factor

Tiny (1L)

Dimensions (WxDxH)^[4]

- Tiny only (without rubber feet) | 179 x 182.9 x 34.5 mm (7.05 x 7.2 x 1.36 inches)
- Tiny only (with rubber feet) | 179 x 182.9 x 36.5 mm (7.05 x 7.2 x 1.44 inches)

Weight^[5]

Around 1.13 kg (2.49 lbs)

CONNECTIVITY

WLAN + Bluetooth

Qualcomm® Wi-Fi® 6E NFA765A, 802.11ax 2x2 + BT5.3

WWAN

WWAN Not Supported

Ethernet

Integrated 100/1000M

Front Ports

- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with data transfer and 5V@0.9A charging
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), with Always On and 5V@2.1A charging
- 1x headphone / microphone combo jack (3.5mm)

Rear Ports

- 2x USB-A (Hi-Speed USB / USB 2.0)
- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x HDMI® 2.1 TMDS
- 1x DisplayPort™ 1.4a (HBR2)
- 1x Ethernet (GbE RJ-45)
- 1x Power connector

Optional Rear Ports (configured)

DP

Monitor Cable

None

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified

Physical Locks

Kensington Security Slot™, 3 x 7 mm

Chassis Intrusion Switch

No chassis intrusion switch

MANAGEABILITY

System Management

Non-vPro®

SERVICE

Base Warranty

1-year, Onsite

Included Upgrade

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- GREENGUARD®
- RoHS compliant
- TCO Certified, generation 10
- VOC Report

SOFTWARE

Operating System

Windows® 11 Pro (on ARM), English

Bundled Software

Lenovo® AI Now

ACCESSORIES

Bundled Accessories

None

MODEL

TopSeller	: Yes	EAN / UPC / JAN: 198157501058
Announce Date:	2025-06-27	End of Support : 2031-09-25

Note:
[1] Copilot+ PCs have at least 16GB RAM, 256GB storage, and a NPU that runs 40+ TOPs to run the latest AI tools build-in latest Windows 11 to accelerate productivity and creativity.
[2] The max memory is based on the test results with current Lenovo memory offerings.
[3] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.
[4] The system dimensions may vary depending on configurations.
[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.