

ThinkCentre M70s Gen 6 12YQ001YUS



PSREF
Product Specifications
Reference

PERFORMANCE

Processor
Intel Core™ Ultra 5 235, 14C (6P + 8E) / 14T, Max Turbo up to 5.0GHz, 24MB Intel® Smart Cache

AI PC Category
AI PC^[1]

NPU
Integrated Intel® AI Boost, up to 13 TOPS

Graphics
Integrated Intel® Graphics

Chipset
Intel® Q870 Chipset

Memory
1x 32GB UDIMM DDR5-5600

Memory Slots
Four DDR5 UDIMM slots, dual-channel capable

Max Memory^[2]
Up to 128GB DDR5

Storage
512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Max Storage Support^[3]
Up to four drives, 1x 3.5" HDD + 1x 2.5" HDD + 2x M.2 SSD • 3.5" HDD up to 2TB • 2.5" HDD bay is only for customer self upgrade • M.2 SSD up to 2TB each^[4]

RAID Preset
None

Card Reader
No Card Reader

Optical
DVD±RW

Audio Chip
High Definition (HD) Audio, Realtek® ALC623-CG codec

Speakers
1Wx1

Power Supply
260W 90%

DESIGN

Keyboard
USB Traditional Keyboard, Black, English

Mouse
USB Calliope Mouse, Black

Optional Bay
2nd M.2 Bracket + 2.5" HDD Bracket

Expansion Slots
• One PCIe® 4.0 x16, low-profile, length ≤ 155mm, height ≤ 70mm
• Two PCIe® 3.0 x1, low-profile, length ≤ 155mm, height ≤ 70mm

• Three M.2 slots (one for WLAN, two for SSD)

Case Color
Black

Stand
Vertical Stand

Dust Filter
None

Pen
Pen Not Supported

Form Factor
SFF (8.2L)

Dimensions (WxDxH)^[5]
92.5 x 299.7 x 339.5 mm (3.6 x 11.8 x 13.4 inches)

Weight^[6]
5.1 kg (11.2 lbs, maximum configuration)

CONNECTIVITY

WLAN + Bluetooth^[7]
Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®^[8]

WWAN
WWAN Not Supported

Ethernet
Integrated 100/1000M

Front Ports
• 1x USB-C® (USB 5Gbps / USB 3.2 Gen 1), with 15W charging
• 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
• 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
• 1x headphone / microphone combo jack (3.5mm)

Rear Ports^[9]
• 4x USB-A (USB 5Gbps / USB 3.2 Gen 1)
• 1x HDMI® 2.1 TMDS
• 2x DisplayPort™ 1.4a (HBR3, DSC)
• 1x Ethernet (RJ-45)
• 1x line-out (3.5mm)

Optional Rear Ports (configured)
None

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Fingerprint Reader
No fingerprint reader

Physical Locks
• Kensington Security Slot™, 3 x 7 mm
• Padlock Loop

Smart Cable Clip
None

Chassis E-Lock
None

Chassis Intrusion Switch
None

MANAGEABILITY

System Management^[10]
Intel® vPro® Enterprise

SERVICE

Base Warranty
3-year, Onsite

Included Upgrade
None

CERTIFICATIONS

Green Certifications
• ErP Lot 3
• GREENGUARD®
• RoHS compliant

Mil-Spec Test
MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Solar Radiation, Contamination by Fluids, Salt Fog)

SOFTWARE

Operating System
Windows® 11 Pro, English

Bundled Software
None

ACCESSORIES

Bundled Accessories
None

MODEL

TopSeller : Yes **EAN / UPC / JAN:** 199273547784

Announce Date: 2025-11-03 **End of Support** : 2031-11-29

Note:
^[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft Copilot key or using Win + C.
• Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
• Lenovo reserves the right to change specifications without notice. To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.

- 

Advanced technical support, 24x7x365, in more than 100 markets
- 

Technical Account Managers for proactive relationship and escalation management
- 

Comprehensive hardware & OEM software support
- 

Priority on service delivery and repair parts
- 

Single point of contact for simplified end-to-end case management
- 

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

 United States of America



Lenovo Self-Charging Bluetooth Keyboard-French Canadian 058 4Y41R69498



Lenovo Wired VoIP Headset 5000 4XD1R88995

Please click [here](#) to view the full list of accessories.

Recommended Services

BEST	3Y Premier Support for AIPC upgrade from 3Y Onsite + 3Y Keep Your Drive Add On + CO2 Offset 0.5 ton (2nd Generation Carbon Offset Projects) (5WS1V00194, 5PS0D81209, 5WS1L72255)
BETTER	3Y Premier Support for AIPC upgrade from 3Y Onsite + 3Y Keep Your Drive Add On (5WS1V00194, 5PS0D81209)
GOOD	3Y Premier Support for AIPC upgrade from 3Y Onsite (5WS1V00194)



PSREF
Product Specifications
Reference