



PERFORMANCE

Processor
Intel Core™ 5 210H, 8C (4P + 4E) / 12T, P-core 2.2 / 4.8GHz, E-core 1.6 / 3.6GHz, 12MB Intel® Smart Cache

AI PC Category
Non-AI PC

NPU
None

Graphics
Integrated Intel® Graphics

Chipset
Intel® SoC Platform

Memory
1x 16GB SODIMM DDR5-5600

Memory Slots
Two DDR5 SODIMM slots, dual-channel capable

Max Memory^[1]
Up to 64GB DDR5-5600

Storage
512GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

Storage Slot
Two M.2 slots • One M.2 2242 PCIe® 4.0 x4 slot • One M.2 2280 PCIe® 4.0 x4 slot

Max Storage Support^[2]
Up to two drives, 2x M.2 SSD • M.2 2242 SSD up to 2TB • M.2 2280 SSD up to 2TB

Card Reader
SD Card Reader

Audio Chip
High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers
Stereo speakers, 2W x2, Dolby Audio™

Microphone
2x, Array

Camera
FHD 1080p + IR Hybrid with Privacy Shutter

Battery
48Wh

Power Adapter
65W USB-C® Slim (2-pin, Wall-mount)

Special Features
Modern Standby

DESIGN

Display
16'' WUXGA (1920x1200) IPS 400nits Anti-glare, 100% sRGB, 120Hz, Touch^[3]

Touchscreen
In-cell, 10-point Multi-touch

Screen-to-Body Ratio
90%

Pen
Pen Not Supported

Keyboard
Backlit, English

Touchpad
Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 75 x 120 mm (2.95 x 4.72 inches)

Dimensions (WxDxH)^[4]
356 x 253.5 x 17.5 mm (14.01 x 9.98 x 0.69 inches)

Weight^[5]
Starting at 1.7 kg (3.75 lbs)

Case Color
Arctic Grey

Case Material
Aluminium (Top), PC-ABS (Bottom)

Surface Treatment
Anodizing Sandblasting (Top), Texture (Bottom)

SOFTWARE

Operating System
Windows® 11 Pro, English (US) / English (UK)

Bundled Software
Office Trial

CONNECTIVITY

WLAN + Bluetooth
Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

WWAN
WWAN Not Supported

Ethernet
100/1000M (RJ-45)

Standard Ports
• 1x USB-A (USB 5Gbps), Always On
• 1x USB-A (USB 5Gbps)
• 1x USB-C® (USB 10Gbps), with USB PD 45-65W and DisplayPort™ 1.4
• 1x Thunderbolt™ 4, with USB PD 45-65W and DisplayPort™ 1.4
• 1x HDMI® 2.1, up to 4K/60Hz
• 1x Headphone / microphone combo jack (3.5mm)
• 1x Ethernet (RJ-45)
• 1x SD card reader

Docking
Various docking solutions supported via Thunderbolt™ or USB-C®. For more compatible docking solutions, please visit [Docking for](#)

[ThinkBook® 16 G9 IRL](#)

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0 Enabled

Physical Locks
Kensington Nano Security Slot™, 2.5 x 6 mm

Fingerprint Reader
Touch Style, Match-on-Chip, Integrated in Power Button

Other Security
• Camera privacy shutter
• IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management
Non-vPro®

SERVICE

Base Warranty
1-year, Courier or Carry-in

Included Upgrade
None

ACCESSORIES

CERTIFICATIONS

Green Certifications
• ENERGY STAR® 9.0
• EPEAT™ Gold Registered
• ErP Lot 6/26
• RoHS compliant
• TCO Certified, generation 10

Mil-Spec Test
MIL-STD-810G military test passed

Other Certifications
• Eyesafe® Certified 2.0
• TÜV Rheinland® Low Blue Light (Hardware Solution)

MODEL

TopSeller : Yes **EAN / UPC / JAN:** 199272037750
Announce Date: 2025-12-12 **End of Support** : 2032-06-07
• Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
• Lenovo reserves the right to change specifications without notice.
• California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>
To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.

- 

Advanced technical support, 24x7x365, in more than 100 markets
- 

Technical Account Managers for proactive relationship and escalation management
- 

Comprehensive hardware & OEM software support
- 

Priority on service delivery and repair parts
- 

Single point of contact for simplified end-to-end case management
- 

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Dual-Mode Wireless ANC Headset 6550 (USB-C, Teams) 4XD1S19778



Lenovo Self-Charging Bluetooth Keyboard-French Canadian 058 4Y41R69498

Please click [here](#) to view the full list of accessories.

Recommended Services

BEST	4Y Premier Support Upgrade from 1Y Courier/Carry-in (5WSOT36121)
BETTER	3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WSOT36151)
GOOD	3Y Onsite upgrade from 1Y Courier/Carry-in (5WSOA23681)



PSREF
Product Specifications
Reference