

# IMPACT 1000 Series



- ✓ On-ear Bluetooth® headset with adaptive ANC and industry-leading voice pickup
- ✓ Get your message across through adaptive microphone technology powered by EPOS AI™
- ✓ Protect your brain in noisy open office environments with hybrid adaptive ANC
- ✓ Enjoy a superior headset with super wideband and stereo sound
- ✓ Wear all day thanks to lightweight design, soft cushions, and headband padding
- ✓ Experience true convenience with a wireless charging stand and smart features

## Design

Wearing style	Headband; Stereo and mono variants
Ear coupling	On-ear
Ear pad material	Leatherette
Color	Black

## Smart features

LED features and functions	Call control on headset, 360-degree busylight, mute LED on boom arm
Boom arm features	Flexible, 270 degrees rotation for left and right wearing. Lift to mute, answer calls
Wearing detection	Accept calls, mute, pause and resume media
Charge stand	Wireless charging (variant depending)

## Connectivity

Connectivity	Bluetooth®, USB-C to USB-C cable, USB-A dongle
Bluetooth® version	5.3
Bluetooth® profiles	HSP 1.2, HFP 1.8, A2DP 1.3.2, AVRCP 1.6.2
Audio codecs supported	SBC, AAC
Operating range (Bluetooth)	Up to 30 m   98 ft
Paired devices	Up to 8 Bluetooth® devices
Simultaneous Bluetooth connections	3

## Battery

Battery type	Rechargeable lithium-pol battery
Battery capacity	580 mAh
Music time ANC off	Up to 55 hours
Music time with ANC	Up to 32 hours
Talk time*	Up to 20 hours
Corded charging	USB-C
Power via USB cable	5V max 670mA
Charging time	With cable: 1.5 hours Wireless charging: 2.5 hours
Fast charge	10 minutes gives up to 90 minutes

\*Based on industry standard test conducted in listening mode with ANC off and single connection to mobile

## Microphone

Microphone noise cancelling	Ultra noise cancelling
Environmental noise cancellation (ENC)	AI based noise reduction
Number of microphones	6
Microphones for voice pick-up	3 (ANC variants 4)
Microphone pick up pattern	Adaptive beamforming
Microphone technology	Digital MEMS
Frequency response	100 Hz - 16 KHz super wideband
Sensitivity	-17 dBFS/Pa @1kHz

<b>Speaker</b>	Acoustical principle	Dynamic closed
	Active noise cancellation (ANC)	Hybrid adaptive and manual mode in 3 levels
	Passive damping (ANC off)	-16 dB
	Bandwidth (speak mode)	100 Hz - 16 KHz Super wideband
	Bandwidth (music mode)	20 Hz - 20 KHz Music quality
	Sensitivity	111 +/- 3 dB @ 1 kHz, 1 mW
	Max sound pressure	109 dB SPL @ 1 kHz
	Total harmonic distortion	< 0,2 % @ 1 kHz
	Impedance	20 ohm
	Size	36 mm
	User hearing protection	EPOS ActiveGard®, EU Noise at Work limiter, Australia G616 Acoustic Safety
	Talk through	Yes, 3 levels
	<b>Weight</b>	Headset weight
<b>Dimensions</b>	Headset (LxWxH)	Mono: 66 x 177 x 179 mm   2.59 x 6.96 x 7.04 in Stereo: 66 x 176 x 178 mm   2.59 x 6.92 x 7.00 in
	Earcups	74 mm   2.91 in
	Length boom arm	136 mm   5.35 in
	USB cable length	120 cm   47.24 in
<b>Software &amp; Apps</b>	EPOS devices can be managed with following software solutions:	
	EPOS Connect desktop app	EPOS Connect freeware for Windows and Mac. Conduct firmware updates and configure headsets for personal audio preferences: <a href="https://eposaudio.com/software-epos-connect">eposaudio.com/software-epos-connect</a>
	EPOS Connect mobile app	Compatible with most iOS and Android systems and available in 7 languages including English, French, German, Spanish, Japanese, Korean and Simplified Chinese.
	EPOS Connect for thin clients	Conduct firmware updates, supported by DellWyse, Linux, IGEL, eLux
	EPOS Connect for web	A web-based solution to conduct firmware updates and configure headsets for personal audio preferences
	EPOS Manager	Manage, update and configure EPOS audio devices from any location. For both cloud and on-premises solutions: <a href="https://eposaudio.com/software-epos-manager">eposaudio.com/software-epos-manager</a>
<b>Extended info</b>	Warranty	2 years
	Operating temperature	-10°C - 50°C
	Storage temperature	-10°C - 60°C
	Packaging weight	408 g   14.39 oz
	Master carton weight	4880 g   172.13 oz
	Packaging dimensions (LxWxH)	203 x 203 x 57 mm   7.99 x 7.99 x 2.24 in
	Master carton dimensions (LxWxH)	432 x 313 x 257 mm   17 x 12.32 x 10.11 in
	Units per master carton:	10

## Product information

Product	Whats in the box	Certifications and compliance	EAN code	UPC code
IMPACT 1061T ANC Art. no. 1001171	Stereo headset and wireless charging stand (CH 40), sustainable carry pouch, Bluetooth® USB dongle (BTD 800a), USB-C Cable (1.2m), Safety & Compliance sheet.	Certified for Microsoft Teams	57 14708 00975 7	8 40064 40975 9
IMPACT 1061T Art. no. 1001173	Stereo headset and wireless charging stand (CH 40), sustainable carry pouch, Bluetooth® USB dongle (BTD 800a), USB-C Cable (1.2m), Safety & Compliance sheet.	Certified for Microsoft Teams	57 14708 00977 1	8 40064 40977 3
IMPACT 1061 ANC Art. no. 1001131	Stereo headset and wireless charging stand (CH 40), sustainable carry pouch, Bluetooth® USB dongle (BTD 800a), USB-C Cable (1.2m), Safety & Compliance sheet.	Certified for Zoom, Google Meet, Google Voice, Webex by Cisco, Unify, RingCentral	57 14708 00933 7	8 40064 40933 9
IMPACT 1061 Art. no. 1001135	Stereo headset and wireless charging stand (CH 40), sustainable carry pouch, Bluetooth® USB dongle (BTD 800a), USB-C Cable (1.2m), Safety & Compliance sheet.	Certified for Zoom, Google Meet, Google Voice, Webex by Cisco, Unify, RingCentral	57 14708 00937 5	8 40064 40937 7
IMPACT 1060T ANC Art. no. 1001136	Stereo headset, sustainable carry pouch, Bluetooth® USB dongle (BTD 800a), USB-C Cable (1.2m), Safety & Compliance sheet.	Certified for Microsoft Teams	57 14708 00938 2	8 40064 40938 4
IMPACT 1060T Art. no. 1001138	Stereo headset, sustainable carry pouch, Bluetooth® USB dongle (BTD 800a), USB-C Cable (1.2m), Safety & Compliance sheet.	Certified for Microsoft Teams	57 14708 00940 5	8 40064 40940 7
IMPACT 1060 ANC Art. no. 1001130	Stereo headset, sustainable carry pouch, Bluetooth® USB dongle (BTD 800a), USB-C Cable (1.2m), Safety & Compliance sheet.	Certified for Zoom, Google Meet, Google Voice, Webex by Cisco, Unify, RingCentral	57 14708 00932 0	8 40064 40932 2
IMPACT 1060 Art. no. 1001134	Stereo headset, sustainable carry pouch, Bluetooth® USB dongle (BTD 800a), USB-C Cable (1.2m), Safety & Compliance sheet.	Certified for Zoom, Google Meet, Google Voice, Webex by Cisco, Unify, RingCentral	57 14708 00936 8	8 40064 40936 0
IMPACT 1030T Art. no. 1001137	Mono headset, soft carry pouch, Bluetooth® USB dongle (BTD 800a), USB-C Cable (1.2m), Safety & Compliance sheet	Certified for Microsoft Teams	57 14708 00939 9	8 40064 40939 1
IMPACT 1030 Art. no. 1001132	Mono headset, soft carry pouch, Bluetooth® USB dongle (BTD 800a), USB-C Cable (1.2m), Safety & Compliance sheet	Certified for Zoom, Google Meet, Google Voice, Webex by Cisco, Unify, RingCentral	57 14708 00934 4	8 40064 40934 6
<b>Spare parts</b>	<b>Description</b>		<b>EAN code</b>	<b>UPC code</b>
IMPACT 800/1000 ANC ear pads Art. no. 1001289	Leatherette non-ANC ear pads - 2 pcs.		57 14708 01119 4	8 40064 41099 1
IMPACT 800/1000 ear pads Art. no. 1001290	Leatherette ANC ear pads - 2 pcs.		57 14708 01120 0	8 40064 41100 4
CH 40 Art. no. 1001139	Wireless charging stand. Dimensions: 10 x 13.5 x 23 cm   3.93 x 5.31 x 9.05 in USB-C cable 1.2 m   0.39 ft		57 14708 00941 2	8 40064 40941 4
Spare battery O6 Art. no. 1001291	Spare battery IMPACT 1000		57 14708 01121 7	8 40064 41101 1
Replacement USB-C to USB-A Adapter Art. no. 1001474	Converts USB-C cables to connect to USB-A ports		57 14708 01295 5	8 40064 41274 2
Replacement cable Art. no. 1001489	USB-C to USB-C 1.2m		57 14708 01310 5	8 40064 41289 6
Headset Pouch O1 Art. no. 1001239	Headset Pouch Grey RPET Felt Material		57 14708 01046 3	8 40064 41046 5