



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- 27-inch FHD display with IPS panel
- 99% sRGB color space coverage & 1,500:1 contrast ratio
- 100Hz refresh rate, which can be manually adjust to 48Hz
- HDMI® and VGA ports for connectivity
- Low Blue Light Hardware and Flicker Free Technology
- Ergonomic tilt stand for adjustability (-5°/+22°)
- Case color - Raven Black
- 3-year limited warranty

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON
Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK
Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that’s right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Recommended Accessories United States of America




Lenovo Ultra High Speed HDMI™ Cable 1.8m

4X91U92141



NanoSaver Cable Lock from Lenovo

4XE1L51710



Lenovo Cloth Gaming Mouse Pad M

GXH1C97873

>> [View More Accessories](#)

Recommended Services

Best

4Y Premier Support upgrade from 3Y Courier/CCI Product Exchange ThinkVision (5WS1N78824)

Better

3Y Premier Support upgrade from 3Y Courier/CCI Product Exchange ThinkVision (5WS1N78823)

PERFORMANCE

Display Size
27"

View Area
597.9x336.3 mm

Panel
In-Plane Switching

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920x1080

Pixel Pitch
0.3114x0.3114 mm

Dot / Pixel Per Inch
82 dpi

View Angle (H / V)
178° / 178°

Response Time
4ms GtG (Extreme mode) / 6ms GtG (Typical mode)

Color Support
16.7 Million

Refresh Rate
100Hz

Brightness
300 cd/m²

Contrast Ratio
1500:1

Color Gamut
99% sRGB

Screen Surface Treatment
Anti-glare

Curvature
Flat Panel

Camera
None

Microphone
None

Speakers
None

Power Consumption (Typical / Maximum)
17.3W / 19.8W

Power Adapter
Integrated

DESIGN

Stand
Tilt Stand

Case Color
Raven Black

Side Bezel Width
2.0 mm

Mounting
Supports VESA mount 100 x 100 mm

ThinkCentre M Series Support
Tiny Support

Dimensions (WxDxH)^[1]
• Unpacked with Stand | 611.9 x 210.0 x 443.5 mm (24.09 x 8.27 x 17.46 inches)
• Head Only | 611.9 x 44.4 x 366.5 mm (24.09 x 1.75 x 14.43 inches)

Packaging Dimensions (WxDxH)
690.0 x 111.0 x 525.0 mm (27.17 x 4.37 x 20.67 inches)

Weight^[2]
• Monitor With Stand | 4.1 kg (9.0 lbs)
• Monitor Head Only | 3.7 kg (8.2 lbs)

Packaging Weight
• EPS: 5.8 kg (12.8 lbs)
• Pulp: 6.4 kg (14.1 lbs)

CONNECTIVITY

Rear Ports
• 1x HDMI® 1.4, supports 1920x1080@100Hz
• 1x VGA

SERVICE

Base Warranty
3-year limited warranty

CERTIFICATIONS

Environmental Certification
ENERGY Star Certified, EPEAT™ Gold, EU Energy Efficiency Level (Level-D), RoHS, Volatile Organic Compound Certification

Ergonomic Certification
TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Flicker Free

Sync Technology
None

SOFTWARE

Operating System
Support Windows® 10, Windows® 11

ACCESSORIES

In the Box
• Monitor with stand
• 1x HDMI® 1.4 cable (1.8m)
• 1x Power cable (1.8m)
• Quick setup guide

MODEL

Region : NA
EAN / UPC / JAN: 0199271591604 / 199271591604 / None
Announce Date : 2025-07-02



Product image is a sample, it may not match the real color of this model

Note:
[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
 - California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>