

ZoomSHOT 4K with OneLINK Bridge System **SKU: 999-69350-300W**



A low-cost point-of-view camera with UHD 4K image quality.

Key Features:

- 30x powered zoom with 70.2° horizontal field of view
- Up to 2160p/30 HD image quality
- HDMI output
- Local 12V power supply for camera included or available with optional OneLINK HDMI or OneLINK Bridge Extension Systems
- RS-232 Control
- Manual Pan/Tilt with EZ Set tensioning system
- Compatible with Kensington lock

The ZoomSHOT 4K is a cost-effective, versatile, high-definition point-of-view camera well-suited for small, medium, and large rooms. It is designed to support a wide range of applications, including houses of worship, pro A/V system integration, live events, IMAG systems, UCC applications, videoconferencing, distance learning classrooms and lecture capture. The camera captures with a full HD 1/2.5" Sony Exmor 8.57 megapixel 2160p image sensor, 30x optical zoom, and 70.2° horizontal field of view. It also features a manual pan/tilt, an EZ Set tensioning system, and a presenter-friendly IR remote control. The ZoomSHOT 4K OneLINK Bridge System is easy to install and use, and it offers a variety of outputs including simultaneous HDMI, SDI and USB 3.0 outputs. The OneLINK Bridge System also includes audio inputs and echo cancelled outputs usable for in-room conferencing systems.

The ZoomSHOT 4K is a reliable and affordable solution for your video capture needs. Record a lecture, conduct a video conference, or capture live events with outstanding performance and quality. Versatile features, outputs, and ease of use, make this system an excellent choice. Can also be used as a stand alone camera with no extenstion system if desired.

This Package Includes:

- ZoomSHOT 4K camera (black or white)
- Thin Profile Wall Mount (black or white) with mounting hardware
- Vaddio IR Shot Commander remote with 2x AAA batteries
- OneLINK HDBT EZIM (easy interface module)
- Cables to connect ZoomSHOT 4K to EZIM
- OneLINK Bridge HDBT extension
- 48V power supply for OneLINK Bridge with AC cord set(s)

Total Pixels: 2.14 Megapixel

Specifications

Dimensions & Measurements	Depth	Camera: 5.8 in (14.73 cm) QUSB: 6 in (15.24 cm)
	Height	Camera: 7 in (17.78 cm) QUSB: 1.72 in (4.37 cm)
	Max Distance Support	150 ft (45.7 m)
	Operating Temperature	32° to 104°F (0° to 40°C)
	Product Weight	Camera: 3.5 lbs (1.59 kg) QUSB: 1.4 lbs (0.64 kg)
	Shipping Weight	1 lbs (0.5 kg)
	Width	Camera: 5.5 in (14 cm) QUSB: 8.38 in (21.27 cm)
Characteristics & Features	3rd Party Control	RS232
	Camera Type	Fixed

Color	White
Compatible With	Vaddio
Control Method	• IR Remote • RS232
Estimated Room Size	• Large Room • Medium Room
Field of View	70.2 Degrees Wide End
Field of View Wide	70.2
Focus System	• Auto • Manual
Gain	• Auto • Manual
Image Sensor Type	1/2.8 Exmor CMOS
Input Ports	EZ Power Video
Invertible	Yes
Manufacturer	Vaddio
Max Resolution	2160p 30
Minimum Illumination	0.3 Lux
OneLINK Compatibility	No
Output Ports	• HDMI 1.4b • RS-232 • USB 3.0
Pan and Tilt Range	• Tilt 30 degrees to negative 30 degrees • Unlimited Pan
Pan and Tilt Speed	Manual
Pixels	2.14 Megapixel
Power Cord	US Cord

Power Supply	• 208A • 24VDC
Power Type	EZ Power
Preset Positions	16
PTZ Motors	No Motors Manual
Quick-Connect Compatibility	QUSB
Signal Type	• HD YPbPr • HDMI • RS 232 • USB 2.0
Solution Type	Camera with Extension
TAA Compliant	Yes
Tri-Sync Motion	No
UPC	840077509132
White Balance	• Auto • Manual
Zoom	30x

Certifications & Warranties

Certifications	• CE • FCC • TAA
Warranty	3 years

Source: https://www.legrandav.com/products/cameras/4k_fixed_camera/zoomshot-4k-onelink-system/999-69350-300w