



# HP Poly Mission 615 Monaural USB Wired Headset (C01C3AA)



## Overview

### Comfort meets performance

Built for long days and countless calls, the HP Poly Mission 615 headset blends exceptional comfort with high-quality audio and easy USB connectivity — helping teams stay focused, productive, and connected all day.

### Custom fit for long days

Designed for all day comfort – the adjustable padded headband pad and plush memory foam earcups provide a personalized fit that supports focus and reduces fatigue — even through all-day meetings.

### Simple, reliable connections

Plug in and get to work. With USB Type-C® and USB Type-A compatibility, intuitive inline controls, and easy device management via HP Poly Studio App, setup is effortless and reliable for every user, every time.

### Always clear, always professional

When your workday gets loud, HP Poly Mission 615 headset helps your voice shine through. Noise-canceling mics and AI noise reduction[1] keep conversations professional and distraction free, so your calls are clear and focused.

### Built for a better tomorrow

This headset is thoughtfully designed containing at least 25% post-consumer recycled plastics[2] and shipped in paper-based packaging[3].

## Features

### AI noise reduction[1]

AI noise reduction[1] detects and filters ambient sounds so only your voice comes through. Meetings stay quiet and focused without manual muting.

### SoundGuard Digital[5]

SoundGuard Digital[5] technology controls sudden audio spikes and continuous noise to keep levels safe and comfortable throughout the day without distorting speech quality.

### Super wideband audio

Super wideband audio captures a broader frequency range to reproduce voice detail and tone more naturally. Conversations sound closer to in-person speech for clearer calls.

### 32 mm speaker driver

Large 32 mm driver delivers richer audio and sharper clarity, making voices easier to recognize and reducing listening fatigue during long sessions.

### Rotatable microphone boom

A 285-degree rotating microphone lets users wear the boom on either side for comfort and control. Quick upward movement automatically mutes the mic for seamless silence when needed.

### On-ear busy light indicator

360-degree visible busy light, on earcup illuminates red during calls to let others know you are engaged. A simple visual cue helps reduce interruptions and maintains focus in shared workspaces.

---

*[1] On-device AI reduces typical background noises, allowing the user to be heard clearly improving the overall user experience.*

*[2] Post-consumer recycled plastic is expressed as a percentage of the total weight of plastic.*

*[3] HP paper-based packaging is reported by suppliers as recycled or certified, with a minimum of 97% by volume verified by HP. Packaging includes box and inserts.*

## Specifications

<b>Audio Features</b>	Microsoft Teams Open Office certified; AI enhanced transmit noise reduction; Super wideband audio
<b>Product Dimensions (metric)</b>	150 x 180 x 40 mm
<b>Product Dimensions (imperial)</b>	5.9 x 7 x 1.6 in
<b>Weight (metric)</b>	117.5 g
<b>Weight (imperial)</b>	0.26 lb
<b>Package Dimensions (metric)</b>	210 x 185 x 55 mm
<b>Package Weight (metric)</b>	289 g
<b>Sustainable Impact Specifications</b>	Paper-based packaging; At least 25% post-consumer recycled plastic
<b>UPC Number</b>	(ABB) 199642899278; (AC3) 199251820830; (B13) 199251820847
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>What Is In The Box</b>	Headset; USB Type-C® to USB Type-A adapter; Carrying case; Quick start guide; Warranty card; Product notice

## Additional specifications

<b>Acoustic Protection Technology</b>	SoundGuard Digital <sup>[4]</sup>
<b>Boom Mic Length (imperial)</b>	0.43 ft
<b>Boom Mic Length (metric)</b>	130 mm
<b>Boom Mic Rotation</b>	285°
<b>Button User Controls</b>	Mute/unmute; Volume +/-; Microsoft Teams; Call answer/ignore/end
<b>Cable Length (imperial)</b>	6.5 ft
<b>Cable Length (metric)</b>	2 m
<b>Cartons Per Layer</b>	10
<b>Cartons Per Pallet</b>	60 (air); 80 (ocean)
<b>Certified Collaboration Software</b>	Microsoft Teams certified; Google Meet certified; Works With Chromebook certified; Zoom Workplace Headset certified; Zoom Workplace Contact Center certified
<b>Charging</b>	Cable
<b>Color</b>	Black
<b>Compatible Operating Systems</b>	Windows 11; macOS; Chrome OS™; Android™; iOS
<b>Connection Type</b>	USB Type-C®
<b>Connection Type</b>	Wired: USB Type-C®, USB Type-C®/A adapter
<b>Datasheet Photo 01</b>	<a href="https://prism-pui-int.inc.hp.com/pro/crystal/1/DAMHandler/Accessories/HP%20Mission%20615%20USB%20Headset_Monaural_Catalog_TransparentBG_Spill_OFF_FrontRight_1.png">https://prism-pui-int.inc.hp.com/pro/crystal/1/DAMHandler/Accessories/HP Poly Mission 615 USB Headset_Monaural_Catalog_TransparentBG_Spill_OFF_FrontRight_1.png</a>
<b>Datasheet Photo 02</b>	<a href="https://prism-pui-int.inc.hp.com/pro/crystal/1/DAMHandler/Accessories/HP%20Mission%20615%20USB%20Headset_Monaural_Catalog_TransparentBG_Front_2.png">https://prism-pui-int.inc.hp.com/pro/crystal/1/DAMHandler/Accessories/HP Poly Mission 615 USB Headset_Monaural_Catalog_TransparentBG_Front_2.png</a>
<b>Datasheet Photo 03</b>	<a href="https://prism-pui-int.inc.hp.com/pro/crystal/1/DAMHandler/Accessories/HP%20Mission%20615%20USB%20Headset_Monaural_Catalog_TransparentBG_FrontRight_3.png">https://prism-pui-int.inc.hp.com/pro/crystal/1/DAMHandler/Accessories/HP Poly Mission 615 USB Headset_Monaural_Catalog_TransparentBG_FrontRight_3.png</a>
<b>Datasheet Photo 04</b>	<a href="https://prism-pui-int.inc.hp.com/pro/crystal/1/DAMHandler/Accessories/HP%20Mission%20615%20USB%20Headset_Monaural_Catalog_TransparentBG_FrontLeft_5.png">https://prism-pui-int.inc.hp.com/pro/crystal/1/DAMHandler/Accessories/HP Poly Mission 615 USB Headset_Monaural_Catalog_TransparentBG_FrontLeft_5.png</a>
<b>Datasheet Photo 05</b>	<a href="https://prism-pui-int.inc.hp.com/pro/crystal/1/DAMHandler/Accessories/HP%20Mission%20615%20USB%20Headset_Monaural_Catalog_TransparentBG_BoomUp_RightProfile_4.png">https://prism-pui-int.inc.hp.com/pro/crystal/1/DAMHandler/Accessories/HP Poly Mission 615 USB Headset_Monaural_Catalog_TransparentBG_BoomUp_RightProfile_4.png</a>
<b>Ear Cushion Material</b>	Leatherette
<b>Ear Cushions</b>	PU leather (surface material); Memory foam (padding material)
<b>Headphone Type</b>	On-ear (monaural)

<b>Indicator Light</b>	On call; On muted call; Incoming call; On hold call
<b>Layers Per Pallet</b>	6 (air); 8 (ocean)
<b>Management Software</b>	HP Poly Studio App
<b>Master Carton Dimension (imperial)</b>	22.63 x 7.87 x 9.05 in
<b>Master Carton Dimension (metric)</b>	57.5 x 20 x 23 cm
<b>Master Carton Weight (imperial)</b>	7.85 lb
<b>Master Carton Weight (metric)</b>	3.56 kg
<b>Microphone Bandwidth</b>	50 Hz to 16 kHz
<b>Microphone Type</b>	Two-microphone AI noise reduction
<b>Multiple Order Quantity</b>	10
<b>Number of Microphones</b>	2
<b>Package Dimensions (imperial)</b>	8.26 x 7.28 x 2.16 in
<b>Package Weight (imperial)</b>	0.63 lb
<b>Pallet Dimensions (imperial)</b>	48 x 40 x 59.5 in (air); 48 x 40 x 77.8 in (ocean)
<b>Pallet Dimensions (metric)</b>	121.9 x 101.6 x 151.2 cm (air); 121.9 x 101.6 x 197.6 cm (ocean)
<b>Pallet Weight (imperial)</b>	650 lb
<b>Pallet Weight (metric)</b>	295 kg
<b>Products Per Pallet</b>	600 (air); 800 (ocean)
<b>Products per Pallet Layer</b>	100 (air); 100 (ocean)
<b>Rotate Mic Boom to Mute</b>	Yes
<b>Sensitivity (Microphone)</b>	-35 ±3 (boom mic); -38±1 (capsule mic)
<b>Sensitivity (Speaker)</b>	84 dB SPL (1 mW/1 cm) +/- 3 dB
<b>Signal-To-Noise Ratio</b>	>58 dB for Boom mic; >65 dB for capsule mic
<b>Speaker Bandwidth</b>	20 Hz to 20 kHz (multimedia mode)
<b>Speaker Size</b>	32 mm
<b>TCO Certified</b>	TCO Certified, generation 10
<b>UC Compatibility</b>	Universal
<b>UNSPSC Code</b>	43191638
<b>Voice Alerts</b>	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Incoming call; Call answer/ignore
<b>Wearing Style</b>	Mono

[4] HP Poly SoundGuard Digital includes G616 anti-startle protection which limits the noise level to below 102 dB SPL and is compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; HP Poly owned proprietary Advanced Audio Limiter, compliant to ACIF G616; and Average Daily Noise Exposure that measures and controls sound to prevent the Average Daily Noise Exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA). HP Poly Studio

*App is required to enable SoundGuard Digital features. HP Poly SoundGuard protects against Acoustic Shock by limiting sounds to below 118 dBA. This feature is enabled by default and is not a user configurable feature.*

---

## Disclaimer — Copyright

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Apr 08, 2026 12:56 PM UTC+0000