



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- 27-inch FHD display with IPS panel
- 99% sRGB color space coverage & 1,500:1 contrast ratio
- 100Hz refresh rate, which can be manually adjust to 48Hz
- HDMI® and VGA ports for connectivity
- Low Blue Light Hardware and Flicker Free Technology
- Ergonomic tilt stand for adjustability (-5°/+22°)
- Case color - Raven Black
- 3-year limited warranty

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories Bolivia




Lenovo Ultra High Speed HDMI™ Cable 1.8m

4X91U92141



NanoSaver Cable Lock from Lenovo

4XE1L51710



Lenovo Cloth Gaming Mouse Pad M

GXH1C97873

>> [View More Accessories](#)

Recommended Services

Best

3Y Premier Support upgrade from 3Y Courier/CCI Product Exchange ThinkVision (5WS1N78823)

Better

4Y Premier Support upgrade from 3Y Courier/CCI Product Exchange ThinkVision (5WS1N78824)

ThinkVision S27-4e Monitor 64BEKAT1UZ



PERFORMANCE

- Display Size
27"
- View Area
597.9x336.3 mm
- Panel
In-Plane Switching
- Backlight
WLED
- Aspect Ratio
16:9
- Resolution
1920x1080
- Pixel Pitch
0.3114x0.3114 mm
- Dot / Pixel Per Inch
82 dpi
- View Angle (H / V)
178° / 178°
- Response Time
4ms GtG (Extreme mode) / 6ms GtG (Typical mode)
- Color Support
16.7 Million
- Refresh Rate
100Hz
- Brightness
300 cd/m²
- Contrast Ratio
1500:1
- Color Gamut
99% sRGB
- Screen Surface Treatment
Anti-glare
- Curvature
Flat Panel
- Camera
None
- Microphone
None
- Speakers
None
- Power Consumption (Typical / Maximum)
17.3W / 19.8W
- Power Adapter
Integrated

DESIGN

- Stand
Tilt Stand

- Case Color
Raven Black
- Side Bezel Width
2.0 mm
- Mounting
Supports VESA mount 100 x 100 mm
- ThinkCentre M Series Support
Tiny Support
- Dimensions (WxDxH)^[1]
 - Unpacked with Stand | 611.9 x 210.0 x 443.5 mm (24.09 x 8.27 x 17.46 inches)
 - Head Only | 611.9 x 44.4 x 366.5 mm (24.09 x 1.75 x 14.43 inches)
- Packaging Dimensions (WxDxH)
690.0 x 111.0 x 525.0 mm (27.17 x 4.37 x 20.67 inches)
- Weight^[2]
 - Monitor With Stand | 4.1 kg (9.0 lbs)
 - Monitor Head Only | 3.7 kg (8.2 lbs)

- Packaging Weight
 - EPS: 5.8 kg (12.8 lbs)
 - Pulp: 6.4 kg (14.1 lbs)

CONNECTIVITY

- Rear Ports
 - 1x HDMI® 1.4, supports 1920x1080@100Hz
 - 1x VGA

SERVICE

- Base Warranty
3-year limited warranty

CERTIFICATIONS

- Environmental Certification
ENERGY Star Certified, EPEAT™ Gold, EU Energy Efficiency Level (Level-D), RoHS, Volatile Organic Compound Certification
- Ergonomic Certification
TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Flicker Free

- Sync Technology
None

SOFTWARE

- Operating System
Support Windows® 10, Windows® 11

ACCESSORIES

- In the Box
 - Monitor with stand
 - 1x HDMI® 1.4 cable (1.8m)
 - 1x Power cable (1.8m)
 - Quick setup guide

MODEL

- Region : NA
- EAN / UPC / JAN: 0199271758601 / 199271758601 / None
- Announce Date : 2025-07-02



Product image is a sample, it may not match the real color of this model

Note:
[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
 - California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>