




The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- 14" 2.2k (2240x1400) IPS display, Anti-glare 16:10
- Extreme mode 6 ms response time
- 1500:1, 100% sRGB, 8-bit
- -5° to +95° tilt, up to 11mm lift
- Eyesafe® Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Low Blue Light, TÜV Rheinland® Flicker Free
- Case color - Raven Black
- 3-year limited warranty

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.


- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories Bolivia



NanoSaver Cable Lock from
Lenovo

4XE1L51710



Lenovo Cloth Gaming Mouse
Pad M

GXH1C97873



ThinkCentre Tiny Sandwich
Kit II

4XH0N04098

>> [View More Accessories](#)

Recommended Services

Best

3Y Premier Support
upgrade from 3Y
Courier/CCI Product
Exchange ThinkVision
(5WS1N78820)

Better

4Y Premier Support
upgrade from 3Y
Courier/CCI Product
Exchange ThinkVision
(5WS1N78821)

PERFORMANCE

Display Size
14”

View Area
301.5x188.5 mm

Panel
In-Plane Switching

Backlight
WLED

Aspect Ratio
16:10

Resolution
2240x1400

Pixel Pitch
0.135x0.135 mm

Dot / Pixel Per Inch
189 dpi

View Angle (H / V)
178° / 178°

Response Time
6ms (Extreme mode) / 8ms (Normal mode)

Color Support
16.7 Million

Refresh Rate
60Hz

Brightness
300 cd/m²

Contrast Ratio
1500:1

Color Gamut
100% sRGB

Screen Surface Treatment
Anti-glare

Curvature
None

Camera
None

Microphone
None

Speakers
None

Power Consumption (Typical / Maximum)
6W / 7.5W

DESIGN

Stand
Tilt, Height Adjust Stand

Case Color
Raven Black

Side Bezel Width
4.9 mm

Mounting
Supports VESA mount 100mm

ThinkCentre M Series Support
None

Dimensions (WxDxH)^[1]
• Lowest Position | 314.4 x 106.4 x 216.5mm (12.38 x 4.19 x 8.52 inches)
• Highest Position | 314.4 x 106.4 x 227.5 mm (12.38 x 4.19 x 8.96 inches)

Packaging Dimensions (WxDxH)
384 x 277 x 76 mm (15.12 x 10.91 x 2.99 inches)

Weight^[2]
0.6 kg (1.3 lbs)

Packaging Weight
1.8 kg (4.0 lbs)

CONNECTIVITY

Rear Ports
2x USB-C® 3.1 Gen 1 (DP 1.2 Alt Mode, USB 2.0 data transfer)

SERVICE

Base Warranty
3-year limited warranty

CERTIFICATIONS

Environmental Certification
ENERGY STAR® Certified, EPEAT™ Silver, RoHS

Ergonomic Certification
Eyesafe® Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Low Blue Light, TÜV Rheinland® Flicker Free

Sync Technology
None

Special Features
• Lenovo® ThinkColour (Lenovo® Accessories and Display Manager) Support Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems) Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center
• Natural Low Blue Light

SOFTWARE


Operating System
Support Windows® 10, Windows® 11

ACCESSORIES

In the Box
• Monitor with stand
• 1x USB-C® to USB-C® cable (1m)
• Quick setup guide

MODEL

Region : NA
EAN / UPC / JAN: 0199271591581 / 199271591581 / None
Announce Date : 2026-06-06



Product image is a sample, it may not match the real color of this model

Note:
[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

• Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.

• Lenovo reserves the right to change specifications without notice.
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>