

MFC-J6975DW

Business Color Inkjet All-in-One Printer with 11" x 17" Print, Copy, Scan, Fax, Low-Cost Printing, and Advanced Security Features

brother
at your side

Specifications:

Print	
Print Technology	Color Inkjet
Print Speeds (max.) ¹	Up to 31ppm black / 30ppm color
Time to First Page ²	Approx. 4.4 seconds black / 4.6 seconds color
Print Resolution (max.) ³	Up to 4800 x 1200 dpi
Print Emulations	PCL6, BR-Script3 ⁴ , PDF Version 2.0
Borderless Printing ⁵	Up to 11" x 17" (Ledger)
Copy	
Copy Speeds (max.) ⁶	Up to 25ipm black / 16ipm color
Copy Resolution (max.) ³	Up to 4800 x 1200 dpi
Copy Reduction / Enlargement	25% - 400% in 1% increments
Copy Options	Stack, Sort, Fit to Page, Auto Deskew, Copy Preview, N-in-1, ID Copy, Watermark Copy, Thin Paper Copy, Base Color Removal
Scan	
Scan / Copy Size (max.)	11" x 17" (Ledger)
Scan Resolution (max.) ³	ADF (optical): Up to 600 x 600 dpi Glass (optical): Up to 2400 x 1200 dpi Interpolated: Up to 19200 x 19200 dpi ⁷
Scan Speeds (max.) ⁸	Simplex: Up to 24ipm color / black; Duplex: Up to 29ipm color / black
Scan To Capability	PC (Image, E-mail, OCR, File), E-mail Server ⁹ , SharePoint, FTP, SSH Server (SFTP), USB Memory Stick ¹⁰ , Cloud Services (Web Connect) ¹¹ , SharePoint ¹¹ , Network Folder ¹¹ , Easy Scan to E-mail ¹² , Mobile Devices ¹³
Advanced Scanning Features	Auto Deskew, Blank Page Skip, Scan Preview, Multi-page to Single-page, Background Color Removal
Fax	
Fax Features	33.6K bps modem speed; Fax page memory: up to 150 pages ¹⁴ Fax forward to: Network Folder ⁷ and E-mail, Internet Fax ¹² , PC Fax ¹⁵
Connectivity & Compatibility	
Standard Interfaces	Wireless 802.11b/g/n (2.4GHz) / 802.11a/n (5GHz), Gigabit Ethernet, Hi-Speed USB 2.0
USB Host ¹⁰	Front: Print from and scan to USB memory stick; external card reader
Operating Systems Compatibility ¹⁶	For the latest OS compatibility and to download drivers, visit support.brother.com .
Mobile Device Compatibility ¹³	AirPrint [®] , Mopria [®] , Brother Mobile Connect, Wi-Fi Direct [®]
Cloud Services (Web Connect) ¹¹	Google Drive [™] , Evernote [®] , OneDrive, OneNote, Dropbox, Box, SharePoint Online
Brother Cloud Apps ¹²	Easy Scan to E-mail, Scan to Mobile, Cloud Secure Print, Fax Forward to Cloud or E-mail, Scan to Searchable PDF, Scan to Word, Scan to Excel, Scan to PowerPoint, E-mail Print
Security	
Security Features	Integrated NFC Card Reader, External Card Reader Compatibility, Secure Function Lock, Enterprise Security (802.1x), Active Directory, Syslog Reporting, SNMP v3, SSL/TLS, IPsec, LDAP Authentication, OAuth 2.0 (SMTP, POP3, IMAP4), IP Filter
Paper Handling	
Paper Input Capacity (max.) ¹⁷	Dual 250-sheet capacity paper trays; 100-sheet multipurpose tray
Output Capacity (max.) ¹⁸	100 sheets (up to 8.5" x 11") / 50 sheets (larger than 8.5" x 11", up to 11" x 17")
Document Glass Size	Up to 11" x 17" (Ledger)
Auto Document Feeder Capacity ¹⁷	50 pages
Paper Sizes (max.)	Upper Tray / Lower Tray / Multipurpose Tray: Up to 11" x 17" (Ledger) Duplex: Up to 11" x 17" (Ledger); ADF: Up to 11" x 17" (Ledger)
Media Types	Upper Tray / Multipurpose Tray: Plain Paper, Inkjet Paper, Glossy Paper, Recycled Paper, Envelopes, Index Cards Lower Tray: Plain Paper, Recycled Paper
Media Weights	Upper Tray: 17 to 58 lbs.; Lower Tray: 17 to 32 lbs. Multipurpose Tray: 17 to 58 lbs. ADF: 17 to 32 lbs. Auto Duplex: 17 to 32 lbs. for up to 8.5" x 11"; 17 to 24 lbs. for larger than 8.5" x 11", up to 11" x 17" (Ledger)
General	
Automatic Duplex	Print, plus single-pass copy, scan, fax up to 11" x 17" (Ledger)
Display / Customizable Shortcuts	3.5" Color Touchscreen / 18
Processor	960 MHz
Memory (std. / max.)	1GB / 1GB
Included Software ¹³	Brother Mobile Connect for iOS and Android [™] , Brother iPrint&Scan (desktop) for Windows and Mac [®] , BRAdmin Pro 4 ¹ , Tungsten PaperPort [™] 14SE ⁷
Optional Brother Value Added Services	Secure Print+, Secure Print Advanced, Remote Panel, Barcode Print+, ThinPrint Client, Barcode Utility, Request Help, Order Supplies
Optional Solutions	3manager, PaperCut, nndPrint, uniFLOW, Tungsten ControlSuite
Sustainability Features	EPEAT [®] Silver rated, Energy Star [®] certified, EPS-free packaging, 11% Post Consumer Recycled (PCR) material
Maximum Monthly Duty Cycle ¹⁹	Up to 50,000 pages
Recommended Monthly Volume ²⁰	Up to 250 to 4,000 pages
Warranty	1-year limited warranty

Replacement Supplies:



LC506BKS	Standard Yield Black Ink Cartridge (1,000 pages) ²¹
LC506CS/MS/YS	Standard Yield Ink Cartridge (900 pages) ²¹
LC506XLBKS	High Yield Black Ink Cartridge (2,500 pages) ²¹
LC506XLCS/MS/YS	High Yield Ink Cartridge (1,500 pages) ²¹
LC506XL 3PKS	3 Pack of High Yield Cyan, Magenta, and Yellow Ink Cartridges (1,500 pages) ²¹
LC506XXLBKS	Super High Yield Black Ink Cartridge (5,000 pages) ²¹
LC506XXLCS/MS/YS	Super High Yield Ink Cartridge (2,500 pages) ²¹
LC506XXL 2PKS	Twin Pack of Super High Yield Black Ink Cartridges (5,000 pages per cartridge) ²¹
LC507BK	Ultra High Yield Black Ink Cartridge (12,000 pages) ²¹
LC507C/M/Y	Ultra High Yield Ink Cartridges (10,000 pages) ²¹

Setup Information:

UPC Code	012502681984
Unit Dimensions / Weight	22.7" (W) x 20.1" (D) x 14.8" (H) / 52 lbs.
Carton Dimensions / Weight	26.8" (W) x 24.3" (D) x 19.8" (H) / 63.7 lbs.
Pallet Quantity / Tiers	4 / 2
Country of Origin	Philippines
Tariff / Harmonized Code	8443.31.0000

Carton Contents:

Brother MFC-J6975dw, Black Ink Cartridge (5,400 pages)²¹, Cyan, Magenta, Yellow Ink Cartridges (3,900 pages)²¹, AC Power Cord, Dust Cover, Product Safety Guide, Reference Guide, Warranty Card, Quick Setup Guide



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.

COMPATIBLE WITH
WINDOWS



- Print speed based on ISO/IEC 24734 (after first set of ISO test pages). For more details, please visit www.brother-usa.com/printspeed.
- Based on ISO/IEC 17629 and standard tray.
- Resolution listed vertical by horizontal dpi.
- PostScript[®] 3 compatible.
- Borderless printing is available for Letter, Ledger, 3.5"x5", 4"x6", 5"x8", 5"x7", A3, A4, and A6, paper sizes. Borderless not available with duplex printing. Minimum default margins when not printing borderless is 0.12 inches.
- ISO copy speed is based on ISO/IEC 24735. For more details, visit www.brother-usa.com/printspeed.
- Windows only.
- Color and monochrome scan speeds in accordance with ISO/IEC 17991 with all advanced features turned off, using letter-sized paper at 200/300dpi.
- Requires mail server support.
- Requires an Internet connection and an account with desired service.
- Requires an Internet connection.
- May require free download. Compatibility may vary by device and operating system. May require connection to a wireless network.
- Black and white only. Based on ITU-T Test Chart #1 at standard resolution with MMR compression.
- B&W only. PC Fax Receive not available for Mac users.

- For the latest OS compatibility and to download drivers, visit support.brother.com. Printing or scanning via macOS requires the use of AirPrint. Mac drivers are not provided. For Windows Server: USB connection supports printing and scanning; network connections support printing only.
- Maximum capacity based on using 20 lb. paper.
- Maximum capacity based on using 20 lb. paper. Output capacity is 100 sheets for up to Letter-size media and 50 sheets for media larger than Letter.
- Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.
- The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.
- Approximate page yields in accordance with ISO/IEC 24711 (Letter/A4). For more page yield information, see www.brother.com/pageyield.

©2026 BROTHER INTERNATIONAL CORPORATION • All trademarks and registered trademarks referenced herein are the property of their respective companies. macOS, AirPrint, and the AirPrint logo are registered trademarks of Apple Inc., registered in the U.S. and other countries. IOS is a trademark or registered trademark of Cisco in the U.S. and other countries and is used under license. This product works with devices capable of running the latest version of ChromeOS and has been certified to meet Google's compatibility standards. Google is not responsible for the operation of this product or its compliance with safety requirements. Android, Google Drive, Chromebook, and the Works With Chromebook badge are trademarks of Google LLC. Mopria[®] and the Mopria[®] Logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. Wi-Fi Direct[®], the Wi-Fi CERTIFIED[™] logo and the Wi-Fi Protected Setup[™] Identifier Mark are trademarks of Wi-Fi Alliance[®]. ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. EPEAT is a registered trademark of the Green Electronics Council in the United States and other countries. Evernote is a trademark of Evernote Corporation and used under a license. All specifications subject to change without notice.