

**PERFORMANCE****Processor**

Intel® Core 7 240H, 10C (6P + 4E) / 16T, P-core 2.5 / 5.2GHz, E-core 1.8 / 4.0GHz, 24MB Intel Smart Cache

**AI PC Category**

Non-AI PC

**NPU**

None

**Graphics**

Integrated Intel® Graphics

**Chipset**

Intel® SoC Platform

**Memory**

2x 16GB SODIMM DDR5-5600

**Memory Slots**

Two DDR5 SODIMM slots, dual-channel capable

**Max Memory<sup>[1]</sup>**

Up to 64GB DDR5-5600

**Storage**

512GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

**Storage Slot**

Two M.2 slots • One M.2 2242 PCIe® 4.0 x4 slot • One M.2 2280 PCIe 4.0 x4 slot

**Max Storage Support<sup>[2]</sup>**

Up to two drives, 2x M.2 SSD • M.2 2242 SSD up to 2TB • M.2 2280 SSD up to 2TB

**Card Reader**

SD Card Reader

**Audio Chip**

High Definition (HD) Audio, Realtek® ALC3287 codec

**Speakers**

Stereo speakers, 2W x2, Dolby Audio™

**Microphone**

2x, Array

**Camera**

FHD 1080p + IR Hybrid with Privacy Shutter

**Battery**

48Wh

**Power Adapter**

65W USB-C® (3-pin)

**Special Features**

Modern Standby

**DESIGN****Display**

16" WUXGA (1920x1200) IPS 400nits Anti-glare, 45% NTSC, 60Hz<sup>[3]</sup>

**Touchscreen**

None

**Screen-to-Body Ratio**

90%

**Pen**

Pen Not Supported

**Keyboard**

Backlit, English

**Touchpad**

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 75 x 120 mm (2.95 x 4.72 inches)

**Dimensions (WxDxH)<sup>[4]</sup>**

356 x 253.5 x 17.5 mm (14.01 x 9.98 x 0.69 inches)

**Weight<sup>[5]</sup>**

Starting at 1.7 kg (3.75 lbs)

**Case Color**

Arctic Grey

**Case Material**

Aluminium (Top), PC-ABS (Bottom)

**Surface Treatment**

Anodizing Sandblasting (Top), Texture (Bottom)

**SOFTWARE****Operating System**

Windows® 11 Pro, English (US) / English (UK)

**Bundled Software**

Office Trial

**CONNECTIVITY****WLAN + Bluetooth**

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

**WWAN**

WWAN Not Supported

**Ethernet**

100/1000M (RJ-45)

**Standard Ports**

- 1x USB-A (USB 5Gbps), Always On
- 1x USB-A (USB 5Gbps)
- 1x USB-C® (USB 10Gbps), with USB PD 45-65W and DisplayPort™ 1.4
- 1x Thunderbolt™ 4, with USB PD 45-65W and DisplayPort™ 1.4
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x SD card reader

**Docking**

Various docking solutions supported via Thunderbolt™ or USB-C®. For more compatible docking solutions, please visit [Docking for ThinkBook 16 G9 IRL](#)

**SECURITY & PRIVACY****Security Chip**

Discrete TPM 2.0 Enabled

**Physical Locks**

Kensington® Nano Security Slot, 2.5 x 6 mm

**Fingerprint Reader**

Touch Style, Match-on-Chip, Integrated in Power Button

**Other Security**

- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)

**MANAGEABILITY****System Management**

Non-vPro®

**SERVICE****Base Warranty**

1-year, Courier or Carry-in

**Included Upgrade**

1Y Onsite upgrade from 1Y Courier/Carry-in

**ACCESSORIES****Bundled Accessories**

None

**CERTIFICATIONS****Green Certifications**

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified, generation 10

**Mil-Spec Test**

MIL-STD-810G military test passed

**Other Certifications**

TÜV Rheinland® Low Blue Light (Software Solution)

**MODEL**

**TopSeller** : Yes **EAN / UPC / JAN:** 199272962960

**Announce Date:** 2025-12-08 **End of Support** : 2032-06-07

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice. To see more note information, please access the [web page](#).

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories

 United States of America



Lenovo Dual-Mode Wireless ANC Headset 6550 (USB-C, Teams) 4XD1S19778



Lenovo Self-Charging Bluetooth Keyboard-French Canadian 058 4Y41R69498

Please click [here](#) to view the full list of accessories.

## Recommended Services

BEST	4Y Premier Support Upgrade from 1Y Onsite (5WS0T36131)
BETTER	3Y Premier Support Upgrade from 1Y Onsite (5WS0T36120)
GOOD	3Y Onsite upgrade from 1Y Onsite (5WS0K27114)

**Lenovo**

PSREF  
Product Specifications  
Reference