



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- 27" FHD, 144Hz refresh rate, 99% sRGB, 1,500:1 contrast ratio
- 4ms GTG and 1ms MPRT response time, AMD FreeSync™ support
- HDMI®, VGA and Audio out ports, Built-in 2 x 3W audio speakers
- Hardware low blue light and TÜV-certified flicker-free screen technology
- Tilt stand with phone holder, built-in cable management design and VESA mount 100 x 100
- Lenovo® Artery (Lenovo® Accessories and Display Manager)software
- Case color - Cloud Grey
- 1-year

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade


Recommended Accessories United States of America



Humanscale Arm for dual monitor configuration, polished aluminum with whit...
4ZE1U10767



NanoSaver Cable Lock from Lenovo
4XE1L51710



Lenovo Cloth Gaming Mouse Pad M
GXH1C97873

>> [View More Accessories](#)

Product Illustration



PERFORMANCE

Display Size	27"
View Area	597.9x336.3 mm
Panel	In-Plane Switching
Backlight	WLED
Aspect Ratio	16:9
Resolution	1920x1080
Pixel Pitch	0.1038x0.3114 mm
Dot / Pixel Per Inch	82 dpi
View Angle (H / V)	178° / 178°
Response Time	1ms (MPRT) / 4ms (Extreme Mode) (G to G) / 6ms (Normal Mode) (G to G)
Color Support	16.7 Million
Refresh Rate	144Hz
Brightness	300 cd/m²
Contrast Ratio	1500:1
Color Gamut	99% sRGB (CIE 1931)
Screen Surface Treatment	Anti-glare
Curvature	None
Camera	None
Microphone	None
Speakers	3Wx2
Power Consumption (Typical / Maximum)	18.5W / 31.5W
Power Adapter	Integrated
Touchscreen	None

Smart System	None
DESIGN	
Stand	Tilt
Case Color	Cloud Grey
Side Bezel Width	2 mm
Mounting	Supports VESA mount 100 x 100 mm
ThinkCentre M Series Support	Tiny Support
Pen	None
Dimensions (WxDxH) ^[1]	• Monitor with stand 611.5 x 181.5 x 474.6 mm (24.07 x 7.15 x 18.69 inches) • Head Only 611.5 x 41.0 x 355.6 mm (24.07 x 1.61 x 14.00 inches)
Packaging Dimensions (WxDxH)	715.0 x 113.0 x 417.0 mm (28.15 x 4.45 x 16.42 inches)
Weight ^[2]	• Monitor With Stand 3.9 kg (8.6 lbs) • Monitor Head Only 2.9 kg (6.4 lbs)
Packaging Weight	6.2 kg (13.7 lbs)
CONNECTIVITY	
Rear Ports	• 2x HDMI® 1.4 • 1x VGA • 1x audio-out (3.5mm)
SERVICE	
Base Warranty	1-year
CERTIFICATIONS	
Environmental Certification	ENERGY STAR® Certified, EPEAT™ Gold, EU Energy Efficiency Level (Level-E), Volatile Organic Compound Certification, RoHS
Ergonomic Certification	TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Flicker Free
Sync Technology	AMD FreeSync™
Special Features	• AMD FreeSync™ AMD FreeSync™ technology only can work with AMD Radeon™ series graphics card. • Lenovo® Artery (Lenovo® Accessories and Display Manager) Support Lenovo® Artery supports Windows® 10 & 11, Mac OS, and Windows®

On Arm (functions vary across systems). Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
• Natural Low Blue Light

SOFTWARE

Operating System	Support Windows® 10, Windows® 11
------------------	----------------------------------

ACCESSORIES

In the Box	• Monitor with stand • 1x HDMI® 1.4 cable (1.8m) • 1x Power cable (1.8m) • 1x Screw • Quick setup guide • Warranty booklet
------------	---

MODEL

Region	: NA
EAN / UPC / JAN	: 0199271706121 / 199271706121 / None
Announce Date	: 2025-09-08



Product image is a sample, it may not match the real color of this model

Note:
[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
 - California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>