



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- Intel N100 (4C / 4T, Max Turbo up to 3.4GHz, 6MB Intel Smart Cache)
- 1x 8GB SODIMM DDR5-5600
- 256GB SSD M.2 2280 PCIe 4.0x4 NVMe Opal 2.0
- Integrated Intel UHD Graphics
- IGEL Linux (IGEL COSMOS Select PAS 3-year)
- Case color - Eclipse Black
- 1-year, Onsite

Premier Support - A direct 24x7x365 line to our most elite technicians.

Advanced technical support, 24x7x365, in more than 100 markets

Technical Account Managers for proactive relationship and escalation management

Comprehensive hardware & OEM software support

Priority on service delivery and repair parts

Single point of contact for simplified end-to-end case management

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo’s Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that’s right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Recommended Accessories United States of America

ThinkPad Bluetooth Presenter Mouse (Aura Edition)

4Y51T62792

Lenovo Wireless Headphone 2000

4XD1V42464

Lenovo Essential FHD Webcam Gen2

4XC1S15018

>> [View More Accessories](#)

Recommended Services

Best

3Y Premier Support Plus upgrade from 1Y Onsite (5WS1P43522)

Better

4Y Onsite upgrade from 1Y Onsite (5WS1P43589)

Good

3Y Premier Support Upgrade from 1Y Onsite (5WS1P43563)

PERFORMANCE

Processor

Intel® N100 (4C / 4T, Max Turbo up to 3.4GHz, 6MB Intel® Smart Cache)

Graphics

Integrated Intel® UHD Graphics

Chipset

Intel® SoC Platform

Memory

1x 8GB SODIMM DDR5-5600

Memory Slots

One DDR5 SODIMM slot

Max Memory^{[1][2]}

Up to 16GB DDR5-5600

Storage

256GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Max Storage Support^[3]

One drive, up to 512GB M.2 SSD

Card Reader

No card reader

Optical

None

Audio Chip

High Definition (HD) Audio

Speakers

2Wx1

Power Supply^[4]

65W 89% Adapter

DESIGN

Keyboard

USB, Calliope, Black, English (US)

Mouse

USB Calliope Mouse, Black

Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

Case Color

Eclipse Black

Stand

Vertical Stand

Adapter Cage

None

Toolless Chassis Screw

None

Dust Filter

None

Mounting

None

IO Box

None

Pen

Pen Not Supported

Form Factor

Tiny (1L)

Dimensions (WxDxH)^[5]

• Tiny only (without rubber feet) | 179 x 182.9 x 34.5 mm (7.05 x 7.2 x 1.36 inches)

• Tiny only (with rubber feet) | 179 x 182.9 x 36.5 mm (7.05 x 7.2 x 1.44 inches)

Weight^[6]

Around 0.89 kg (1.96 lbs)

CONNECTIVITY

WLAN + Bluetooth

Intel® Wi-Fi® 6 AX203, 802.11ax 2x2 + BT5.2

WWAN

WWAN Not Supported

Ethernet

Integrated 100/1000M

Front Ports

• 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)

• 1x headphone / microphone combo jack (3.5mm)

Rear Ports

• 1x USB-A (USB 10Gbps / USB 3.2 Gen 2)

• 2x USB-A (Hi-Speed USB / USB 2.0), one supports Smart Power On

• 1x HDMI® 1.4

• 1x DisplayPort™ 1.4

• 1x Ethernet (RJ-45)

Optional Rear Ports (configured)

None

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0 integrated in SoC

Physical Locks

Kensington Security Slot™, 3 x 7 mm

Kensington Cable Lock

None

Chassis Intrusion Switch

Chassis intrusion switch

MANAGEABILITY

System Management

None

SERVICE

Base Warranty

1-year, Onsite

Included Upgrade

None

CERTIFICATIONS

Green Certifications

• ENERGY STAR® 9.0

• EPEAT™ Gold Registered

• ErP Lot 3/7

• GREENGUARD®

• RoHS compliant

• VOC Report

SOFTWARE

Operating System

IGEL Linux (IGEL COSMOS Select PAS 3-year)

Bundled Software

None

ACCESSORIES

Bundled Accessories

None

MODEL

TopSeller : Yes EAN / UPC / JAN: 199275512476

Announce Date: 2026-03-03 End of Support : 2032-04-30

Note:
[1] The max memory is based on the test results with current Lenovo memory offerings.
[2] Installed memory is actually 5600MHz, but may run at 4800MHz depending on the memory support capability of processor.
[3] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.
[4] When work with TIO monitor, an appropriate power adapter is needed. Customer may need to: ? Order a Tiny for TIO MT (13GF, 13GH) models ? Or order an additional 90W power adapter. If original power adapter is 65W. For detailed information, please refer to [Lenovo V100q Adapter Matrix](#)
[5] The system dimensions may vary depending on configurations.
[6] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.