



intel



intel

The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- Intel Core Ultra 7 268V, 8C (4P + 4LPE) / 8T, Max Turbo up to 5.0GHz, 12MB Intel Smart Cache
- 32GB Soldered LPDDR5X-8533, MoP Memory
- 512GB SSD M.2 2280 PCIe 4.0x4 NVMe Opal 2.0
- Integrated Intel Arc Graphics 140V
- Windows 11 Pro, English (US) / English (UK)
- Case color - Black, Paint
- 1-year, Courier or Carry-in

Premier Support - A direct 24x7x365 line to our most elite technicians.

- 

Advanced technical support, 24x7x365, in more than 100 markets
- 

Comprehensive hardware & OEM software support
- 

Single point of contact for simplified end-to-end case management
- 

Technical Account Managers for proactive relationship and escalation management
- 

Priority on service delivery and repair parts
- 

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Recommended Accessories Netherlands



Lenovo Dual-Mode Wireless ANC Headset 6550 (USB-C, Teams)
4XD1S19778



ThinkPad Universal Thunderbolt 4 Dock - EU/INA/VIE/ROK
40B00135EU



ThinkPad Bluetooth Presenter Mouse (Aura Edition)
4Y51T62792

>> [View More Accessories](#)

Recommended Services

Best

3Y Premier Support for AIPC upgrade from 1Y Courier/Carry-in (5WS1U93985)

Better

3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0E97384)

Good

3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0E97328)

PERFORMANCE

Processor

Intel Core™ Ultra 7 268V, 8C (4P + 4LPE) / 8T, Max Turbo up to 5.0GHz, 12MB Intel® Smart Cache

AI PC Category

Copilot+ PC

NPU

Integrated Intel® AI Boost, up to 48 TOPS

Graphics

Integrated Intel® Arc™ Graphics 140V

Chipset

Intel® SoC Platform

Memory

32GB Soldered LPDDR5X-8533, MoP Memory

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

32GB soldered memory, not upgradable

Storage

512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0^[1]

Storage Slot

Models with V or H series processor: one M.2 2280 PCIe® 5.0 x4 slot

Max Storage Support^[2]

One drive, up to 2TB M.2 2280 SSD

Card Reader

No Card Reader

Audio Chip

Lunar Lake: SoundWire®, Realtek® ALC713 codec

Speakers

Stereo speakers, 2W x2, Dolby Atmos®

Microphone

2x, 360°

Camera

FHD 1080p + IR Discrete with Privacy Shutter

Battery

57Wh

Power Adapter

65W USB-C® Slim GaN (2-pin)

DESIGN

Display

14" 2.8K (2880x1800) OLED 500nits Anti-glare / Anti-reflection / Anti-smudge, 100% DCI-P3, 120Hz VRR, DisplayHDR™ True Black 500, Dolby Vision®

Touchscreen

None

Screen-to-Body Ratio

89.2%

Pen

Pen Not Supported

Keyboard

Backlit, English

Touchpad

Trackpad

Dimensions (WxDxH)^[3]

312.80 x 214.75 x 8.08/14.37 (front/rear), 16.95 (maximum) mm; 12.31 x 8.45 x 0.32/0.56 (front/rear), 0.67 (maximum) inches

Weight^[4]

Starting at 986 g (2.17 lbs)

Case Color

Black, Paint

Case Material

Carbon Fiber (Top), Magnesium (Bottom)

SOFTWARE

Operating System

Windows® 11 Pro, English (US) / English (UK)

Bundled Software

Intel® Connectivity Performance Suite + Lenovo® AI Now

CONNECTIVITY

WLAN + Bluetooth

Intel® Wi-Fi® 7 BE201, 802.11be 2x2 + BT5.4, vPro®^[5]

WWAN

WWAN Not Supported

SIM Card

No physical SIM card inbox

Ethernet

No Onboard Ethernet^[6]

NFC

No NFC

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports (configured)

None

Docking

Various docking solutions supported via Thunderbolt™ / USB-C®. For more compatible docking solutions, please visit [Docking for ThinkPad® X1 Carbon Gen 13 Aura Edition](#)

SECURITY & PRIVACY

ThinkShield

ThinkShield is a comprehensive security solution that encompasses hardware, software, and supply chain components. For more detials, visit [here](#)

Security Chip

Discrete TPM 2.0 Enabled

Physical Locks

Kensington Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader

No Smart Card Reader

Fingerprint Reader

Touch Style, Match-on-Chip, in Keyboard Key

Other Security

- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management

Intel® vPro® Enterprise^[7]

SERVICE

Base Warranty

1-year, Courier or Carry-in

Included Upgrade

None

ACCESSORIES

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered^[8]
- ErP Lot 6/26
- RoHS compliant
- TCO Certified, generation 10

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

- Intel Evo™ Platform
- SGS High Performance AI PC Certification
- Eyesafe® Certified 2.0

MODEL

TopSeller	: Yes	EAN / UPC / JAN: 199275756672
Announce Date:	2026-03-06	End of Support : 2031-06-05

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
 - California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>
- To see more note information, please access the [web page](#).