



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- AMD Ryzen AI 7 PRO 350 (8C / 16T, 2.0 / 5.0GHz, 8MB L2 / 16MB L3)
- 64GB (16+48GB) SODIMM DDR5-5600 Non-ECC
- 1TB SSD M.2 2280 PCIe 4.0x4 Performance NVMe Opal 2.0
- Integrated AMD Radeon 860M Graphics
- Windows 11 Pro, English (US) / English (UK)
- Case color - Black
- 1Y Premier Support Upgrade from 1Y Courier/Carry-in

Premier Support - A direct 24x7x365 line to our most elite technicians.

- 

Advanced technical support, 24x7x365, in more than 100 markets
- 

Comprehensive hardware & OEM software support
- 

Single point of contact for simplified end-to-end case management
- 

Technical Account Managers for proactive relationship and escalation management
- 

Priority on service delivery and repair parts
- 

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Recommended Accessories United Kingdom



Lenovo Dual-Mode Wireless ANC Headset 6550 (USB-C, Teams)
4XD1S19778



ThinkPad Bluetooth Presenter Mouse (Aura Edition)
4Y51T62792



Lenovo 16" Laptop Everyday Backpack B510
4X41U80414

>> [View More Accessories](#)

Recommended Services

Best

5Y Premier Support for AIPC upgrade from 1Y Premier Support (5WS1U94201)

Better

3Y Premier Support for AIPC upgrade from 1Y Premier Support (5WS1U94199)

Good

3Y Premier Support Plus for AIPC upgrade from 1Y Premier Support (5WS1U94622)

PERFORMANCE

Processor

AMD Ryzen™ AI 7 PRO 350 (8C / 16T, 2.0 / 5.0GHz, 8MB L2 / 16MB L3)

AI PC Category

Copilot + PC, AI-Ready Workstations

NPU

Integrated AMD Ryzen™ AI, up to 50 TOPS

Graphics

Integrated AMD Radeon™ 860M Graphics

Chipset

AMD SoC Platform

Memory

64GB (16+48GB) SODIMM DDR5-5600 Non-ECC

Memory Slots

Two DDR5 SODIMM slots, dual-channel capable

Max Memory

Up to 96GB (2x 48GB DDR5 SODIMM)

Storage

1TB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

Storage Slot

One M.2 2280 PCIe® 4.0 x4 slot

Max Storage Support^[1]

One drive, up to 2TB M.2 2280 SSD

Card Reader

No card reader

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby Atmos®

Microphone

2x, Array

Camera

5.0MP + IR with Privacy Shutter and Human Presence Detection

Battery

52.5Wh

Power Adapter

65W USB-C® Slim GaN (2-pin)

DESIGN

Display

14" WUXGA (1920x1200) IPS 500nits Anti-glare, 100% sRGB, Low Power, Eyesafe®, UL Low Blue Light^[2]

Touchscreen

None

Color Calibration

ICC Template Color Calibration

Pen

Pen Not Supported

Keyboard

Backlit, English

Dimensions (WxDxH)^[3]

315.90 x 223.70 x 10.90/16.13 (front/rear), 21.8 (maximum) mm; 12.44 x 8.81 x 0.43/0.64 (front/rear), 0.86 (maximum) inches

Weight^[4]

Starting at 1.39 kg (3.06 lbs)

Case Color

Black

Case Material

PC + 20% CF + 50% GF + 30% PCC (Top), PC + 20% CF + 30% PCC (Bottom)

SOFTWARE

Operating System

Windows® 11 Pro, English (US) / English (UK)

Bundled Software

Lenovo® AI Now

CONNECTIVITY

WLAN + Bluetooth

MediaTek Wi-Fi® 7 MT7925, 802.11be 2x2 + BT5.4

WWAN

WWAN Not Supported

SIM Card

No physical SIM card inbox

Ethernet

100/1000M (RJ-45)

NFC

No NFC

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with PD 3.0 and DisplayPort™ 1.4
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (GbE RJ-45)
- 1x Kensington Nano Security Slot™

Optional Ports (configured)

None

Docking

Various docking solutions supported via Thunderbolt™ or USB-C®. For more compatible docking solutions, please visit [Docking for ThinkPad® P14s Gen 6 \(AMD\)](#)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0 Enabled

Physical Locks

Kensington Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader

No Smart Card Reader

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Other Security

- Bottom cover tamper detection
- Camera privacy shutter (camera models)
- Ultrasonic Human Presence Detection for IR camera
- IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management

AMD PRO Manageability

SERVICE

Base Warranty

1-year, Courier or Carry-in

Included Upgrade

1Y Premier Support Upgrade from 1Y Courier/Carry-in

ACCESSORIES

CERTIFICATIONS

ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

Green Certifications

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered^[5]
- RoHS compliant
- TCO Certified, generation 10

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

- Eyesafe® Certified 2.0
- UL Low Blue Light

MODEL

TopSeller	: Yes	EAN / UPC / JAN: 199275502408
Announce Date:	2026-03-03	End of Support : 2031-11-22

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
- California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>
- To see more note information, please access the [web page](#).