



LCD DISPLAY

VX2779-HD-PRO

Key Features

- SuperClear® IPS panel
- 180Hz Refresh rate delivers fluid visuals
- Rapid 1ms MPRT for crisp image
- AMD FreeSync™ and NVIDIA G-sync Compatible eliminate screen tearing and reduce stuttering
- HDR10 Delivers Stellar Contrast and Color Accuracy



Product Description

The ViewSonic VX2779-HD-PRO is a versatile 27-inch Full HD monitor designed to elevate your visual experience, whether you're working or gaming. With a high 180Hz refresh rate and lightning-fast 1ms MPRT response time, this monitor ensures smooth visuals and minimal input lag – ideal for gamers seeking a competitive advantage. Equipped with SuperClear® IPS technology, it boasts wide viewing angles and breathtaking visuals, perfect for immersive gaming sessions, creative endeavors, and efficient office work. Beyond performance, the monitor's sleek design elevates your workspace aesthetics, combining form and function for a complete package.

Visit Uswww.viewsonic.com

DISPLAY

Display Size (in.):	27
Viewable Area (in.):	27
Panel Type:	IPS Technology
Resolution:	1920 x 1080
Resolution Type:	FHD (Full HD)
Static Contrast Ratio:	1,000:1 (typ)
Dynamic Contrast Ratio:	50M:1
High Dynamic Range:	HDR10
Light Source:	LED
Brightness:	250 cd/m ² (typ)
Colors:	16.7M
Color Space Support:	8 bit (6 bit + FRC)
Aspect Ratio:	16:9
Response Time (MPRT):	1ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30000 Hrs (Min)
Curvature:	Flat
Refresh Rate (Hz):	180
Variable Refresh Rate Technology:	FreeSync, G-Sync compatible
Low Blue Light:	Software solution
Flicker-Free:	Yes
Color Gamut:	NTSC: 72% size (Typ) sRGB: 104% size (Typ)
Pixel Size:	0.311 mm (H) x 0.311 mm (V)
Surface Treatment:	Anti-Glare, Hard Coating (3H)

COMPATIBILITY

PC Resolution (max):	1920x1080
Mac® Resolution (max):	1920x1080
PC Operating System:	Windows 10/11 certified; macOS tested
Mac® Resolution (min):	1920x1080

CONNECTOR

3.5mm Audio Out:	1
HDMI 1.4:	2
DisplayPort:	1
Power in:	DC Socket (Center Positive)

POWER

Eco Mode (Conserve):	24W
Eco Mode (optimized):	28W
Consumption (typical):	30W
Consumption (max):	34W
Voltage:	AC 100-240V
Stand-by:	0.5W
Power Supply:	External Power Adaptor

ADDITIONAL HARDWARE

Kensington Lock Slot:	1
-----------------------	---

CONTROLS

Physical Controls:	Key 1 (favorite), Key 2, Key 3, Key 4, Key 5 (power)
On Screen Display:	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu

OPERATING CONDITIONS

Temperature:	32°F to 104°F (0°C to 40°C)
Humidity (non-condensing):	20% to 90%

WALL MOUNT

VESA Compatible:	100 x 100 mm
------------------	--------------

INPUT SIGNAL

Frequency Horizontal:	30 ~ 202KHz
Frequency Vertical:	48 ~ 180Hz

VIDEO INPUT

Digital Sync:	TMDS - HDMI (v1.4), PCI-E - DisplayPort (v1.4)
---------------	--

ERGONOMICS

Tilt (Forward/Back):	-5° / 20°
----------------------	-----------

WEIGHT (IMPERIAL)

Net (lbs):	9
Net Without Stand (lbs):	8
Gross (lbs):	12.1

WEIGHT (METRIC)

Net (kg):	4.1
Net Without Stand (kg):	3.7
Gross (kg):	5.5

DIMENSIONS (IMPERIAL) (WXHxD)

Packaging (in.):	26.8 x 18.1 x 5.3
Physical (in.):	24.2 x 17.9 x 7.1
Physical Without Stand (in.):	24.2 x 14.3 x 1.8

DIMENSIONS (METRIC) (WXHxD)

Packaging (mm):	680 x 460 x 135
Physical (mm):	615 x 454 x 182
Physical Without Stand (mm):	615 x 364 x 46

GENERAL

Regulations:	CE, CE EMC, CB, RoHS, ErP, REACH, WEEE, EAC, UkrSEPRO, BSMI, RCM, GEMS, BIS, CCC, China RoHS, China Energy Label
--------------	--

PACKAGE CONTENTS:	VX2779-HD-PRO x1, 3-pin Plug (IEC C13 / CEE22) x1, HDMI Cable (v1.4; Male-Male) x1, AC/DC Adapter x1, Quick Start Guide x1
-------------------	--

Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
-------------------	--

Warranty:	*Warranty offered may differ from market to market
-----------	--