



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- 39.7", 21:9, WUHD 5120 x 2160 resolution, TÜV certified IPS black, 2500R curved screen
- 98% DCI-P3 color gamut with factory calibration
- 24-120Hz variable refresh rate
- Thunderbolt™ 4 one cable solution with Thunderbolt™ out, DP out, PD3.1 140W power delivery, 2.5G RJ45, and USB ports
- Daisy chain support, Lenovo® patented True Split and (e)KVM functions
- Remote manageability with LDFM software; local monitor adjustment with LADM (ThinkColor) software
- Case color - Eclipse Black
- 3-year limited warranty

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support

- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories Netherlands



Lenovo USB 20Gbps USB-C to USB-C Cable 1.5m

4X91U92143



Lenovo Essential FHD Webcam Gen2

4XC1S15018



ThinkCentre Tiny Mounting Kit

4XF1R07369

>> [View More Accessories](#)

Recommended Services

Best

4Y Premier Support upgrade from 3Y Courier/CCI Product Exchange ThinkVision (5WS1N92563)

Better

3Y Premier Support upgrade from 3Y Courier/CCI Product Exchange ThinkVision (5WS1N92559)

PERFORMANCE**Display Size**

39.7"

View Area

929.3x392 mm

Panel

In-Plane Switching

Backlight

WLED

Aspect Ratio

21:9

Resolution

5120x2160

Pixel Pitch

0.1815x0.1815 mm

Dot / Pixel Per Inch

140 dpi

View Angle (H / V)

178° / 178°

Response Time

4ms GtG (Extreme mode) / 6ms GtG (Typical mode)

Color Support

1.07 Billion

Refresh Rate

24Hz - 120Hz

Brightness400 cd/m²**Contrast Ratio**

2000:1

Color Gamut

99% sRGB, 98% DCI-P3, 99% BT.709

Screen Surface Treatment

Anti-glare

Curvature

2500R

Camera

Modular Camera Support

Microphone

None

Speakers

5Wx2, Optional Soundbar Support

Power Consumption (Typical / Maximum)

41W / 300W

Power Adapter

Integrated

DESIGN**Stand**

Tilt, Swivel, Height Adjust Stand

Case Color

Eclipse Black

Side Bezel Width

2.0 mm

Mounting

Supports VESA mount 100 x 100 mm

ThinkCentre M Series Support

Tiny Support

Dimensions (WxDxH)^[1]

• Head Only | 947.6 x 105.3 x 419.5 mm (37.31 x 4.15 x 16.52 inches)

• Lowest Position | 947.6 x 227.1 x 453.5 mm (37.31 x 8.94 x 17.85 inches)

• Highest Position | 947.6 x 227.1 x 608.5 mm (37.31 x 8.94 x 23.96 inches)

Packaging Dimensions (WxDxH)

1071.0 x 227.0 x 525.0 mm (42.17 x 8.94 x 20.67 inches)

Weight^[2]

• Monitor With Stand | 13.5 kg (29.8 lbs)

• Monitor Head Only | 9.7 kg (21.4 lbs)

Packaging Weight

20.5 kg (45.1 lbs)

CONNECTIVITY**USB Port**

1x Thunderbolt™ 4 (40Gbps, PD3.1 up to 140W, DP1.4 Alt Mode HBR3, USB upstream), 1x USB-B (USB 5Gbps, USB upstream), 5x USB-A (USB 5Gbps, 1x BC 1.2, USB downstream), 2x USB-C® (USB 5Gbps, 15W PD, data only, USB downstream)

Video Connector

1x Thunderbolt™ 4 (40Gbps), 1x Thunderbolt™ 4 Out, 1x HDMI® 2.1 FRL, 1x DP 1.4 (HBR3), 1x DP 1.4 Out

Network Connectivity

1x RJ45, Ethernet (10M/100M/1000M/2500M)

SERVICE**Base Warranty**

3-year limited warranty

CERTIFICATIONS**Environmental Certification**

Energy Star Certified, TCO 10, TCO Edge 2.1, EPEAT™ Gold, EU Energy Level (Level-F), Volatile Organic Compound Certification, RoHS

Ergonomic Certification

Eyesafe® Display 2.0, TÜV Rheinland® Low Blue Light (Hardware solution), TÜV Rheinland® In-Plane Switching Black, TÜV Rheinland® Eye Comfort (5 Stars)

Sync Technology

None

Special Features

• HDR10 Compliance

• Factory Calibration: Avg. Delta E<2 at sRGB and DCI-P3

• Picture In Picture (PIP) / Picture By Picture (PBP) Support

- Lenovo® ThinkColour (Lenovo® Accessories and Display Manager) Support Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS (functions vary across systems). Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.

- AI Power Saving Mode

- DP Power Saving (Panel Replay)

- KVM Switch (with eKVM)

- LDFM (Lenovo® Display Fleet Manager)

- Mirrored Power Button

- Multi-sync

- Natural Low Blue Light

- Smart Power

- Smart Sensor (Ambient Light Sensor)

- True Split

SOFTWARE**Operating System**

Support Windows® 10, Windows® 11

ACCESSORIES**In the Box**

- Monitor with stand

- 1x DP 1.4 cable (1.8m)

- 1x USB-A to USB-B Gen 1 cable (1.8m)

- 1x Thunderbolt™ cable (1m, 40Gbps), for models 64B4Y** and 64B4X** only

- 1x Power cable (1.8m)

- Factory calibration report

- Quick setup guide

MODEL

Region : APS

EAN / UPC / JAN: 0199274964344 / 199274964344 / None

Announce Date : 2026-01-27

Note:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.

- Lenovo reserves the right to change specifications without notice.