

GAMING GEAR

FORGE GK600 TKL WIRELESS MARS







SPECIFICATIONS

MODEL NAME	FORGE GK600 TKL WIRELESS MARS
INTERFACE	USB Type-C (USB 2.0)
BACKLIGHT	20-Mode RGB
CONNECTIVITY	2.4 GHz Wireless / Bluetooth / USB 2.0
SWITCH TYPE	Mechanical Linear
KEY STROKE LIFE	50 Million
NORMAL KEYS	83 keys (Different by languages)
N-KEY ROLLOVER	Full Keys Anti-ghosting
ANTI-GHOSTING	26 Keys
OPERATING SYSTEM	Windows 10, 11 (or later) MacOS 11 (or later)
CABLE LENGTH	1.8m
PRODUCT DIMENSIONS	348 x 140 x 45 mm
WEIGHT	943g

FEATURES

HOT-SWAPPABLE DESIGN

Customizable keyboard design allows for swapping the default mechanical switches with third-party switches (5-pin) without soldering.

MECHANICAL LINEAR SWITCHES

The mechanical switches offer a linear profile and a precise feel for every key press.

VERSATILE CONNECTIVITY

Offers 2.4GHz wireless, Bluetooth, and wired USB Type-C for versatile device compatibility.

RESILIENT AESTHETICS

Dye-sublimated PBT keycaps ensure lasting durability, fade resistance, and a premium typing feel.

INTUITIVE CONTROL & DISPLAY

The 1.06-inch display shows battery status and RGB settings for quick access.

ENJOY THE SILENCE

Foam and gaskets ensure pure, satisfying switch acoustics with no unwanted noise.

ADJUSTABLE KEYBOARD ANGLES

Two keyboard feet support a tilt angle to ensure a more comfortable wrist position during gaming sessions.

RGB LED

Lighten the mood by playing with predefined effects for the preferred vibe.

Generated 2026-06-10, check for the latest version www.msi.com/datasheet. The information provided in this document is intended for informational purposes only and is subject to change without notice.

© 2026 Micro-Star Int'l Co.Ltd. MSI is a registered trademark of Micro-Star Int'l Co.Ltd. All rights reserved.