





Overview	
Dimensions	442.4 x 87.4 x 325 mm (17.4 x 3.4 x 12.8")
Managed Cameras	(100) HD (70) 2K (50) 4K
Managed Access Hubs ⓘ	150+
Storage Capacity	(8) 2.5/3.5" drive bays
Data Protection	✓
Networking Interface	(1) 10G SFP+ port (1) 2.5 GbE RJ45 port
Power Redundancy	✓ ⓘ
Form Factor	Rack Mount (2U)
Door Access Support	✓
Management Application	UniFi Protect UniFi Access UniFi Connect
Hardware	
Hard Drive Capacity	(8) 2.5/3.5" HDD / SSD support
Max. Power Budget for Drives	155W
Max. Power Consumption	200W
Power Method	(1) Universal AC input, 100–240V AC, 3A Max., 50/60 Hz (1) USP-RPS DC input, 11.5V DC
Power Supply	AC/DC, Internal PSU, 200W
Processor	Qualcomm® Kryo™ CPU built on Arm® Cortex® technology (4 nm) (1) Prime core (3.2 GHz) (4) Performance cores (2.8 GHz) (3) Efficiency cores (2.0 GHz)
Memory	16 GB
Management	Ethernet Bluetooth
Weight	8.4 kg (18.5 lb)
Enclosure Material	SGCC steel
Mount Material	SGCC steel
LEDs	Ethernet ✓ SFP+ ✓ HDD ✓ RPS ✓ System ✓
Ambient Operating Temperature	0 to 40° C (32 to 104° F)
Ambient Operating Humidity	5 to 95% noncondensing
NDAA Compliant	✓
Certifications	CE, FCC, IC
Software	
Application Requirements	UniFi Protect Version 7.1.55 or later. UniFi Access Version 4.2.16 or later.