LCD DISPLAY

VP2766-2K

Key **Features**



- **Lifelike Visuals:** Pantone-validated display covering 100% of the sRGB spectrum to offer vivid colors
- **Precise Color:** Factory-calibrated to professional-grade Delta E<2 color accuracy
- **Comfort & Productivity:** Eye ProTech+ and a smooth 120Hz refresh rate reduce visual fatigue and keep your workflow efficient
- **Seamless Connectivity:** 90W fast-charging USB-C port, HDMI 1.4, and USB-A 3.2 ports
- **Unlimited Flexibility:** Ergonomic stand with tilt, swivel, pivot and height adjustments

Product **Description**

Made for the modern creative, the ViewSonic ColorPro VP2766-2K brings beauty into your space with Pantone-validated 100% sRGB color. Featuring a smooth 120Hz refresh rate, it delivers clear, comfortable motion for everything from design and video editing to livestreaming. Eye ProTech+ helps reduce visual fatigue so you can stay in your flow longer, while 90W USB-C port offers fast charging and convenient single-cable connectivity to cut back on clutter. With flexible ergonomic adjustments that enable an optimal view every time, it's a monitor that settles naturally into your setup, supports the way you create, and allows your work to look exactly as you imagined.

1. DC In
2. HDMI x1
3. 3.5mm Audio Out x1
4. USB-A x1
5. USB-C x4

Visit Us www.viewsonic.com

DISPLAY

Display Size (in.):	27
Viewable Area (in.):	27
Panel Type:	IPS Technology
Resolution:	2560 x 1440
Resolution Type:	QHD (Quad HD)
Static Contrast Ratio:	1,500:1 (typ)
Dynamic Contrast Ratio:	20M:1
High Dynamic Range:	HDR10
Light Source:	LED
Brightness:	350 cd/m² (typ)
Colors:	16.7M
Color Space Support:	8 bit (6 bit + Hi-FRC)
Aspect Ratio:	16:9
Response Time (Typical GTG):	5ms
Response Time (GTG w/OD):	4.75ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30000 Hrs (Min)
Curvature:	Flat
Refresh Rate (Hz):	120
Variable Refresh Rate Technology:	Yes
Low Blue Light:	Hardware solution
Flicker-Free:	Yes
Color Gamut:	Adobe RGB: 89% size / 81% coverage (Typ) DCI-P3: 89% size / 87% coverage (Typ) EBU: 119% size / 100% coverage (Typ) REC709: 121% size / 100% coverage (Typ) SMPTE-C: 130% size / 100% coverage (Typ) NTSC: 85% size (Typ) sRGB: 121% size / 100% coverage (Typ)
Pixel Size:	0.233 mm (H) x 0.233 mm (V)
Surface Treatment:	Anti-Glare, Hard Coating (3H)

COMPATIBILITY

PC Resolution (max):	2560x1440
Mac® Resolution (max):	2560x1440
PC Operating System:	Windows 10/11 certified; macOS tested
Mac® Resolution (min):	2560x1440

CONNECTOR

USB 3.2 Type A Down Stream:	1
USB 3.2 Type C Down stream:	3 (15W power charger & Data transfer only)
USB 3.2 Type C Up Stream; DisplayPort Alt mode :	1 (90W power charger)
3.5mm Audio Out:	1
HDMI 2.1:	1
Power in:	DC Socket (Center Positive)

AUDIO

Internal Speakers:	3Watts x2

POWER

Eco Mode (Conserve):	14W
Eco Mode (optimized):	16W
Consumption (typical):	18W
Consumption (max):	22W
Voltage:	AC 100-240V
Stand-by:	0.5W
Power Supply:	External Power Adaptor

ADDITIONAL HARDWARE

Kensington Lock Slot:	1
Cable Organization:	Yes

CONTROLS

Physical Controls:	Key 1, Key 2, Key 3, Key 4, Key 5, Key 6 (power)
On Screen Display:	Input Select, Color Mode, ViewMode, Audio Adjust, Setup Menu

OPERATING CONDITIONS

Temperature:	32°F to 104°F (0°C to 40°C)
Humidity (non-condensing):	20% to 90%

WALL MOUNT

VESA Compatible:	100 x 100 mm

INPUT SIGNAL

Frequency Horizontal:	15 ~ 190KHz
Frequency Vertical:	48 ~ 120Hz

VIDEO INPUT

Digital Sync:	TMDS - HDMI (v2.1), Micro-Packet - Type C

ERGONOMICS

Height Adjust (mm):	130
Swivel:	90°
Tilt (Forward/Back):	-5° / 20°
Pivot (Right/Left):	90° / 90°

WEIGHT (IMPERIAL)

Net (lbs):	12.1
Net Without Stand (lbs):	8.2
Gross (lbs):	20.5

WEIGHT (METRIC)

Net (kg):	5.5
Net Without Stand (kg):	3.7
Gross (kg):	9.3

DIMENSIONS (IMPERIAL) (WXHXD)

Packaging (in.):	29.8 x 20.7 x 5.4
Physical (in.):	24.15 x 16.09~21.21 x 8.15
Physical Without Stand (in.):	24.15 x 14.35 x 1.45

DIMENSIONS (METRIC) (WXHXD)

Packaging (mm):	758 x 527 x 136
Physical (mm):	613.34 x 408.8~538.8 x 207
Physical Without Stand (mm):	613.34 x 364.46 x 36.71

GENERAL

Regulations:	Energy Star, CE, CE EMC, CB, RoHS, ErP, REACH, WEEE, EAC, UkrSEPRO, BSMI
PACKAGE CONTENTS:	VP2766-2K x1, 3-pin Plug (IEC C13 / CEE22) x1, HDMI Cable (v1.4; Male-Male) x1, USB Type-C Cable (Male-Male) x1, USB Type-C to Type-A 3.2 Gen1 Cable (Male-Male) x1, AC/DC Adapter x1, Quick Start Guide x1
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Warranty:	*Warranty offered may differ from market to market
Power Management:	Energy Star standards

Copyright © ViewSonic Corporation 2000-2026. All rights reserved.