



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- 27-inch, 16:9 QHD (2560 x 1440) IPS panel
- Attachable slot for ThinkCentre® and ThinkStation® Tiny PC
- 48-120Hz variable refresh rate
- 5MP camera, 2 x 3W front speakers, 2 microphones
- TÜV Rheinland® 5-star Eye Comfort Certification
- Lenovo® Display Fleet Manager and Lenovo® ThinkColor
- Case color - Eclipse Black
- 3-year limited warranty

Premier Support - A direct 24x7x365 line to our most elite technicians.

- | | |
|--|---|
|  Advanced technical support, 24x7x365, in more than 100 markets |  Technical Account Managers for proactive relationship and escalation management |
|  Comprehensive hardware & OEM software support |  Priority on service delivery and repair parts |
|  Single point of contact for simplified end-to-end case management |  Lenovo Service Connect Portal for customized reporting and product support |

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo’s Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that’s right for your circumstances.

- | | |
|----------------------------|----------------------------------|
| • Pick Up & Return Courier | • Technician Installed Customer |
| • Onsite Support | • Replaceable Unit Service |
| | • International Warranty Upgrade |

Product Illustration



PERFORMANCE

Display Size	27"
View Area	596.7×335.7 mm
Panel	In-Plane Switching
Backlight	WLED
Aspect Ratio	16:9
Resolution	2560x1440
Pixel Pitch	0.2331 x 0.2331 mm
Dot / Pixel Per Inch	109 dpi
View Angle (H / V)	178° / 178°
Response Time	4ms (Extreme mode) / 6ms (Typical mode)
Color Support	16.7 Million
Refresh Rate	48Hz - 120Hz
Brightness	350 cd/m²
Contrast Ratio	1500:1
Color Gamut	99% sRGB, 99%BT.709
Screen Surface Treatment	Anti-glare
Curvature	Flat Panel
Camera	5.0MP + IR
Microphone	Integrated Microphone
Speakers	3Wx2
Power Consumption (Typical / Maximum)	22W / 60W
Power Adapter	External, 170W
Touchscreen	None

DESIGN

Stand	Tilt, Swivel, Pivot, Height Adjust Stand
Case Color	Eclipse Black
Side Bezel Width	2.0 mm
Mounting	Supports VESA mount 100 x 100 mm
ThinkCentre M Series Support	Tiny Support
Pen	None
Dimensions (WxDxH) ^[1]	• Lowest Position 613.6 x 212.0 x 447.2 mm (24.16 x 8.35 x 17.61 inches) • Highest Position 613.6 x 212.0 x 602.2 mm (24.16 x 8.35 x 23.71 inches) • Head Only 613.6 x 79.5 x 404.7 (24.16 x 3.13 x 15.93 inches)
Packaging Dimensions (WxDxH)	692.0 x 156.0 x 526.0 mm (27.24 x 6.14 x 20.71 inches)
Weight ^[2]	• Monitor With Stand 7.2 kg (15.9 lbs) • Monitor Head Only 4.5 kg (9.9 lbs)
Packaging Weight	10.4 kg (22.9 lbs)
CONNECTIVITY	
Rear Ports	• 1x USB-B (USB 5Gbps / USB 3.2 Gen 1), USB upstream • 1x HDMI® 2.1 TMDS ^[3] • 1x DisplayPort™ 1.4 • 1x DisplayPort™ 1.4(Supports 3-in-1 ports to connect Tiny)
Left Ports	1x USB-A (USB 5Gbps / USB 3.2 Gen 1, supports 3-in-1 ports to connect Tiny), USB downstream / USB upstream
SERVICE	
Base Warranty	3-year limited warranty
CERTIFICATIONS	
Environmental Certification	ENERGY STAR® Certified, TCO 10.0, TCO Edge 2.1, EPEAT™ Gold, RoHS, Volatile Organic Compound Certification, EU Energy Level Certification (Level-E)
Ergonomic Certification	Eyesafe® Display 2.0, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Flicker Free, TÜV Rheinland® Eye Comfort 5 Stars
Sync Technology	QHD Support VRR (HDMI®)
Special Features	• Factory Calibration: Avg. Delta E<4 at sRGB

- Lenovo® ThinkColour (Lenovo® Accessories and Display Manager)^[4]
- LDFM (Lenovo® Display Fleet Manager)
- Mirrored Power Button
- Natural Low Blue Light
- QHD Support VRR (HDMI®)

SOFTWARE

Operating System
Support Windows® 10, Windows® 11

ACCESSORIES

- In the Box
- Monitor with stand
 - Power Brick (170W)
 - Power cable (1.0 m)
 - Quick setup guide

MODEL

Product : ThinkCentre® Tiny-In-One 27 Gen 6 Touch
Region : APS
EAN / UPC / JAN: 0199273501427 / 199273501427 / None
Announce Date : 2026-06-07

Note:
^[1] The system dimensions may vary depending on configurations.
^[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
^[3] Supports 2560x1440@120Hz as specified in HDMI 2.1
^[4] Formerly Lenovo Display Control Center. Supports Windows 10 & 11, Mac OS (functions vary across systems).

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.