



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- 27" QHD (2560 × 1440) fast VA display, 1500R curvature
- 240Hz refresh rate, 0.5ms MPRT response time
- AMD FreeSync™™ Premium and VESA Adaptive Sync support
- 99% sRGB and 95% DCI-P3 color gamut, 1.07B colors
- 400 nits brightness, VESA DisplayHDR™™ 400
- Natural Low Blue Light with Eyesafe® 2.0 certification
- Ergonomic stand with lift, tilt, pivot, and swivel adjustments
- 2 × HDMI® 2.1, 1 × DisplayPort™™ 1.4
- Lenovo® Accessory Display Manager (LADM) and Legion Space software support
- Case color - Eclipse Black
- 3-year

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

‘Getting started’ and ‘how-to’ assistance for hardware and software. Easy solutions that are simple to reach - that’s how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.


Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo’s Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that’s right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Recommended Accessories United States of America

	
Kensington MicroSaver DS 2.0 Cable Lock from Lenovo	Lenovo Cloth Gaming Mouse Pad M
4XE1L68273	GXH1C97873

>> [View More Accessories](#)

Product Illustration



PERFORMANCE

Display Size	27"
View Area	596.7x335.7 mm
Panel	Vertical Alignment
Backlight	WLED
Aspect Ratio	16:9
Resolution	2560x1440
Pixel Pitch	0.2331x0.2331 mm
Dot / Pixel Per Inch	109 dpi
View Angle (H / V)	178° / 178°
Response Time	0.5 ms (MPRT) / 1 ms (Level 4) / 2 ms (Level 3) / 3 ms (Level 2) / 4 ms (Level 1) / 6 ms (Off)
Color Support	1.07 Billion
Refresh Rate	240Hz
Brightness	400 cd/m²
Contrast Ratio	3000:1
Color Gamut	99% sRGB, 95% DCI-P3
Screen Surface Treatment	None
Curvature	1500R
Camera	None
Microphone	None
Speakers	None
Power Consumption (Typical / Maximum)	22W / 48W
Power Adapter	Integrated
Touchscreen	None

Smart System	None
DESIGN	
Stand	Tilt, Swivel, Pivot, Height Adjust Stand
Case Color	Eclipse Black
Side Bezel Width	2.0 mm
Mounting	Supports VESA mount 100 x 100 mm
ThinkCentre M Series Support	None
Pen	Pen Not Supported
Dimensions (WxDxH) ^[1]	• Lowest Position 617.0 x 200.0 x 413.6 mm (24.29 x 7.87 x 16.28 inches) • Highest Position 617.0 x 200.0 x 548.6 mm (24.29 x 7.87 x 21.60 inches) • Unpacked Head Only 617.0 x 91.8 x 366.7 mm (24.29 x 3.61 x 14.44 inches)
Packaging Dimensions (WxDxH)	820.0 x 150.0 x 510.0 mm (32.28 x 5.91 x 20.08 inches)
Weight ^[2]	• Monitor With Stand 6.5 kg (14.3 lbs) • Monitor Head Only 4.0 kg (8.8 lbs)
Packaging Weight	• 8.7 kg (19.1 lbs) EPS • Pulp: 9.6 kg (21.2 lbs)
CONNECTIVITY	
Rear Ports	• 2x HDMI® 2.1 TMDS ^[3] • 1x DisplayPort™ 1.4 (HBR2) ^[4]
SERVICE	
Base Warranty	3-year
CERTIFICATIONS	
Environmental Certification	RoHS, EU Energy Efficiency Level (Level-E), Volatile Organic Compound Certification
Ergonomic Certification	TÜV Low Blue Light (Hardware solution), Eyesafe® Display 2.0
Sync Technology	AMD FreeSync™ Premium, VESA Adaptive Sync
Special Features	• DisplayHDR™ 400 • AMD FreeSync™ Premium

- VESA Adaptive Sync
- Lenovo® Artery (Lenovo® Accessories and Display Manager)^[5]
- Legion Space
- Gaming Console Support
- Mirrored Power Button
- Natural Low Blue Light

SOFTWARE

Operating System
Support Windows® 10, Windows® 11

ACCESSORIES

- In the Box
- Monitor with stand
 - 1x DP cable (1.8m)
 - 1x Power cable (1.8m)
 - Quick setup guide
 - Warranty booklet

MODEL

Region : NA
EAN / UPC / JAN: 0199273576036 / 199273576036 / None
Announce Date : 2026-06-15

Note:
^[1] The system dimensions may vary depending on configurations.
^[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
^[3] Supports 2560 x 1440 @ 144Hz as specified in HDMI 2.1.
^[4] Supports 2560 x 1440 @ 240Hz bandwidth 21.6Gbps
^[5] Formerly Lenovo Display Control Center. Supports Windows 10 & 11, Mac OS (functions vary across systems).

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
- California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>