

HP LaserJet 3052/3055 All-in-One



Benefit from full functionality with the compact, flatbed HP LaserJet 3052 and 3055 All-in-One. Versatile and reliable, it lets you produce professional documents quickly with fast print, fax*, scan and copy functions, plus network connectivity.



HP LaserJet 3052
All-in-One



HP LaserJet 3055
All-in-One

Ideal for individuals and small work teams in micro to medium-sized businesses, as well as home office users, the HP LaserJet 3052 and 3055 All-in-ones are fast, versatile, reliable devices for printing, faxing*, scanning and copying professional documents.

Get performance you can rely on to produce professional quality documents promptly.

- Quickly print and copy documents at up to 18 ppm
- True 1200 dpi for printing crisp text and sharp images
- Instant-on Technology ensures a first printed page out in just 8 seconds
- Handle complex print jobs with a 264 MHz processor and powerful 64 MB memory for fast document handling
- Conveniently and reliably share your device thanks to integrated 10/100 Ethernet networking and Hi-Speed USB
- Depend on built-in support for PCL 5e, PCL6 and HP Postscript level 3 emulation.

Handle all your essential day-to-day tasks easily with this all-in-one's versatile features.

- Benefit from advanced copy functions such as automatic collation, reduce/enlarge and fit-to-page
- Copy a variety of materials on the flatbed scanner including books and other bound documents, while the 50-sheet automatic document feeder enables unattended faxing, scanning and copying of multi-page documents
- Fast and advanced 33.6 Kbps faxing* including delayed faxing and fax to and from PC**
- Up to 19200 dpi scan resolution yields high-quality colour images.

Save space and simplify office tasks with multiple functions in one reliable, compact device.

- The compact design of this flatbed all-in-one lets you make the most of your office space
- Easy to use and maintain thanks to an intuitive front-panel interface with backlit display and straightforward, uncomplicated software – focus on your work, not on your equipment
- Using functions simultaneously allows efficient multi-tasking
- All-in-one HP print cartridges are clean and simple to replace
- Robust 7,000 page per month duty cycle and proven HP LaserJet quality.

*Available with the HP LaserJet 3055 All-in-One.

**Fax to and from PC available with Microsoft® Windows® 2000 and XP.

Technical specifications

Print technology	Monochrome Laser		
Print speed	Up to 18 ppm. First page out black: 8 sec. for printing (Instant-on Technology virtually eliminating warm-up time – from cold or warm start).. (Exact speed varies depending on the system configuration, software program and document complexity)		
Processor	264 MHz. Motorola Coldfire® v 4e		
Memory	64 MB		
Print	Quality Printer languages Economical printing Typefaces/fonts Duty cycle Print margins (mm)		
	Up to 1200 x 1200 dpi HP PCL 6, HP PCL 5e, HP Postscript Level 3 emulation Economode print quality setting prints text with less toner, N-up printing (multiple pages per sheet) PCL: 45 scalable TrueType fonts, PostScript: 35 scalable TrueType fonts		
Fax*	Modem speed Telecom Fax memory Fax resolution Quick dialing		
	33.6 Kbps (3 sec per page) Telecom: TBR-21: 1998, EG 201 121: 1998, FCC Part 68 Up to 110 pages (2 MB) Standard: 203 x 98 dpi. Fine: 203 x 196 dpi. Superfine: 300 x 300 dpi. Photo: 300 x 300 dpi 12 one-touch front panel keys		
Scan	Type Scan resolution Bit depth Grey scale level Twain version Scannable area Margins for scanned items		
	Flatbed, ADF. Colour scanning: Yes Optical: Up to 1200 dpi. Enhanced: Up to 19200 x 19200 dpi 24 bit 256 TWAIN compatible Version 1.9 Minimum media size: No minimum. Maximum media size: 216 x 381 mm Left: 4 mm. Top: 4 mm. Right: 4 mm. Bottom: 4 mm		
Copy	Copy speed Copy resolution Multiple copies Reduce/enlarge		
	Up to 18 ppm Up to 600 x 600 dpi Up to 99 copies (with automatic collation) 25 to 400% (1% increments)		
Media handling	Input: Tray 1 Tray 2 ADF Output: Duplex printing:		
	Capacity Up to 10 sheets Up to 250 sheets Up to 50 sheets Up to 100 sheets. Up to 10 envelopes. Up to 10 transparencies Manual (driver support provided)	Weight 60 to 163 g/m ² 60 to 105 g/m ² 60 to 90 g/m ² 60 to 105 g/m ²	Size A4, A5, B5, C5, C6, DL (ISO), postcard, 76 x 127 to 216 x 356 mm A4, A5, B5, 147 x 211 to 216 x 356 mm A4, A5, 127 x 127 to 216 x 381 mm
Media types	Paper (bond, colour, glossy, heavy, letterhead, light, plain, preprinted, prepunched, recycled, rough), envelopes, transparencies, labels, cardstock		
Interface and connectivity	Built-in 10/100 wired Ethernet network connectivity with 1 RJ-45 port; Hi-Speed USB (compatible with USB 2.0 specifications) port		
Operating systems compatibility	Microsoft® Windows® 2000, XP (full solution); 98 SE, Me, XP-64, Server 2003, Linux (print driver only); Mac OS X v 10.3 and higher (full solution). Optional: Windows XP 64-bit, UNIX, Linux, OS/2 (print functionality available via Web). Latest drivers available from http://www.hp.com		
Network operating systems compatibility	Via built-in 10/100 Ethernet connection (supports TCP/IP-based solutions): Microsoft® Windows NT® 4.0, 98, Me, 2000, XP, XP-64, Server 2003; Novell® NetWare NDPS services via TCP/IP only on 3.2, 4.2, 5.x, 6.x; HP Gateway (TCP/IP raw only) and Novell LPD gateway; Apple Mac OS X v 10.3 and later; Bonjour discovery supported; Red Hat Linux 6.x and later; SuSE Linux 6.x and later; HP-UX 10.20, 11.x; Solaris™ 2.5x, 2.6, 7, 8, 9, 10 (SPARC systems only); IBM AIX 3.2.5 and later; MPE-iX; Citrix MetaFrame; Windows Terminal Services		
Minimum system requirements	Microsoft® Windows® 98 SE, Me, Server 2003: any Pentium® II processor or greater, 64 MB RAM, 10 MB hard disk space, SVGA 800 x 600 with 16-bit colour display (print driver only); Windows 2000, XP: any Pentium II processor (Pentium III or greater recommended), 128 MB RAM, 250 MB hard disk space, SVGA 800 x 600 with 16-bit colour display, Internet Explorer 5.5 or greater (full install), CD-ROM drive, Hi-Speed USB (compatible with USB 2.0 specifications) port or network port. Mac OS X v 10.3.x; G3, G4 or G5 processor, 32 MB RAM, 30 MB disk space, Hi-Speed USB (compatible with USB 2.0 specifications) port or network port, CD-ROM drive		
Standard software	HP Toolbox FX, HP LaserJet Scan, TWAIN 1.9 or WIA scan drivers, Readiris PRO text recognition software (not installed with other software, separate installation required), printer drivers (HP PCL 6, HP PCL 5e, HP Postscript Level 3 emulation), installer/uninstaller, HP Director (Macintosh)		
Control panel	HP LaserJet 3052: Intuitive control panel with 2-line, 16-character back lit display, numeric buttons, menu and cancel controls, copy and scan controls; HP LaserJet 3055: Intuitive control panel with 2-line, 16-character back lit display, alphanumeric buttons, menu and cancel controls, fax, copy and scan controls, speed-dial keys		
Power	Requirements: Input voltage 220 to 240 VAC (+/- 10%), 50/60 Hz (+/- 2 Hz), 2.3 amp. Consumption: 0 watt (off), 10 watts (powersave), 13 watts (standby), 300 watts (active)		
Dimensions (w x d x h)	Out of package: 497 x 406 x 393 mm. Packaged: 600 x 500 x 505 mm		
Weight	Out of package: 12 kg. Packaged: 14.5 kg		
Printer management	HP Toolbox FX, HP Web Jetadmin, HP Embedded Web Server (Mac only)		
Operating environment	Operating temperature: 15 to 32.5° C. recommended operating temperature: 15 to 32.5° C. operating humidity: 10 to 80% RH. operating humidity recommended: 10 to 80% RH. storage temperature: -20 to 40° C. storage humidity: 0 to 95% RH. noiselevel per ISO 9296: sound power: LwAd 6.3 B(A). sound pressure: LpAm 50 dB(A)		
Certifications	CISPR 22: 1993+A1+A2/EN 55022: 1994+A1+A2 - Class B; EN 61000-3-2: 1995/A14: 2000; EN 61000-3-3: 1995+A1; EN 55024: 1998+A1+A2; FCC Title 47 CFR, Part 15 Class B/ICES-003, Issue 3; GB9254-1998. Regulatory standards: IEC 60950-1: 2001/EN 60950-1: 2001+A1; IEC 60825-1: 1993 + A1: 1997 + A2: 2001/EN 60825-1: 1994 + A1: 2002 + A2: 2001 (Class 1 Laser/LED Product); GB4943-1995. ENERGY STAR: Yes		
Warranty	One-year limited warranty		

Ordering information

Q6502A	HP LaserJet 3052 All-in-One, HP LaserJet Q2612A Black Print Cartridge, getting started guide, support flyer, CDs containing device software and electronic user's guide, Readiris PRO text recognition software, 250-sheet media input tray, ADF input support, ADF output support, output bin support, power cord(s), one year limited warranty
Q6503A	HP LaserJet 3055 All-in-One includes same as Q6502A plus phone cord(s)

Supplies

Q2612A	HP LaserJet Q2612A Black Print Cartridge with Ultraprecise Toner
C6518A	HP USB Cable, 2m
C6520A	HP USB Cable, 3m

Connectivity

U9809A/E	Return to HP, 3 years
UA152PA/PE	Post Warranty, Return to HP, 1 year

UD906E	Return to HP, 2 years
--------	-----------------------

H3110A/E	Installation & Network Configuration
----------	--------------------------------------

For a complete list of supplies, accessories and services, please refer to <http://www.hp.com>

<http://www.hp.com>



© 2006 Hewlett-Packard Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP Products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Published in EMEA 01/06 EEE

