Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Power Cord, C19 to 5-20P, 2.5m



AP9873

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

| Product or Component Type | Power cord |
|---------------------------|----------------|
| Input Connection Type | NEMA 5-20P |
| Cable length | 8.2 ft (2.5 m) |
| Number of cables | 1 |

Physical

| Color | Black |
|---------------------|-----------------------|
| Height | 2.01 in (5.1 cm) |
| Width | 9.02 in (22.9 cm) |
| Depth | 4.02 in (10.2 cm) |
| Net Weight | 0.49 lb(US) (0.22 kg) |
| Mounting preference | No preference |
| Mounting Mode | Not rack-mountable |

Input

| Input Frequency | 50/60 Hz |
|----------------------|----------|
| Permissible voltage | 100120 V |
| Max line current | 20 A |
| Input current limits | 20 A |
| Load Capacity | 2400 VA |

Output

| Max current draw | 20 A |
|--------------------------------|-------------------------|
| Number of power socket outlets | 1 IEC 60320 C19 |
| Protection Type | Without circuit breaker |

Conformance

| Product Certifications | CSA |
|------------------------|-----------|
| | UL Listed |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environmental

| Ambient air temperature for operation | 32113 °F (045 °C) | |
|---------------------------------------|--|--|
| Relative Humidity | 095 % | |
| Operating altitude | 010000 ft | |
| Ambient Air Temperature for Storage | -13149 °F (-2565 °C) | |
| Storage Relative Humidity | 095 % | |
| Storage altitude | 050000 ft (0.000000000015240.0000000000 m) | |

Ordering and shipping details

| Category | 11309-APC RESALE PRODUCTS | |
|-------------------|---------------------------|--|
| Discount Schedule | APC1 | |
| GTIN | 731304189367 | |
| Returnability | No | |
| Country of origin | US | |

Packing Units

| Unit Type of Package 1 | PCE |
|------------------------------|---------------------|
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4.02 in (10.2 cm) |
| Package 1 Width | 4.25 in (10.8 cm) |
| Package 1 Length | 12.52 in (31.8 cm) |
| Package 1 Weight | 0.7 lb(US) (0.3 kg) |

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

| EU RoHS Directive | Compliant |
|---------------------------|--|
| REACh Regulation | REACh Declaration |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |

Use Again

| ○ Repack and remanufacture | |
|----------------------------|-------------------------|
| Circularity Profile | End of Life Information |
| Take-back | Yes |