

# Rack PDU, Basic, Zero U, 15A, 100/120V, (14) 5-15

AP9567

#### **Overview**

Presentation	APC Basic Rack PDUs distribute reliable rack power distribution via a single input with multiple output receptacles. Easily mount this vertical PDU in racks or enclosures. It occupies zero U of valuable rack space, which allows space for more equipment in the rack. This vertical PDU does not require additional tools to mount into APC NetShelter Enclosures. Enables a quick recovery from overload events. Packaging Includes PDU, Installation guide, Rack Mounting brackets, Toolless Mounting Kit.
Lead time	Usually in Stock

#### Main

Color	Black	
Product or Component Type	PDU	
PDU Type	Basic	
Cord length	12 ft (3.7 m)	
Number of cables	1	
Provided Equipment	Installation guide Rack Mounting brackets Toolless Mounting Kit	

## Complementary

Input Voltage	100 V	
	120 V	
Height	24.02 in (61 cm)	
Width	1.73 in (4.4 cm)	
Output Voltage	100 V	
	120 V	
Depth	1.73 in (4.4 cm)	
Net Weight	4.81 lb(US) (2.18 kg)	
Mounting Location	Side	
Mounting preference	No preference	
Input Plug Type	NEMA 5-15P	
Mounting Mode	Rack-mounted	
Rack units	0U	
Mounting position	Vertical	
Line Rated Current	12 A	
Permissible voltage	100125 V	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Input current limits	15 A
Load Capacity	1400 VA
Input Frequency	50/60 Hz
Outlet type and quantity	14 NEMA 5-15R

## **Environment**

Product Certifications	cUL Listed METI Denan UL Listed
Ambient air temperature for operation	32113 °F (045 °C)
Relative Humidity	095 %
Operating altitude	010000 ft
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)
Storage Relative Humidity	095 %
Storage altitude	050000 ft (0.000000000015240.0000000000 m)

# Ordering and shipping details

GTIN 731304207061

# **Packing Units**

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	25.51 in (64.8 cm)	
Package 1 Width	5.98 in (15.2 cm)	
Package 1 Length	7.01 in (17.8 cm)	
Package 1 Weight	6.44 lb(US) (2.92 kg)	

# **Contractual warranty**

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	55
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Materials and Substances	
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
₩ Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	Yes