

AEC MODELS



Max Load
500lb
(227kg)

Adjustable Extension Column

FOR USE WITH PEERLESS-AV® DISPLAY MOUNTS,
PROJECTOR MOUNTS AND CEILING PLATE ACCESSORIES

Designed to blend in and work in almost any environment, our line of AEC adjustable columns range in lengths from 6-9" up to 10-12'. Whether it's for an office or mounted from a tall cathedral ceiling, the adjustable column supports up to 500lb, making it ideal for exhibit, retail or digital signage applications. The adjustment slot design makes for easy incremental height adjustments to find the perfect position and then securely locking it into place. The AEC column's cylinder shape conveniently offers ample internal space for cable management of multiple cords, ultimately giving a clean look to any installation.

- 1-1/2"-11.5 NPT (38mm) aluminum column threaded on both ends
- Height adjustment at 1" (25mm) increments
- Lightweight aluminum construction for ease of installation and lower freight cost
- Offers unobtrusive cable management
- Notched adjustment design enables easy height adjustment and position locking



EASE OF ADJUSTABILITY

Simplest slot design allows for easy glide adjustment

CABLE MANAGEMENT

Allows added capability for routing cables



Cable management



Available in black, silver or white to match displays, projectors and ceiling mount surfaces



RoHS
COMPLIANT

TAA
COMPLIANT

Please visit peerless-av.com/en-us/patents for patent information.

✉ info@peerless-av.com

🌐 peerless-av.com

peerless-AV®
Driving Technology Through Innovation

Model Numbers

WARRANTY: Limited 5-year

AEC Models: Adjustable Extension Column for use with Peerless-AV® Display Mounts, Projector Mounts and Ceiling Plate Accessories

Product Specifications

	DIMENSIONS (COLUMN LENGTH)	PRODUCT WEIGHT	LOAD CAPACITY	FINISH	AVAILABLE COLORS
AEC006009(-S)(-W)	6"-9" (0.15-0.23m)	1.0lb (0.45kg)	500lb (227kg)	Powder Coat	AEC006009 - AEC1012: Black AEC006009-S - AEC1012-S: Silver AEC006009-W - AEC1012-W: White
AEC009012(-S)(-W)	9"-12" (0.23-0.30m)	1.2lb (0.55kg)			
AEC012018(-S)(-W)	12"-18" (0.30-0.46m)	1.8lb (0.82kg)			
AEC018024(-S)(-W)	18"-24" (0.46-0.61m)	2.3lb (1.05kg)			
AEC0203(-S)(-W)	2'-3' (0.61-0.91m)	3.2lb (1.45kg)			
AEC0305(-S)(-W)	3'-5' (0.91-1.52m)	5.5lb (2.50kg)			
AEC0406(-S)(-W)	4'-6' (1.22-1.83m)	7.6lb (3.45kg)			
AEC0507(-S)(-W)	5'-7' (1.52-2.13m)	8.4lb (3.82kg)			
AEC0608(-S)(-W)	6'-8' (1.83-2.44m)	9.2lb (4.12kg)			
AEC0709(-W)	7'-9' (2.13-2.74m)	10.1lb (4.58kg)			
AEC0810(-S)(-W)	8'-10' (2.44-3.05m)	11.0lb (5.00kg)			
AEC0911(-W)	9'-11' (2.74-3.35m)	11.9lb (5.40kg)			
AEC1012(-S)(-W)	10'-12' (3.05-3.66m)	12.8lb (5.82kg)			


Package Specifications

	PACKAGE SIZE (D x L)	PACKAGE SHIP WEIGHT	PACKAGE UPC CODE		PACKAGE CONTENTS	UNITS IN PACKAGE
AEC006009(-S)(-W)	3" x 9" (76 x 228mm)	1.3lb (0.59kg)	AEC006009:	735029275121	Extension Column, Adjuster Column and M8 x 10mm Screw	1
AEC009012(-S)(-W)	3" x 12" (76 x 304mm)	1.6lb (0.73kg)	AEC006009-S:	735029275138		
AEC012018(-S)(-W)	3" x 14" (76 x 355mm)	2.2lb (1.00kg)	AEC006009-W:	735029275145		
AEC018024(-S)(-W)	3" x 21" (76 x 533mm)	2.9lb (1.32kg)	AEC009012:	735029302476		
AEC0203(-S)(-W)	3" x 27" (76 x 685mm)	4.1lb (1.86kg)	AEC009012-S:	735029302483		
AEC0305(-S)(-W)	3" x 41" (76 x 1041mm)	6.7lb (3.05kg)	AEC009012-W:	735029302490		
AEC0406(-S)(-W)	3" x 48" (76 x 1219mm)	9.1lb (4.14kg)	AEC012018:	735029275152		
AEC0507(-S)(-W)	3" x 61" (76 x 1549mm)	10.4lb (4.73kg)	AEC012018-S:	735029275169		
AEC0608(-S)(-W)	3" x 73" (76 x 1854mm)	11.4lb (5.18kg)	AEC012018-W:	735029275176		
AEC0709(-W)	3" x 85" (76 x 2,159mm)	12.7lb (5.74kg)	AEC018024:	735029275183		
AEC0810(-S)(-W)	3" x 97" (76 x 2464mm)	13.9lb (6.32kg)	AEC018024-S:	735029275190		
AEC0911(-W)	3" x 108" (76 x 2,756mm)	14.9lb (6.78kg)	AEC018024-W:	735029275206		
AEC1012(-S)(-W)	3" x 120" (76 x 3048mm)	16.0lb (7.27kg)	AEC0203:	735029267027		
			AEC0203-S:	735029267218		
			AEC0203-W:	735029267126		
			AEC0305:	735029267034		
			AEC0305-S:	735029267225		
			AEC0305-W:	735029267133		
			AEC0406:	735029267041		
			AEC0406-S:	735029267232		
			AEC0406-W:	735029267140		
			AEC0507:	735029302506		
			AEC0507-S:	735029302513		
			AEC0507-W:	735029302520		
			AEC0608:	735029267058		
			AEC0608-S:	735029267249		
			AEC0608-W:	735029267157		
			AEC0709:	735029363781		
			AEC0709-W:	735029363798		
			AEC0810:	735029267065		
			AEC0810-S:	735029267256		
			AEC0810-W:	735029267164		
			AEC0911:	735029363804		
			AEC0911-W:	735029363811		
			AEC1012:	735029267072		
			AEC1012-S:	735029267263		
			AEC1012-W:	735029267171		

All dimensions = inch (mm)

MODEL	Drop Length (x)
AEC006009	6.00" - 9.00" (152 - 228mm)
AEC009012	9.00" - 12.00" (228 - 304mm)
AEC012018	12.00" - 18.00" (304 - 457mm)
AEC18024	18.00" - 24.00" (457 - 609mm)
AEC0203	24.00" - 36.00" (609 - 914mm)
AEC0305	36.00" - 60.00" (914 - 1524mm)
AEC0406	48.00" - 72.00" (1219 - 1828mm)
AEC0507	60.00" - 84.00" (1524 - 2133mm)
AEC0608	72.00" - 96.00" (1828 - 2438mm)
AEC0709	84.00" - 108.00" (2134 - 2743mm)
AEC0810	96.00" - 120.00" (2438 - 3048mm)
AEC0911	108.00" - 132.00" (2743 - 3353mm)
AEC1012	120.00" - 144.00" (3048 - 3657mm)

*overall length is 1.0" (25.4mm) longer than drop length.



Architect Specifications

The Adjustable Extension Column shall be a Peerless-AV model AEC% and shall be located where indicated on the plans. Assembly and installation shall be done according to instructions provided by the manufacturer.

Visit peerless-av.com to see the complete line of AV solutions from Peerless-AV, including outdoor displays, kiosks, display mounts, projector mounts, carts/stands, and a full assortment of accessories.

Peerless-AV
2300 White Oak Circle
Aurora, IL 60502
USA
(800) 865-2112
(630) 375-5100

Peerless-AV EMEA
Unit 2 Curo Park
Frogmore, St. Albans
Hertfordshire, AL2 2DD
United Kingdom
+44 (0) 1923 200 100

Peerless-AV B.V.
Papendorpseweg 75
3528 BJ Utrecht
The Netherlands
+31 (0) 70 770 8037

Peerless-AV Latin America
Av. de las Industrias 413
Parque Industrial Escobedo
General Escobedo, N.L.,
México, 66062
+52 (81) 8384-8300

