Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Rack PDU, Basic, 1U, 15A, 120V, (10)5-15



AP9562

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

| Color | Black | |
|---------------------------|---|--|
| Product or Component Type | PDU | |
| PDU Type | Basic | |
| Cord length | 12 ft (3.7 m) | |
| Number of cables | 1 | |
| Provided Equipment | Installation guide Rack Mounting brackets | |

Complementary

| Input Voltage | 100 V | |
|--------------------------|---------------------|--|
| | 120 V | |
| Height | 1.73 in (4.4 cm) | |
| Width | 17.60 in (44.7 cm) | |
| Output Voltage | 120 V | |
| Depth | 2.24 in (5.7 cm) | |
| Net Weight | 5.5 lb(US) (2.5 kg) | |
| Mounting Location | Front Rear | |
| Mounting preference | No preference | |
| Input Plug Type | NEMA 5-15P | |
| Mounting Mode | Rack-mounted | |
| Rack units | 1U | |
| Mounting position | Horizontal | |
| Line Rated Current | 12 A | |
| Input current limits | 15 A | |
| Load Capacity | 1400 VA | |
| Input Frequency | 50/60 Hz | |
| Outlet type and quantity | 10 NEMA 5-15R | |

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Product Certifications | cUL Listed METI Denan UL Listed | |
|---------------------------------------|--|--|
| Ambient air temperature for operation | 23113 °F (-545 °C) | |
| Relative Humidity | 095 % | |
| Operating altitude | 010000 ft | |
| Ambient Air Temperature for Storage | -13149 °F (-2565 °C) | |
| Storage Relative Humidity | 095 % | |
| Storage altitude | 050000 ft (0.000000000015240.0000000000 m) | |

Ordering and shipping details

| Category | 11309-APC RESALE PRODUCTS | |
|-------------------|---------------------------|--|
| Discount Schedule | APC1 | |
| GTIN | 731304203865 | |
| Returnability | No | |
| Country of origin | IN | |

Packing Units

| Unit Type of Package 1 | PCE | |
|------------------------------|-----------------------|--|
| Number of Units in Package 1 | 1 | |
| Package 1 Height | 2.76 in (7 cm) | |
| Package 1 Width | 9.02 in (22.9 cm) | |
| Package 1 Length | 18.27 in (46.4 cm) | |
| Package 1 Weight | 8.02 lb(US) (3.64 kg) | |

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

| ⊘ Environmental footprint | |
|--|-------------------------------|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 114 |
| Environmental Disclosure | Product Environmental Profile |

Use Better

| EU RoHS Directive | Compliant |
|-----------------------------|--|
| REACh Regulation | REACh Declaration |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| ₩ Energy efficiency | |
| Optimized Energy Efficiency | Energy efficient product |

Use Again

| ○ Repack and remanufacture | |
|-----------------------------|---|
| Circularity Profile | End of Life Information |
| Halogen content performance | Product contains halogen above thresholds |
| Take-back | Yes |