Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Power Cord, Locking C19 to 5-15P, 3.0m

AP8750

Product availability: Stock - Normally stocked in distribution facility

Overview

Presentation	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Lead time	Usually in Stock

Main

Product or Component Type	Power cord
Main Output Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	9.84 ft (3.00 m)
Number of cables	1

Physical

Color	Black	
Height	9.06 in (23 cm)	
Width	9.06 in (23 cm)	
Depth	1.77 in (4.5 cm)	
Net Weight	1.12 lb(US) (0.51 kg)	
Mounting preference	No preference	
Mounting Mode	Not rack-mountable	

Input

Max line current	15 A	
Input current limits	15 A	

Output

Max current draw	15 A
Number of power socket outlets	1 IEC 60320 C19
Cord Length	10 ft (3.05 m)

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	CSA	
	PSE	
	UL Listed	

Environmental

Ambient air temperature for operation	32221 °F (0105 °C)	
Relative Humidity	2080 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13221 °F (-25105 °C)	
Storage Relative Humidity	2080 %	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS	
Discount Schedule	APC1	
GTIN	731304279730	
Returnability	No	
Country of origin	CN	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.06 in (23 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	9.06 in (23 cm)
Package 1 Weight	1.12 lb(US) (0.51 kg)
SCC14	10731304279737

Contractual warranty

Warrantv	2 years repair or replace	
wairanty	Z Vears repair or replace	



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes