

Product data sheet

Specifications

Power Cord, Locking C19 to L5-20P, 3.0m



AP8752

Product availability: Stock - Normally stocked in distribution facility

Overview

Presentation	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Lead time	Usually in Stock

Main

Product or Component Type	Power cord
Main Output Voltage	120 V
Input Connection Type	NEMA L5-20P
Cable length	9.84 ft (3.00 m)
Number of cables	1

Physical

Color	Black
Height	9.06 in (23 cm)
Width	9.06 in (23 cm)
Depth	1.77 in (4.5 cm)
Net Weight	1.59 lb(US) (0.72 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Max line current	20 A
Input current limits	20 A

Output

Max current draw	20 A
Number of power socket outlets	1 IEC 60320 C19
Cord Length	10 ft (3.05 m)

Conformance

Product Certifications	CSA UL Listed
------------------------	------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient air temperature for operation	32...221 °F (0...105 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...221 °F (-25...105 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304279754
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.06 in (23 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	9.06 in (23 cm)
Package 1 Weight	1.59 lb(US) (0.72 kg)
SCC14	10731304279751

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile
Use Better	
Materials and Substances	
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Use Again	
Repack and remanufacture	
Circularity Profile	End of Life Information
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes