

Product data sheet

Specifications



APC Service Bypass PDU, 120V 20AMP W/ (8) NEMA 5-15R AND (2) 5-20R

SBP2200RM

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Product or Component Type	Bypass kit
Main Output Voltage	120 V
Input Connection Type	NEMA 5-20P
Number of rack unit	2U
Cable length	7.9 ft (2.4 m)
Number of cables	1
Provided Equipment	User Manual Rack Mounting brackets
Range of Product	Maintenance Bypass Panels

Physical

Color	Black
Height	3.5 in (89 mm)
Width	17.008 in (432 mm)
Depth	3.0 in (76 mm)
Net Weight	6.50 lb(US) (2.95 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Input Frequency	50/60 Hz
permissible voltage	100...125 V
Max line current	20 A
Input current limits	20 A
Load Capacity	2200 VA
Load Power Factor Range	0...1

Output

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Total Current Draw per Phase	20 A
Number of power socket outlets	8 NEMA 5-15R 2 NEMA 5-20R
Number of power socket outlets	10
Protection Type	Circuit breaker
Cord Length	4 ft (1.2 m)
Efficiency	99 %

Conformance

Product Certifications	TÜV
------------------------	-----

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...15000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

Category	80230-IG SEBA TO SEUSA
Discount Schedule	BMS1
GTIN	731304266754
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	5.9 in (15.1 cm)
Package 1 Width	11.6 in (29.5 cm)
Package 1 Length	18.2 in (46.3 cm)
Package weight(Lbs)	8.4 lb(US) (3.8 kg)

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer

Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
Take-back	Yes
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

