

Product data sheet

Specifications



APC NetShelter SV, Server Rack Enclosure, 42U, 600W x 1060 D mm, with Sides, Black, Single Rack Unassembled

AR2400FP1

Overview

Presentation Not all installation sites have space clearance required to move and install standard height enclosures. This unassembled Universal IT enclosure option for low to medium density server and networking applications is packaged for transport through narrow spaces and assembly at the installation site.

Lead time Usually in Stock

Main

Product or Component Type Rack enclosure

Number of rack unit 42U

Provided equipment Adjustable vertical mounting rails
Baying hardware
Casters
Door handle
Doors
Installation guide
Key(s)
Keyed-alike doors and side panels
Leveling feet
Mounting Hardware
Pre-installed casters
2 x Plate
4 x Bolt down brackets
Roof
Side Panels
Side Panel Lock
Slam Latches

Physical

Height 81.0 in (2057 mm)

Width 23.6 in (600 mm)

Depth 41.7 in (1060 mm)

Net Weight 247.4 lb(US) (112.2 kg)

Color Black

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 30.6 in (777.2 mm)

Minimum Mounting Depth 6.6 in (167.6 mm)

Rack Width 19"

Marking 14 gauge EIA mounting rail
16 gauge front door
18 gauge post
16 gauge rear door
19 gauge roof
18 gauge side panels

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Permanent permissible load	1014 lb(US) (459.9 kg) dynamic 2205 lb(US) (1000.2 kg) static
-----------------------------------	--

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
------------------	-----------------------------------

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
-----------------	-----------------------------

GTIN	731304302049
-------------	--------------

Returnability	No
----------------------	----

Country of origin	CN
--------------------------	----

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Nbr. of units in pkg.	1
------------------------------	---

Package 1 Height	31.9 in (81 cm)
-------------------------	-----------------

Package 1 Width	26.9 in (68.3 cm)
------------------------	-------------------

Package 1 Length	87.8 in (223 cm)
-------------------------	------------------

Package weight(Lbs)	486.464 lb(US) (220.656 kg)
----------------------------	-----------------------------

Contractual warranty

Warranty (in months)	60
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	774 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	739 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	19 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	16 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	95
Circularity Profile	End of Life Information
Take-back	No

Image of product / Alternate images

Alternative



















Image of product in real life situation

