

## HP OfficeJet 250 Mobile All-in-One Printer (CZ992A)



**Print, scan, and copy from virtually anywhere with this powerful, portable all-in-one.**

Print, scan, and copy from nearly anywhere with this portable all-in-one. Easily connect to your printer with Bluetooth® Smart technology and Wi-Fi Direct®.[1,2] This quiet workhorse has a long battery life and delivers the most pages.[3]



### **Portability meets productivity**

Quickly print, copy, and scan multipage documents hands-free with the 10-page automatic document feeder.

### **Lead the way with fast, easy mobile printing**

Reduce charging interruptions with a long-lasting battery.

### **High-powered quality and reliability**

Power through the workday. Charge from home, in your car or office, and more.[6]

### **Featuring**

Unleash your printing [9]



## Specifications

<b>Print quality black (best)</b>	Up to 1200 x 1200 rendered dpi (when printing from a computer)
<b>Print quality color (best)</b>	Up to 4800 x 1200 optimized dpi color (when printing from a computer and 1200 input dpi)
<b>Print speed black (ISO, A4)</b>	On AC: up to 10 ppm; On Battery: up to 9 ppm
<b>Print speed black (ISO, letter)</b>	On AC: up to 10 ppm; On Battery: up to 9 ppm
<b>Print Speed Color (ISO)</b>	On AC: up to 7 ppm; On Battery: up to 6 ppm
<b>Print speed color (ISO)</b>	On AC: up to 7 ppm; On Battery: up to 6 ppm
<b>Print speed</b>	Print speed up to 9 ppm (black) and 6 ppm (color)
<b>Functions</b>	Print, copy, scan
<b>Duplex printing</b>	Manual (driver support provided)
<b>Duty cycle (monthly, A4)</b>	Up to 500 pages
<b>Duty cycle (monthly, letter)</b>	Up to 500 pages <sup>[7]</sup>
<b>Printer smart software features</b>	Automatic Paper Width Sensing
<b>Scanner advanced features</b>	10-page Automatic Document Feeder (ADF)
<b>Energy savings feature technology</b>	HP Auto-Off Technology
<b>Replacement cartridges</b>	HP 62 Black Original Ink Cartridge; HP 62 Tri-color Original Ink Cartridge; HP 62XL High Yield Black Original Ink Cartridge; HP 62XL High Yield Tri-color Original Ink Cartridge
<b>Connectivity, standard</b>	1 USB 2.0 device; 1 USB 2.0 host; 1 wireless; 1 wifi direct; 1 BLE
<b>Network capabilities</b>	Yes, via built-in wireless
<b>Wireless capability</b>	Yes. Wireless, wifi direct & BLE
<b>Mobile printing capability</b>	Chrome OS
<b>Network protocols, supported</b>	Wi-Fi network support
<b>Software included</b>	HP Dropbox, HP Google Drive, Microsoft DotNet
<b>Compatible Operating Systems</b>	Windows 11; Windows 10; Windows 8; Windows 8.1; Windows 7; Windows Vista; macOS 10.12 Sierra; macOS 10.13 High Sierra; macOS 10.14 Mojave; macOS 13 Ventura; macOS 14 Sonoma; Linux; Chrome OS
<b>Energy star certified</b>	Yes
<b>Ecolabels</b>	ENERGY STAR® qualified, EPEAT® Silver
<b>Copy speed black (best, A4)</b>	On AC: up to 2 ppm; On Battery: up to 2 ppm
<b>Copy speed black (best, letter)</b>	On AC: up to 2 ppm; On Battery: up to 2 ppm
<b>Copy speed color (best, A4)</b>	On AC: up to 1 ppm; On Battery: up to 1 ppm
<b>Copy speed color (best, letter)</b>	On AC: up to 1 ppm; On Battery: up to 1 ppm
<b>Scan speed (normal, A4)</b>	Up to 9 ppm black/white or greyscale; up to 3.6 ppm color
<b>Scan file format</b>	Scan File Type supported by Software: Bitmap (.bmp), JPEG (.jpg), PDF (.pdf), PNG (.png), Rich Text (.rtf), Searchable PDF (.pdf), Text (.txt), TIFF (.tif)
<b>Scan input modes</b>	Front-panel scan, copy; HP Officejet 250 Mobile AiO SW Driver: HP AIO apps in mobile device.
<b>Scan technology</b>	CIS
<b>Scanner type</b>	Sheet-feed
<b>Display</b>	2.65" CGD DISPLAY, IR Touch
<b>Minimum dimensions (W x D x H)</b>	380.2 x 198.3 x 91.3 mm
<b>Minimum dimensions (W x D x H)</b>	14.96 x 7.8 x 3.6 in
<b>Weight</b>	2.96 kg (3.06 kg with Battery) <sup>[2]</sup>
<b>Weight</b>	6.51 lb (6.73 lb with Battery)
<b>Power consumption</b>	0.14 watts (Manual-Off), 3.4 watts (Standby), 0.81 watts (Sleep) <sup>[3]</sup>
<b>Power supply type</b>	Built-in universal power supply
<b>What's in the box</b>	HP OfficeJet 250 Mobile All-in-One Printer; HP 62 Setup Black Ink Cartridge (~200 pages); HP 62 Setup Tricolor Ink Cartridge (~120 pages); Regulatory flyer; Setup Poster; Power Cord (US, EMEA, APJ); Rechargeable Battery. [For ink volume and page yield information, visit <a href="http://hp.com/go/learnaboutesupplies">hp.com/go/learnaboutesupplies</a> ]
<b>Manufacturer Warranty</b>	One-year limited hardware warranty; 24-hour, 7 days a week support

Top Recommended Displays, Accessories and Services

HP Inkjet Printer Cartridges and Ink Supplies

HP 62XL High Yield Black Original Ink Cartridge	C2P05AE
HP 62XL High Yield Tri-color Original Ink Cartridge	C2P07AE

## Messaging Footnotes

[1] Mobile device needs to support Bluetooth v4.0+ and be enabled. A mobile app such as HP AiO Remote must be installed and opened for printing. Mobile device must be within 5 feet of the printer. For details, see <http://www.hp.com/go/bleprinting>. Bluetooth is a trademark owned by its proprietor and used by HP under license.

[2] Mobile device needs to be connected directly to the Wi-Fi Direct® signal of a Wi-Fi Direct supported AiO or printer prior to printing. Depending on mobile device, an app or driver may also be required. For details, see <http://www.hp.com/go/mobileprinting>. Wi-Fi Direct is a registered trademark of Wi-Fi Alliance®.

[3] Best-in-class performance claim compares all inkjet color mobile printers as of October 2015 based on market share as reported by Q2 2015 IDC, based on manufacturer's published specifications.

[6] Supports USB charging in OFF mode when connected to a 1A-minimum-charge-capable USB charging port.

[9] Mobile device needs to be connected directly to the wireless network of a wireless direct-capable printer prior to printing. Depending on mobile device, an app or driver may also be required. Wireless performance is dependent on physical environment and distance from the access point in the printer.

## Technical Specifications Footnotes

[2] Weight varies as per configuration

[3] Power consumption varies with print job, the use of wireless connectivity and the charging of battery. Values given are nominal.

[7] HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement

---

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

