

Product datasheet

Specifications



Rack PDU, Switched, Zero U, 10A, 230V, (16) C13

AP7950B

Overview

Lead time Usually in Stock

Main

Colour	Black
Product or component type	PDU
PDU type	Switched
Cord length	3.05 m
Number of cables	1
Provided equipment	Cord retention bracket(s) Installation guide Rack mounting brackets Toolless mounting kit User manual

Complementary

Input Voltage	200 V 208 V 230 V
Height	124.5 cm
Width	5.6 cm
Output Voltage	230 V
Depth	4.4 cm
Net weight	4.32 kg
Mounting location	Rear
Mounting preference	No preference
Input Plug Type	IEC 60320 C14
Mounting mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
Permissible voltage	200...240 V
Max line current	10 A
Input current limits	10 A
Load capacity	2300 VA
Network frequency	47...63 Hz

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Outlet type and quantity	16 IEC 60320 C13
--------------------------	------------------

Environment

Product certifications	CE GOST IRAM VDE
------------------------	---------------------------

Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3
-----------	--

Ambient air temperature for operation	-5...45 °C
---------------------------------------	------------

Relative humidity	5...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient air temperature for storage	-25...65 °C
-------------------------------------	-------------

Storage Relative Humidity	5...95 %
---------------------------	----------

Storage altitude	0.0000000000...15240.0000000000 m
------------------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	213.4 cm
------------------	----------

Package 1 Width	12.7 cm
-----------------	---------

Package 1 Length	15.2 cm
------------------	---------

Package 1 Weight	5.23 kg
------------------	---------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle) **1735**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant with Exemptions**

SCIP Number **1cdb2fed-a06f-4574-913d-8df8e70936b2**

REACH Regulation [REACH Declaration](#)

Halogen content performance **Product contains halogen above thresholds**

Energy efficiency

Optimized Energy Efficiency **Energy efficient product**

Use Again

Repack and remanufacture

Circularity Profile [End of Life Information](#)

Removable battery **Yes**

Take-back **Yes**

Image of product / Alternate images

Alternative

