

Product data sheet

Specifications



APC NetShelter 13U Wallmount Rack Cabinet Vented Door Double Hinged Server Depth

AR100HD

Overview

Presentation	Ideal for retail, healthcare, and educational facilities, the wall rack offers an efficient solution for deploying server and networking equipment for edge computing applications. For areas with limited floor space. Designed to house your server, as well as network solutions such as network switches and patch panels. Rack hinges at the rear allowing for access to the back of the rack during installation and setup or while undergoing maintenance. The door is reversible allowing for the door to open direction desired to avoid interference with its surroundings. Optional 120V fan tray top-mounted and caster kit. Several APC Smart-UPS models low-profile provide easy UPS integration and mounting. 13U Wall mount cabinet, 19 inches maximum mounting depth, 200lb weight capacity, 19" rack width, ships fully assembled, vented door, 5 year APC warranty.
---------------------	--

Lead time	Usually in Stock
------------------	------------------

Main

Product or Component Type	Rack enclosure
Number of rack unit	13U
Number of cables	1
Provided equipment	Key(s) User Manual Wall-mounting template

Physical

Height	26.1 in (663 mm)
Width	23.0 in (584 mm)
Depth	24.8 in (631 mm)
Net Weight	94.20 lb(US) (42.73 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	19.0 in (482.6 mm)
Rack Width	19"
Marking	16 gauge EIA mounting rail 16 gauge front door 16 gauge post 13 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	200 lb(US) (90.7 kg) static

Conformance

Standards	EIA-310E
------------------	----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

GTIN 731304111467

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	33.0 in (83.8 cm)
Package 1 Width	27.008 in (68.6 cm)
Package 1 Length	30.5 in (77.5 cm)
Package weight(Lbs)	115.02 lb(US) (52.17 kg)

Contractual warranty

Warranty (in months) 60



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	183 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	175 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	4 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	4 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	95
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

