

MSA Uncoded Compatible 3m 10G SFP+ to SFP+ Direct Attach Breakout Cable Twinax - 10 GbE
SFP+ Copper DAC 10 Gbps Low Power Passive Transceiver Module DAC

Product ID: SFP10GPC3M



The SFP10GPC3M is an MSA compliant direct-attach copper SFP+ cable that's designed, programmed and tested to work in 10G network deployments. It delivers dependable 10 GbE connectivity over copper cabling, which is a cost-effective alternative to fiber-optic cable setups.

This passive Twinax cable supports 10 Gigabit Ethernet applications connected through SFP+ (Mini-GBIC) ports. The cable is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

At 3 meters long and designed for high-speed performance, this copper SFP+ cable is ideal for medium-distance applications such as across-rack network switch or server connections.

All StarTech.com SFP & SFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP Cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Use in 10Gb Ethernet network applications
- Point-to-point in-rack and across-rack server or network switch connections

Features

- **MSA UNCODED SFP+ CABLE (DAC):** 10G direct attach cable works with MSA compliant switches the accept uncoded transceivers and modules
- **TECHNICAL SPECS:** 3m (9.84ft) 10 Gbps Passive Twinax (Copper) 2x SFP+ Pluggable Connector 100 Ohm Impedance 30 AWG Wire Gauge PVC Cable Jacket Hot swappable MSA Compliant
- **DESIGNED FOR SERVER ROOMS:** Mini GBIC DAC is a cost-effective copper alternative to fiber cable inside & between racks. Factory termination means high performance & reliability with less maintenance.
- **OUTSTANDING SUPPORT:** Backed by StarTech.com for the life of the cable itself, not your equipment; our cables won't void your OEM support and with access to our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Low power 10 GbE DAC also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules and transceivers

Website Filters

| | |
|--------------|--------------|
| Warranty | Lifetime |
| Cable Length | 9.8 ft [3 m] |

Hardware

| | |
|-----------------------|--------------------------|
| Compatible Brand | MSA Compliant |
| Cable Jacket Material | PVC - Polyvinyl Chloride |

Performance

| | |
|------------------------------|-------------------|
| Maximum Data Transfer Rate | 10Gbps |
| Impedance | 100 Ohm |
| Compatible Networks | 10 Gbps |
| Power Consumption (In Watts) | < 0.1 W (per end) |

Connector(s)

| | |
|-------------|----------|
| Connector A | 1 - SFP+ |
| Connector B | 1 - SFP+ |

Power

| | |
|----------------|---------|
| Output Voltage | 3.3V DC |
|----------------|---------|

Environmental

| | |
|-----------------------|----------------------------|
| Operating Temperature | 0C to 70C (32F to 158F) |
| Storage Temperature | -40C to 80C (-40F to 158F) |
| Humidity | 35 - 60% RH |

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | Black |
| Product Length | 9.8 ft [3.0 m] |
| Product Width | 0.6 in [1.4 cm] |
| Product Height | 0.5 in [1.2 cm] |
| Weight of Product | 4.2 oz [120 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Length | 7.1 in [18.0 cm] |
| Package Width | 7.8 in [19.8 cm] |
| Package Height | 0.8 in [2.1 cm] |
| Shipping (Package) Weight | 4.8 oz [136.0 g] |

What's in the Box

| | |
|---------------------|----------------|
| Included in Package | 1 - SFP+ cable |
|---------------------|----------------|

Warranty Information

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

****Product appearance and specifications are subject to change without notice.***