



GUD3C06

USB-C Travel Dock with Power Pass Through

Quickly Add USB Ports Expand your laptop or tablet's USB-C port with three USB Type-A 3.0 ports. Use your existing USB peripherals like your favorite keyboard and mouse, printer, or HDD with your new mobile device.



HDMI[®]
HIGH-DEFINITION MULTIMEDIA INTERFACE



Features

- 8-in-1 Travel-size USB-C docking station for mobile professionals
- Charge laptop & devices with up to 100W pass-through **
- Connect an HDMI display and enjoy HD audio and video resolution to 4K
- SD/MicroSD card reader/writer supports memory expansion
- 3x USB 3.0 ports; 1x BC1.2 charging port (1.5A)
- Gigabit Ethernet Data Port*
- Compatible with Thunderbolt 3 (USB-C) laptops & tablets
- Rugged aluminum housing
- Fast Role Swap provides safe operation for connected devices during power changes
- HDCP 1.4 compliant
- Works with the new USB-C iPad Pro under mirror-mode

* For initial setup, Internet may take 1-3 minutes to connect.

** Power pass through offers up to 100W of charging power utilizing the laptop's USB-C power adapter. USB-C power adapter not included..

** Maximum of up to 85W of power can be delivered to the laptop after deduction of 15W used by the docking station. Pass-thru power delivered to the laptop is dependent upon the capacity of your USB-C power supply. Ex. If your USB-C power supply is 60W, then the maximum power can be delivered to the laptop is 60W-15W = 45W. If your power supply is 87W, then the maximum power can be delivered to the laptop is 87W-15W= 60W.

Requirements

- USB-C (Thunderbolt 3 compatible) device with DP Alt Mode support
- Windows 7/8/8.1/10/11
- Mac OS X 10.7+

Package Contents

- GUD3C06 x 1
- Quick Start Guide x 1
- Warranty Card x 1

www.iogear.com



- Chrome OS



Specifications

FUNCTION	GUD3C06
Upstream Port	
USB-C	USB 3.1 Gen 1 supports data and Power Pass through
Downstream Port	
Card Reader	Supports Secure Digital v3.0 UHS-I (Ultra High Speed)?SDR12 (12.5Mbyte/s)/SDR25(25Mbyte/s)/SDR50(50Mbyte/s)/DDR50(50Mbyte/s)/SDR104(104Mbyte/s)
Ethernet	Supports 10/100 /1000Mbps
HDMI	HDMI 1.4 compliant, resolution up to 4Kx2K @30Hz
USB-A	3x USB 3.0, 1 port supports BC1.2 fast charging
USB-C	1x USB 3.1 supports data transfer or Power Delivery 3.0
Power	
Power Pass-Thru	Up to 100W (A total of up to 85W can be charged to the laptop after deduction of max 15W used by the dock)
Data Rate	Up to 5Gbps
Video Resolution	Up to 4K@30Hz, with 16:9 ratio
Environment	
Humidity	10% to 90 % RH (no condensation)
Operation Temperature	0? to +45?
Operating System Requirements	
Mac	Mac OS X 10.7+
Windows	Windows 7 / 8 / 8.1 / 10
DIMENSIONS	GUD3C06
Unit Dimensions	
Height	2" (5.2cm)
Length	4.1" (10.5cm) + tethered USB-C connector 5.35" (13.6cm)
Depth	0.35" (0.9cm)
Inner Pack	
Height	6.30" (16cm)
Length	11.41" (29cm)
Width	5.91" (15cm)
Inner Pack Qty.	6
Unit Package Dimensions	
Height	5.71" (14.5cm)
Length	5.31" (13.5cm)
Depth	1.74" (4.4cm)
Master Carton	
Height	12.20" (31cm)
Width	13.39" (34cm)
Depth	12.6" (32cm)
Master Carton Qty.	24
Weight	
Master Carton Wt.	7 lbs (3.16kg)
Inner Pack Wt.	1.8 lbs (0.82kg)
Unit Pack Wt.	0.3lb (0.14kg)
Unit Wt.	0.2 lb (0.09kg)