

HP DesignJet Z6 24-in PostScript Printer (T8W15A)



High-definition prints, fast and secure. More quality with fewer inks.

Read details more clearly and see high-contrast color with new high-definition HP printheads. HP Pixel Control enables smooth gradients, and the integrated vertical trimmer streamlines finishing.[3] Handle complex files and secure your printers/data.



PRECISE—Clearly distinguish subtle details

Read details more clearly and see high-contrast color with new high-definition HP printheads.

FAST—Work without delays

Handle even the most complex files with powerful processing architecture and the Adobe PDF Print Engine.[2]

SECURE—Protect your work and your information

Protect printers/data from unauthorized access with HP Secure Boot, whitelisting, and encrypted hard disk.

Specifications

Print quality color (best)	Up to 2400 x 1200 optimized dpi
Functions	Print
Connectivity, standard	Gigabit Ethernet (1000Base-T) (802.3, 802.3u, 802.3ab); Hi-Speed USB 2.0 certified interface for direct printing from USB flash drive
Mobile printing capability	Direct print from mobile apps on iOS, Android and Chrome OS; email printing with HP ePrint and HP Smart app for iOS and Android.
Software included	HP Click printing software, HP PrintOS, HP Web Jetadmin, HP DesignJet Utility including HP Color Center, HP Partner Link, HP JetAdvantage Security Manager (optional), HP SmartStream (optional), HP SmartTracker (optional)
Sustainable impact specifications	30% post-consumer recycled plastic; Free, convenient HP ink cartridge and printhead recycling with HP Planet Partners; Highest WIR Print Permanence Ratings in the Industry; Compatible with FSC®-certified HP large format printing materials and HP Recycled Satin Canvas, and a range of recyclable HP media with a take-back program; ENERGY STAR® certified; EPEAT® registered
Energy star certified	Yes
Minimum dimensions (W x D x H)	1293 x 695 x 998 mm
Minimum dimensions (W x D x H)	50.9 x 27.4 x 39.3 in
Weight	66 kg
Weight	145 lb
Power consumption	<100 W (printing); <32 W (ready); <6.5 W (sleep); 0.1 W (off)
Environmental certification	ENERGY STAR; ErP; WEEE; RoHS (EU, China, Korea, India); REACH; EPEAT
What's in the box	HP DesignJet Z6 PostScript Printer, printheads, introductory ink cartridges, printer stand and media bin, spindle, quick reference guide, setup poster, power cord
Manufacturer Warranty	One-year limited hardware warranty

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[2] The Adobe PDF Print Engine (APPE) is Adobe's high speed, high fidelity print platform. Version 4 extends APPE's leading edge for print reproduction with new performance efficiencies and breakthrough rendering features. APPE 4 enables printers to increase workflow efficiency and capitalize on the profit potential of innovations in inkjet print technology. To learn more, visit <https://www.adobe.com/products/pdfprintengine.html>

[3] Vertical trimmer and dual rolls included with the HP DesignJet Z6dr 44-in PostScript® Printer with V-Trimmer only.

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

